



•

•

**Mechanical Data** 

Case: SOT363

DDA (XXXX) U

### **PNP PRE-BIASED DUAL TRANSISTOR IN SOT363**

Case Material: Molded Plastic, "Green" Molding Compound

Terminals: Finish - Matte Tin Plated Leads, Solderable per

UL Flammability Classification Rating 94V-0

Moisture Sensitivity: Level 1 per J-STD-020

MIL-STD-202, Method 208 (B3)

Weight: 0.006 grams (Approximate)


### Features

- Epitaxial Planar Die Construction
- Complementary NPN Types Available (DDC)
- Built-In Biasing Resistors
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DDA (XXXX) UQ are suitable for automotive applications requiring specific change control; these parts are AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/guality/product-definitions/

Part Number	R1 (NOM)	R2 (NOM)
DDA124EU	22kΩ	22kΩ
DDA144EU	47kΩ	47kΩ
DDA114YU	10kΩ	47kΩ
DDA123JU	2.2kΩ	47kΩ
DDA114EU	10kΩ	10kΩ

Part Number	R1 Only
DDA113TU	1kΩ
DDA143TU	4.7kΩ
DDA114TU	10kΩ



### Ordering Information (Notes 4, 5)

Product	Status	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
DDA124EU-7-F	Active	Standard	P17	7	8	3,000
DDA124EUQ-7-F	Active	Automotive	P17	7	8	3,000
DDA124EUQ-13-F	Active	Automotive	P17	13	8	10,000
DDA144EU-7-F	Active	Standard	P20	7	8	3,000
DDA144EUQ-7-F	Active	Automotive	P20	7	8	3,000
DDA114YU-7-F	Active	Standard	P14	7	8	3,000
DDA114YUQ-7-F	NRND (Use ADA114YUQ)	Automotive	P14	7	8	3,000
DDA123JU-7-F	Active	Standard	P06	7	8	3,000
DDA114EU-7-F	Active	Standard	P13	7	8	3,000
DDA114EUQ-7-F	NRND (Use ADA114EUQ)	Automotive	P13	7	8	3,000
DDA113TU-7-F	Active	Standard	P01	7	8	3,000
DDA143TU-7-F	Active	Standard	P07	7	8	3,000
DDA143TUQ-7-F	Active	Automotive	P07	7	8	3,000
DDA143TUQ-13-F	Active	Automotive	P07	13	8	10,000
DDA114TU-7-F	Active	Standard	P12	7	8	3,000
DDA114TUQ-7-F	Active	Automotive	P12	7	8	3,000
DDA114TUQ-13-F	Active	Automotive	P12	13	8	10,000

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.


3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

5. NRND = Not Recommended for New Design.



### **Marking Information**



Pxx = Product Type Marking Code (See Ordering Information) YM = Date Code Marking Y = Year (ex: I = 2021) M = Month (ex: 9 = September)

### Date Code Key

Year	2018		2021	2022	2023	2024	2025	2026	2027	2028	2029	2030
Code	F			J	K	L	М	Ν	0	Р	R	S
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec

## Absolute Maximum Ratings (@ T<sub>A</sub> = +25°C, unless otherwise specified.)

Charao	Characteristic		Value	Unit
Supply Voltage (1) to (6) and (4) to (3)		V <sub>CC</sub>	-50	V
Input Voltage (1) to (2) and (4) to (5)	DDA124EU DDA144EU DDA114YU DDA123JU DDA114EU DDA113TU DDA143TU DDA144TU	Vin	+10 to -40 +10 to -40 +6 to -40 +5 to -12 +10 to -40 +5V Max +5V Max +5V Max	V
Output Current	DDA124EU DDA144EU DDA114YU DDA123JU DDA114EU DDA114EU DDA113TU DDA143TU DDA114TU	Io	-30 -30 -70 -100 -50 -100 -100 -100	mA
Output Current	•	I <sub>C(max)</sub>	-100	mA

### Thermal Characteristics (@ T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation (Notes 6, 7)	PD	200	mW
Thermal Resistance, Junction to Ambient Air (Note 6)	R <sub>θJA</sub>	625	°C/W
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +150	°C

 Notes:
 6. Mounted on FR-4 PC Board with minimum recommended pad layout.

 7. 150mW per element must not be exceeded.



# **Electrical Characteristics** (@ T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic (DDA113TU & DDA143TU & DDA114TU only)	Symbol	Min	Тур	Мах	Unit	Test Condition
Collector-Base Breakdown Voltage	<b>BV</b> CBO	-50		_	V	I <sub>C</sub> = -50μA
Collector-Emitter Breakdown Voltage	$BV_{CEO}$	-50		_	V	I <sub>C</sub> = -1mA
Emitter-Base Breakdown Voltage	$BV_{EBO}$	-5		_	V	Ι <sub>Ε</sub> = -50μΑ
Collector Cutoff Current	I <sub>CBO</sub>	_		-0.5	μA	V <sub>CB</sub> = -50V
Emitter Cutoff Current	I <sub>EBO</sub>	_		-0.5	μA	V <sub>EB</sub> = -4V
Collector-Emitter Saturation Voltage	V <sub>CE(sat)</sub>	_	_	-0.3	v	I <sub>C</sub> /I <sub>B</sub> = -2.5mA / -0.25mA DDA143TU I <sub>C</sub> /I <sub>B</sub> = -1mA / -0.1mA DDA114TU I <sub>C</sub> /I <sub>B</sub> = -10mA / -1mA DDA113TU
DC Current Transfer Ratio	h <sub>FE</sub>	100 160	250 —	600 600		I <sub>C</sub> = -1mA, V <sub>CE</sub> = -5V I <sub>C</sub> = -1mA, V <sub>CE</sub> = -5V DDA143TU/Q
Input Resistor (R1) Tolerance	$\Delta R_1$	-30		+30	%	
Gain-Bandwidth Product (Note 8)	fT		250	—	MHz	V <sub>CE</sub> = -10V, I <sub>E</sub> = 5mA, f = 100MHz

Characterist	ic	Symbol	Min	Тур	Мах	Unit	Test Condition
	DDA124EU DDA144EU DDA114YU DDA123JU DDA123JU	V <sub>I(off)</sub>	-0.5 -0.5 -0.3 -0.5 -0.5	-1.1 -1.1 —  -1.1	_	V	V <sub>CC</sub> = -5V, I <sub>O</sub> = -100µA
Input Voltage	DDA124EU DDA144EU DDA114YU DDA123JU DDA123JU DDA114EU	VI(on)		-1.9 -1.9 — — —1.9	-3.0 -3.0 -1.4 -1.1 -3.0	V	$V_{O} = -0.3$ , $I_{O} = -5mA$ $V_{O} = -0.3$ , $I_{O} = -2mA$ $V_{O} = -0.3$ , $I_{O} = -1mA$ $V_{O} = -0.3$ , $I_{O} = -5mA$ $V_{O} = -0.3$ , $I_{O} = -10mA$
Output Voltage	DDA124EU DDA144EU DDA114YU DDA123JU DDA123JU	V <sub>O(on)</sub>		-0.1	-0.3	V	I <sub>O</sub> /I <sub>I</sub> = -10mA / -0.5mA I <sub>O</sub> /I <sub>I</sub> = -10mA / -0.5mA I <sub>O</sub> /I <sub>I</sub> = -5mA / -0.25mA I <sub>O</sub> /I <sub>I</sub> = -5mA / -0.25mA I <sub>O</sub> /I <sub>I</sub> = -10mA / -0.5mA
Input Current	DDA124EU DDA144EU DDA114YU DDA123JU DDA123JU DDA114EU	h			-0.36 -0.18 -0.88 -3.6 -0.88	mA	V <sub>1</sub> = -5V
Output Current		I <sub>O(off)</sub>	_	_	-0.5	μA	$V_{CC} = -50V, V_1 = -0V$
DC Current Gain	DDA124EU DDA124EUQ DDA144EU DDA114YU DDA114YU DDA123JU DDA114EU	GI	56 60 68 68 80 30			_	$V_{O} = -5V, I_{O} = -5mA$ $V_{O} = -5V, I_{O} = -5mA$ $V_{O} = -5V, I_{O} = -5mA$ $V_{O} = -5V, I_{O} = -10mA$ $V_{O} = -5V, I_{O} = -10mA$ $V_{O} = -5V, I_{O} = -5mA$
Input Resistor (R1) Tolerance		$\Delta R_1$	-30		+30	%	
Resistance Ratio Tolerance		R <sub>2</sub> /R <sub>1</sub>	-20		+20	%	
Gain-Bandwidth Product (Note 8	)	f <sub>T</sub>	_	250		MHz	V <sub>CE</sub> = -10V, I <sub>E</sub> = -5mA, f = 100MHz

Note: 8. Transistor - For Reference Only.



### Typical Curves – DDA123JU (@ T<sub>A</sub> = +25°C, unless otherwise specified.)




Document number: DS30346 Rev. 13 - 2

Downloaded from Arrow.com.

www.diodes.com



## Typical Curves – DDA114TU (@ T<sub>A</sub> = +25°C, unless otherwise specified.)




DDA (XXXX) U Document number: DS30346 Rev. 13 - 2 Downloaded from Arrow.com. 5 of 7 www.diodes.com



## **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.



	SOT363							
Dim	Min	Max	Тур					
A1	0.00	0.10	0.05					
A2	0.90	1.00	0.95					
b	0.10	0.30	0.25					
С	0.10	0.22	0.11					
D	1.80	2.20	2.15					
Е	2.00	2.20	2.10					
E1	1.15	1.35	1.30					
е	C	).650 E	SC					
F	0.40	0.45	0.425					
L	0.25	0.40	0.30					
а	0°	8°						
	Dimen	sions	in mm					

## **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)		
С	0.650		
G	1.300		
X	0.420		
Y	0.600		
Y1	2.500		

SOT363



### IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 products provided subject to Diodes' Standard Terms and Conditions of Sale Diodes are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com