

TES 34000

- **Part # : TES 34000**
- **Description : Engraving stylus**
- **Needle : Carbide**
- **Air consumption : 30 l/min. (unloaded)**
- **Rotation speed : 13 000 rpm**
- **Inlet thread : 1/4" BSPF**
- **Hose ID : 8 mm (5/16")**
- **Working pressure : 6,3 bar**
- **Sound level : 75 dBa**
- **Vibrations : 1,4 m/s²**
- **Length : 160 mm**
- **Weight : 0,24 kg**
- **Material : Aluminium body**



Applications

