

GP Batteries

PRODUCT SPECIFICATION

USB Standard Charger Model : U811

Revision History

Revision	Date	Initiator	Reason for Change
0.0	10 Jul 2017	CC Li	Initial release

Prepared By	Approved By
CC Li	Patrick Lee
Date: 10 Jul 2017	Date: 10 Jul 2017


GPI International Limited

7/F, Building 16W, 16 Science Park West Avenue
Hong Kong Science Park, New Territories, Hong Kong,
Tel: (852) 2484 3333 Fax: (852) 24805912
Email: gpii@goldpeak.com
Website: <http://www.gpbatteries.com>


GP Batteries

Product Specification

Model no.: U811



Product Name	: USB 8-Slot Charger U811
Input	: DC5V 1A
Charging Channels	: 4 independent channels ; 2 slots/channel for 2, 4, 6 or 8 pcs Ni-MH AA/AAA batteries
Charging Current	: 250mA approx for AA ; 140mA approx.. for AAA Ni-MH batteries
Charging Time	: 570 min for AA 2000mAh ; 410min for AAA 800mAh
Trickle Charging Current	: 25mA approx for AA ; 14mA approx. for AAA Ni-MH batteries
Standby current at no input	: <10uA
Operation Temperature	: 0°C to 40°C
LED Indication	: 1 Green LED per Channel, Green LED ON for 0.5 second after just USB power input Charging in progress - Green LED flashing Fully charged – Green LED ON
Safety protection	: 1) Timer protection – 6 or 12 hours according to switch setting 2) Battery Reverse polarity
Dimensions	: 130 (L) x 90 (W) x 23 (H) mm +/-0.5mm
Weight	: 93g +/- 10g approx.)
Certification	: CE, FCC, IEC, Rohs
Warranty Period	: 12 months from ex-factory date



Manufacturer reserves the right to alter or amend the design, model and specification without prior notice