

# CABLE ASSEMBLIES & CONNECTORS

## PRODUCT OVERVIEW

**RG-174** is a very small (approx. 0.1" or 2.5 mm) flexible cable best suited for mobile/portable applications up to 1900 MHz. It can be used in short runs up to 2.7 GHz. For miniature sized connectors it has the widest options available. This Cable covers Cellular, WiFi, and most IoT applications.

**LMR-100** is the low loss alternative for RG-174. It has the same size diameter and can be used with the same range of connectors. The cable is well shielded but is still flexible and easy to handle. This cable is double-shielded and suitable for outdoor/indoor use. It covers Cellular, WiFi, and most IoT applications.


**RF-195** would be suitable for cable runs over 15 ft (4.5 meters) or in high frequency applications up to 6GHz. This is our standard cable for applications above 2.5 GHz.

**LMR-240** is a lower loss cable than LL-195 and best suited for longer cable runs from 20 ft - 50 ft (6 meters - 15 meters) as well as for higher frequency applications up to 6 GHz or more.

**LMR-400** is suitable for long runs & higher frequency applications. Approximately 0.405" diameter (10 mm), it might be too large for some mobile installs, but is perfect for every base station transmitter or access point. Longer lead times may apply

CABLE LOSS PER FOOT ( 30 cm )

Cable Type	900 MHz	2000 MHz	2500 MHz	5000 MHz
RG-174	0.32 dB	0.49 dB	0.55 dB	NR
LMR-100	0.22 dB	0.30 dB	0.39 dB	0.50 dB
RF-195	0.10 dB	0.15 dB	0.17 dB	0.25 dB
LMR-240	0.07 dB	0.10 dB	0.12 dB	0.17 dB
LMR-400	0.04 dB	0.06 dB	0.07 dB	0.12 dB



## CUSTOM COAX CABLE ASSEMBLIES

C A 1 2 0 / 1 9 5 - C C

Cable Length ( Inches )

Cable Type

End Connector 1

End Connector 2

CABLE OPTIONS

Code	Cable	Diameter
174	RG-174	0.1" ( 2.5 mm )
100	LMR-100	0.1" ( 2.5 mm )
195	RF-195	0.1" ( 2.5 mm )
240	LMR-240	0.25" ( 6.3 mm )
400	LMR-400	0.405" ( 10 mm )

CONNECTOR OPTIONS

Code	Connector
C	SMA Plug
V	SMA Jack
X	N Plug ( Male )
Y	N Jack ( Female )
A	TNC J Plug
W	TNC Jack
J	Rev Pol SMA Plug

Other Configurations Available



US Headquarters +1.847.671.6690  
US/CA Toll Free +1.800.648.2800  
European Facility +44.1543.459555

www.MobileMark.com