





REV	DATE	DESCRIPTION
NC	07/23/04	INITIAL RELEASE



NOTES:
 1. CRIMPED FERRULE HEX SIZE :213*
 2. SOLDER CENTER CONTACT.

RECOMMENDED CABLE STRIPPING DIM'S
 FOR 6 GHz PERFORMANCE CABLE WITH FOLD BRAND.
 ELECTRICAL:
 A) IMPEDANCE: 50ohms
 B) FREQUENCY RANGE: DC-6 GHz
 C) VSWR (RETURN LOSS): 1.4 (13.5dB), MAX.
 D) DIELECTRIC WITHSTANDING VOLTAGE:
 1500 VRMS, MIN.

QTY	FINISH	MATERIAL	DESCRIPTION
1	NICKEL	BRASS	BODY
1	NATURAL	TEFLON	INSULATOR
1	GOLD	PHOS. BRONZE	CONTACT PIN
1	NICKEL	COPPER	FERRULE
1	NICKEL	BRASS	NUT

APPROVALS	DATE
DRWN: G.R.S.	07/23/04
CHECKED: ESSBO	
SHEET: 1 OF 1	

PART NO.	DESCR	REV	SCALE
122140RP	TNC REVERSE POLARITY R/A CRIMP PLUG (FOR RG-58/U, 58C/U CABLE)	NC	NA
122140RP			

DWG NO.	REV	SCALE
122140RP DWG	NC	NA

QTY	FINISH	MATERIAL	DESCRIPTION
1	NICKEL	BRASS	BODY
1	NATURAL	TEFLON	INSULATOR
1	GOLD	PHOS. BRONZE	CONTACT PIN
1	NICKEL	COPPER	FERRULE
1	NICKEL	BRASS	NUT

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS (IN PARENTHESES). DIMENSIONS FOR MILLIMETERS ARE: 0.5 - 3mm ± 0.20mm 3 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: 1:180 = 4/24 = ± 0.020 DO NOT SCALE DRAWING

Amphenol Connex

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122140RP](#)