

Q-150K




150°C , BLACK, MODIFIED THIN WALL FLEXIBLE PVDF TUBING
SHRINK RATIO 2:1

Features/Applications

Excellent flame-retardant, heat shrinkable polyvinylidene fluoride tubing for applications requiring high temperature performance, outstanding abrasion and cut-through resistance or superior chemical and solvent resistant properties. It reliably protects solder joints, terminals and connectors from most industrial fluids, solvents and chemicals.

- Operating temperature: -55°C to +150°C
- Minimum shrink temperature: 135°C
- Full recovery temperature: 150°C
- Approval: UL VW-1, File No. E245010
- Meets: SAE-AMS-DTL-23053/18
- Standard colors: Black, Clear
- RoHS Compliant



Technical Data		
Property	Test Method	Typical Data
Tensile Strength	ASTM D 2671	> 30 MPa
Ultimate Elongation	ASTM D 2671	> 150%
Flammability	VW-1	Pass
Volume Resistance	IEC 93	$\geq 10^{14} \Omega \cdot \text{cm}$
Copper Stability	180°C, 168 hrs.	Pass
Copper Corrosion	180°C, 168 hrs.	No Corrosion

Product Dimensions								
Size		As Supplied (mm)	After Recovered (mm)		Tubing Shape	Standard Packaging		
Inch	mm	Inside Diameter (min.)	Inside Diameter (max.)	Wall Thickness (min.)		Standard Spool *(SS) (Meter)	Cut to Length Pcs. *(QB) Qty per bag	
							6"	48"
3/64	1.2	1.2	0.6	0.26	Round	200	32	25
1/16	1.6	1.6	0.8	0.26	Round	200	28	25
3/32	2.4	2.4	1.2	0.26	Round	200	24	25
1/8	3.2	3.2	1.6	0.26	Round	100	20	25
3/16	4.8	4.8	2.4	0.26	Round	100	16	25
1/4	6.4	6.4	3.2	0.26	Round	100	12	25
3/8	9.5	9.5	4.8	0.30	Flat	50	8	25
1/2	12.7	12.7	6.4	0.30	Flat	50	4	5

Notes:

1. * See Part Number Guide for standard packaging codes..
2. Cross Reference Guide available.
3. Special sizes, packaging, colors and cut pieces are available upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

[Q-150K-1/2-02-QB48IN-5](#) [Q-150K-3/8-02-QB48IN-25](#) [Q-150K-1/8-02-QB48IN-25](#) [Q-150K-1/4-02-QB48IN-25](#) [Q-150K-1/16-02-QB48IN-25](#) [Q-150K-3/64-01-QB48IN-25](#) [Q-150K-1/16-01-QB48IN-25](#) [Q-150K-1/16-01-SS200M](#) [Q-150K-3/32-01-QB48IN-25](#) [Q-150K-1/8-01-QB48IN-25](#) [Q-150K-3/16-01-QB48IN-25](#) [Q-150K-1/4-01-QB48IN-25](#) [Q-150K-3/8-01-QB48IN-25](#) [Q-150K-1/2-01-QB48IN-5](#) [Q-150K-3/4-01-QB48IN-5](#) [Q-150K-3/4-01-SS50M](#) [Q-150K-1-01-QB48IN-5](#) [Q-150K-1-01-SS50M](#) [Q-150K-1 1/2-01-QB48IN-5](#) [Q-150K-1 1/2-01-SS30M](#) [Q-150K-3/32-02-SS200M](#) [Q-150K-3/8-02-SS50M](#) [Q-150K-1-02-SS50M](#) [Q-150K-1 1/2-02-QB48IN-5](#) [Q-150K-1 1/2-02-SS30M](#) [Q-150K-1-02-QB48IN-5](#) [Q-150K-3/32-02-QB48IN-25](#) [Q-150K-3/16-02-QB48IN-25](#) [Q-150K-3/64-02-QB48IN-25](#) [Q-150K-3/4-02-QB48IN-5](#) [Q-150K-3/32-01-SS200M](#) [Q-150K-1/8-01-SS200M](#) [Q-150K-3/16-01-QB6IN-16](#) [Q-150K-1/4-01-QB6IN-12](#) [Q-150K-1/4-01-SS100M](#) [Q-150K-3/8-01-QB6IN-8](#) [Q-150K-1/2-01-SS50M](#) [Q-150K-1/4-02-QB6IN-12](#) [Q-150K-3/8-02-QB6IN-8](#) [Q-150K-1/2-02-QB6IN-4](#) [Q-150K-3/64-01-QB6IN-32](#) [Q-150K-3/64-01-SS200M](#) [Q-150K-1/16-01-QB6IN-28](#) [Q-150K-3/32-01-QB6IN-24](#) [Q-150K-1/8-01-QB6IN-20](#) [Q-150K-3/16-01-SS100M](#) [Q-150K-3/8-01-SS50M](#) [Q-150K-1/8-02-QB6IN-20](#) [Q-150K-1/8-02-SS200M](#) [Q-150K-3/16-02-QB6IN-16](#) [Q-150K-3/16-02-SS100M](#) [Q-150K-1/4-02-SS100M](#) [Q-150K-1/2-02-SS50M](#) [Q-150K-1/2-01-QB6IN-4](#) [Q-150K-3/64-02-QB6IN-32](#) [Q-150K-3/64-02-SS200M](#) [Q-150K-1/16-02-QB6IN-28](#) [Q-150K-1/16-02-SS200M](#) [Q-150K-3/32-02-QB6IN-24](#)