


Number of contacts

# 64



## Female connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00		
				3	2	1
Female connector with solder pins 2.9 mm	64		Performance level 3 on request	09 02 264 6824 09 02 464 6824 <sup>b)</sup> 09 02 764 6824 <sup>c)</sup>	09 02 264 2824	
	SMC 64			09 02 264 6841 <sup>d)</sup>		
Female connector with solder pins 4.5 mm	64			09 02 264 6825 09 02 264 6825 222 <sup>f)</sup> 09 02 464 6825 <sup>b)</sup> 09 02 764 6825 <sup>c)</sup>	09 02 264 2825	
	SMC 64			09 02 264 6829 <sup>d)</sup>		
Female connector with solder pins 13 mm	64			09 02 264 6421		
Female connector with press-in pins 4.5 mm	64			09 02 264 6850 09 02 264 6850 222 <sup>f)</sup>	09 02 264 2850	
Female connector with press-in pins without flange 5.3 mm	64			09 02 264 6870		
Female connector with press-in pins 13.2 mm	64			09 02 264 6861 <sup>a)</sup>		
Female connector with wrap posts <sup>1)</sup> 13 mm	64			09 02 264 6821		
Female connector with solder lugs 5.2 mm	64		09 02 264 6823			

DIN Signal up to 2 A

01  
12

1) To be used only for wire wrap termination  
 a) Wrap posts selectively gold plated (performance level 3)  
 b) Connectors with snap-in clips see chapter 00  
 c) Connectors with coding see chapter 00

d) CTI > 400  
 f) Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2  
 Other contact arrangements on request