

PROFINET Hybrid Cable, 4-wire + 4x1.5, Cat. 5, FRNC

Advantages

- Suitable for PROFINET cabling Category 5 / Class D according to ISO/IEC 11801 respectively EN 50173-1 and ISO/IEC 24702 respectively EN 50173-3
- Capable for flexible cords
- Applicable for industrial premises
- RoHS conform, UL recognized, flame retardant FRNC

General

This data cable is suitable for PROFINET Hybrid cabling according to type B in industrial premises and areas. It is useable for flexible cords and installation also. The core is fitted with 4 data wires twisted to star quad that allows the transmission of Fast Ethernet 10/100Mbit/s and 4 power wires each of 1.5 mm² cross section. It is designed for fast assembling in benefit for the customer. The PROFINET Hybrid cable is best capable for termination with Han 3 A RJ45 Hybrid connector set.

Description

PROFINET Hybrid Cable,
4-wire + 4x1.5, Cat. 5, FRNC

10	m ring
20	m ring
50	m ring
100	m ring
500	m reel

Order number

09 45 600 0310
09 45 600 0330
09 45 600 0340
09 45 600 0300
09 45 600 0320



Quad

- Wire: Stranded tinned copper AWG 22/7
- Insulation: PE Ø 1.55 mm
- Colour: wh, ye, bu, og
- Screen: Aluminate foil overlapped, tinned copper wire braid, braid coverage about 85%

Power


- Wire: Stranded bare copper 84 x 0.15mm (AWG 16)
- Insulation: FRNC Ø 2.4 mm
- Colour: bk, number printed

Core

- Plastic tape overlaped
- Outer sheath: Thermoplastic Copolymer (FRNC), flame retardant

Color of outer sheath: green, RAL 6018
Overall diameter: 9.7 mm – 10.3 mm

Technical Characteristics

Performance	Category 5 according to EN 50288-2-1:2003, IEC 61156-5:2002
Mechanical Characteristics	
Minimal bending radius	During installation: 10 x diameter After installation: 5 x diameter
Tensile strength	max. 200 N
Electrical Characteristics at 20°C	
Quad	
Surface transfer impedance at 1 MHz	50 mOhm/m
Surface transfer impedance at 10 - 100 MHz	10 mOhm/m
Loop resistance	max. 120 Ohm/km
Insulation resistance	min. 500 MOhm x km
Signal runtime	5.3 ns/m
Characteristic impedance at 100 MHz	100 Ohm +/- 5 Ohm
Test voltage (wire/wire/screen rms 50Hz 1min)	1500 V
Operating voltage	150 V
Power	
Conductor resistance	max. 14 Ohm/km
Insulation resistance	min. 20 MOhm*km
Test voltage (wire/wire/screen rms 50Hz 1min)	1500 V
Operating voltage	150 V
Chemical Characteristics	
Flame retardant	IEC 60332-1-2
Free of hazardous substances	RoHS 2002/95/EG
Halogen free	
Thermal Characteristics	
Permissible temperature range	- 20° C to + 80° C
Printing	HARTING PROFINET HYBRID CABLE CAT 5 FRNC * 4xAWG22/7 + 4x1.5 (SHIELDED) E130266  AWM 21282 * 09456000300200 "internal lot number" "sequential length in meters"
Weight about	154 kg/km

Technical Characteristics

Frequency MHz	Attenuation dB/100m		NEXT dB		PS NEXT dB		EL FEXT dB		PS EL FEXT dB		Return Loss dB	
	typ.	Cat 5 max*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*	typ.	Cat 5 min*
1	2.1	2.1	65.3	65.3	62.3	62.3	63.8	63.8	60.8	60.8	-	-
4	4	4	56.3	56.3	53.3	53.3	51.8	51.8	48.8	48.8	23.0	23
10	6.3	6.3	50.3	50.3	47.3	47.3	43.8	43.8	40.8	40.8	25	25
16	8	8	47.2	47.2	44.2	44.2	39.7	39.7	36.7	36.7	25	25
20	9	9	45.8	45.8	42.8	42.8	37.8	37.8	34.8	34.8	25	25
31.25	11.4	11.4	42.9	42.9	39.9	39.9	33.9	33.9	30.9	30.9	23.6	23.6
62.5	16.5	16.5	38.4	38.4	35.4	35.4	27.9	27.9	24.9	24.9	21.5	21.5
100	21.3	21.3	35.3	35.3	32.3	32.3	23.8	23.8	20.8	20.8	20.1	20.1

* EN 50288-2-1:2003

All data given are in line with the actual state of art and therefore not binding.
HARTING reserves the right to modify designs without giving the relevant reasons.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09456000340](#) [09456000310](#) [09456000330](#)