


# $16 \times 16$ Crosspoint Switch Array

# AD75019

#### FEATURES

256 Switches in a 16  $\times$  16 Array Wide Signal Range: to Supply Rails of 24 V or ±12 V Low On-Resistance: 200  $\Omega$  Typ TTL/CMOS/Microprocessor-Compatible Control Lines Serial Input Simplifies Interface Serial Output Allows Cascading for More Channels Low Power Consumption: 2 mW Quiescent Compact 44-Lead PLCC

#### FUNCTIONAL BLOCK DIAGRAM



#### **PRODUCT DESCRIPTION**

The AD75019 contains 256 analog switches in a  $16 \times 16$  array. Any of the X or Y pins may serve as an input or output. Any or all of the X terminals may be programmed to connect to any or all of the Y terminals. The switches can accommodate signals with amplitudes up to the supply rails and have a typical onresistance of 150  $\Omega$ .

Data is loaded serially via the SIN input and clocked into an onboard 256-bit shift register via SCLK. When all the switch settings have been programmed, data is transferred into a set of 256 latches via PCLK. The serial shift register is dynamic, so there is a minimum clock rate of 20 kHz. The maximum clock rate of 5 MHz allows loading times as short as 52  $\mu$ s. The switch control latches are static and will hold their data as long as power is applied. To extend the number of switches in the array, you may cascade multiple AD75019s. The SOUT output is the end of the shift register, and may be connected to the SIN input of the next AD75019.

The AD75019 is fabricated in Analog Devices' BiMOS II process. This epitaxial BiCMOS process features CMOS devices for low distortion switches and bipolar devices for ESD protection.

#### REV. D

#### **Document Feedback**

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A. Tel: 781.329.4700 ©2018 Analog Devices, Inc. All rights reserved. Technical Support www.analog.com

# **AD75019—SPECIFICATIONS**<sup>1</sup>( $T_A = +25^{\circ}C$ , $V_{DD}$ and $V_{SS} = \pm 12$ V, $V_{CC} = +5$ V unless otherwise noted)

AD75019	Symbol	Min	Тур	Max	Unit
MULTIPLEXER					
Input Signal Range	V <sub>IN</sub>	$V_{SS} - 0.5$		$V_{DD} + 0.5$	V
Switch ON Resistance, $V_{DD}$ and $V_{SS} = \pm 12$ V, $V_{SIGNAL} = \pm 12$ V	R <sub>ON</sub>		150	300	Ω
Switch ON Resistance, $V_{DD}$ and $V_{SS} = \pm 5 \text{ V}$ , $V_{SIGNAL} = \pm 5 \text{ V}$	R <sub>ON</sub>		300	500	Ω
Switch ON Resistance Matching <sup>2</sup> , $V_{SIGNAL} = \pm 12 V$	$\Delta R_{ON}$		20	30	Ω
Leakage Current, $V_{SIGNAL} = \pm 10$ V			2	10	nA
Input/Output Capacitance	C <sub>IN</sub>			25	pF
Isolation Between Any Two Channels					
$R_s = 600 \Omega$ , $R_L = 10 k\Omega$ , $V_{SIGNAL} = 2 V p-p$					
$f_{SIGNAL} = 1 \text{ kHz}$		92			dB
$f_{SIGNAL} = 20 \text{ kHz}$		69			dB
$f_{SIGNAL} = 1 \text{ MHz}$		38			dB
Total Harmonic Distortion					
$R_s = 600 \Omega$ , $R_L = 10 k\Omega$ , $V_{SIGNAL} = 2 V p-p$				0.01	%
Switch Frequency Response, -3 dB					
$R_s = 600 \Omega$ , $R_L = 10 k\Omega$ , $V_{SIGNAL} = 2 V p-p$		20			MHz
Propagation Delay			4	8	ns
DIGITAL INPUTS (SIN, SCLK, PCLK)					
Logic Levels (TTL Compatible)					
Input Voltage, Logic "1"	$V_{IH}$	2.4		5.5	V
Input Voltage, Logic "0"	V <sub>IL</sub>	0		0.8	V
Input Current, $V_{\rm H} = 5.5 \text{ V}$	I <sub>IH</sub>			$\pm 1$	μA
Input Current, $V_{II} = 0.8 V$	I			$\pm 1$	μĂ
Input Capacitance	Č <sub>IN</sub>			10	pF
DIGITAL OUTPUTS (SOUT)					
Logic Levels (TTL Compatible)					
Output Voltage, Logic "1"	V <sub>OH</sub>	2.8			V
Output Voltage, Logic "0"	V <sub>OL</sub>			0.4	v
Output Current, $V_{OH} = 2.8 V$	I <sub>OH</sub>	3.2			mA
Output Current, $V_{OL} = 0.4 V$	I <sub>OL</sub>	3.2			mA
POWER SUPPLY REQUIREMENTS	01				
Voltage Range, Total Analog	$V_{DD} - V_{SS}$	9.0		25.2	v
Voltage Range, Positive Analog	$V_{DD} - V_{DGND}$			25.2	v
Voltage Range, Negative Analog	$V_{SS} - V_{DGND}$	-20.7		0	v
Voltage Range, Digital	$V_{CC} - V_{DGND}$		5	5.5	v
Supply Current, SCLK = 5 MHz,	$I_{DD}, I_{SS}$	1.5	2	±70	mA
$V_{II} = 0.8 \text{ V}, V_{IH} = 2.4 \text{ V}$	$I_{\rm DD}$ , $I_{\rm SS}$ $I_{\rm CC}$			800	μΑ
$v_{\rm IL} = 0.0 v$ , $v_{\rm IH} = 2.4 v$ Supply Current, Quiescent,	$I_{DD}$ , $I_{SS}$			±400	μΑ
$V_{IL} = 0.8 \text{ V}, V_{IH} = 2.4 \text{ V}$			-	100	μΑ
$v_{\rm IL} - 0.0 v, v_{\rm IH} = 2.4 v$	I <sub>CC</sub>		-	100	μΑ


NOTES <sup>1</sup>All minimum and maximum specifications are guaranteed, and specifications shown in **boldface** are tested on all production units at final electrical test. Results from those tests

are used to calculate outgoing quality levels. <sup>2</sup>Switch resistance matching is measured with zero volts at each analog input and refers to the difference between the maximum and minimum values. Specifications subject to change without notice.

#### **PIN FUNCTION DESCRIPTIONS**

Pin	Name	Description	Pin	Name	Description	
1	PCLK	Parallel Clock Input	23	X8	Analog Input (or Output)	NC SIN SCLK
2	SCLK	Serial Clock Input	24	X9	Analog Input (or Output)	SCL NC NC SCL SCL NC
3	SIN	Serial Data Input	25	X10	Analog Input (or Output)	6 5 4 3 2
4	V <sub>SS</sub>	Negative Analog Power Supply	26	X11	Analog Input (or Output)	
5	NC	No Internal Connection	27	X12	Analog Input (or Output)	Y15 7
6	NC	No Internal Connection	28	X13	Analog Input (or Output)	Y14 8
7	Y15	Analog Output (or Input)	29	X14	Analog Output (or Input)	Y13 9
8	Y14	Analog Output (or Input)	30	X15	Analog Output (or Input)	Y12 10
9	Y13	Analog Output (or Input)	31	Y0	Analog Output (or Input)	Y11 11
10	Y12	Analog Output (or Input)	32	Y1	Analog Output (or Input)	
11	Y11	Analog Output (or Input)	33	Y2	Analog Output (or Input)	Y10 12 TOP
12	Y10	Analog Output (or Input)	34	Y3	Analog Output (or Input)	Y9 13 (Not to
13	Y9	Analog Output (or Input)	35	Y4	Analog Output (or Input)	Y8 14
14	Y8	Analog Output (or Input)	36	Y5	Analog Output (or Input)	X0 15
15	X0	Analog Input (or Output)	37	Y6	Analog Output (or Input)	X1 16
16	X1	Analog Input (or Output)	38	Y7	Analog Output (or Input)	X2 17
17	X2	Analog Input (or Output)	39	NC	No Internal Connection	l
18	X3	Analog Input (or Output)	40	NC	No Internal Connection	18 19 20 21 22
19	X4	Analog Input (or Output)	41	V <sub>DD</sub>	Positive Analog Power Supply	<u>5 7 8 8 7</u>
20	X5	Analog Input (or Output)	42	V <sub>CC</sub>	Digital Power Supply	~ ~ ~ ~ ~ ~
21	X6	Analog Input (or Output)	43	DGND	Digital Ground	NC = NO CONNECT
22	X7	Analog Input (or Output)	44	SOUT	Serial Data Output: Positive True	

#### **PIN CONFIGURATION**



### AD75019

### **TIMING CHARACTERISTICS**<sup>1</sup> ( $T_A = T_{MIN}$ to $T_{MAX}$ , rated power supplies unless otherwise noted)


Parameter	Symbol	Value	Units	Condition
Data Setup Time	t <sub>1</sub>	20	ns	min
SCLK Pulsewidth	t <sub>2</sub>	100	ns	min
Data Hold Time	t <sub>3</sub>	40	ns	min
SCLK Pulse Separation	$t_4$	100	ns	min
SCLK to PCLK Delay	t <sub>5</sub>	65	ns	min
SCLK to PCLK Delay and Release	$(t_5 + t_6)$	5	ms	max
PCLK Pulsewidth	t <sub>6</sub>	65	ns	min
Propagation Delay, PCLK to Switches On or Off	_	70	ns	max
Data Load Time	_	52	μs	SCLK = 5 MHz
SCLK Frequency	_	20	kHz	min
SCLK, PCLK Rise and Fall Times	_	1	μs	max

#### NOTES

<sup>1</sup>Timing measurement reference level is 1.5 V.

Specifications subject to change without notice.

#### TIMING DIAGRAM



#### **OPERATION TRUTH TABLE**

Control Lines				
PCLK	SCLK	SIN	SOUT	Operation/Comment
1	0	Х	Х	No operation.
1	1	Data <sub>i</sub>	Data <sub>i-256</sub>	The data on the SIN line is loaded into the serial register; data clocked into the serial register 256 clocks ago appears at the SOUT output.
0	Х	Х	Х	Data in the serial shift register transfers into the parallel latches which control the switch array.

#### APPLICATIONS INFORMATION

#### **Loading Data**

Data to control the switches is clocked serially into a 256-bit shift register and then transferred in parallel to 256 bits of memory. The rising edge of SCLK, the serial clock input, loads data into the shift register. The first bit loaded via SIN, the serial data input, controls the switch at the intersection of row Y15 and column X15. The next bits control the remaining columns (down to X0) of row Y15, and are followed by the bits for row Y14, and so on down to the data for the switch at the intersection of row Y0 and column X0. The shift register is dynamic, so there is a minimum clock rate, specified as 20 kHz.

After the shift register is filled with the new 256 bits of control data, PCLK is activated (pulsed low) to transfer the data to the parallel latches. Since the shift register is dynamic, there is a maximum time delay specified before the data is lost: PCLK must be activated and brought back high within 5 ms after filling the shift register. The switch control latches are static and will hold their data as long as power is applied.

To extend the number of switches in the array, you may cascade multiple AD75019s. The SOUT output is the end of the shift register, and may be directly connected to the SIN input of the next AD75019. REV. D

#### Power Supply Sequencing and Bypassing

All junction-isolated parts operating on multiple power supplies require proper attention to supply sequencing. Because BiMOS II is a junction-isolated process, parasitic diodes exist between  $V_{DD}$  and  $V_{CC}$ , and between  $V_{SS}$  and DGND. As a result,  $V_{DD}$  must always be greater than ( $V_{CC} - 0.5$  V), and  $V_{SS}$  must always be less than (DGND + 0.5 V).

If you can't ensure that system power supplies will sequence to meet these conditions, external Schottky (e.g., 1N5818) or silicon (e.g., 1N4001) diodes may be used. To protect the positive side, the anode would connect to  $V_{CC}$  (Pin 42) and the cathode to  $V_{DD}$  (Pin 41). For the negative side, connect the anode to  $V_{SS}$  (Pin 4) and the cathode to DGND (Pin 43).

Each of the three power supply pins [V<sub>DD</sub> (Pin 41), V<sub>CC</sub> (Pin 42) and V<sub>SS</sub> (Pin 4)] should be bypassed to DGND (Pin 43) through a 0.1  $\mu$ F ceramic capacitor located close to the package pins.

#### **Transistor Count**

AD75019 contains 5,472 transistors. This number may be used for calculating projected reliability.

### AD75019

#### ABSOLUTE MAXIMUM RATINGS\*

	Min	Max	Units	Conditions
V <sub>DD</sub> to DGND	-0.5	+25.2	V	
V <sub>SS</sub> to DGND	-25.2	+0.5	v	
V <sub>CC</sub> to DGND	-0.5	+7.0	v	
V <sub>DD</sub> to V <sub>SS</sub>	-0.5	+25.2	V	
V <sub>CC</sub> to V <sub>SS</sub>	-0.5	+25.2	V	
Digital Inputs to DGND	-0.3	$V_{CC} + 0.5$	V	
Power Dissipation		1.0	W	$T_A \le 75^{\circ}C$
Operating Temperature Range	0	+70	°C	
Storage Temperature	-65	+150	°C	
Lead Temperature		+300	°C	Soldering, 10 sec


\*Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### CAUTION \_\_\_\_

ESD (electrostatic discharge) sensitive device. The digital control inputs are Zener protected; however, permanent damage may occur on unconnected devices subject to high energy electrostatic fields. Unused devices must be stored in conductive foam or shunts. The protective foam should be discharged to the destination socket before devices are removed.



### **OUTLINE DIMENSIONS**



COMPLIANT TO JEDEC STANDARDS MO-047-AC CONTROLLING DIMENSIONS ARE IN INCHES; MILLIMETER DIMENSIONS (IN PARENTHESES) ARE ROUNDED-OFF INCH EQUIVALENTS FOR REFERENCE ONLY AND ARE NOT APPROPRIATE FOR USE IN DESIGN.

> Figure 1. 44-Lead Plastic Leaded Chip Carrier [PLCC] (P-44) Dimensions shown in inches and (millimeters)

#### **ORDERING GUIDE**

Model <sup>1</sup>	Temperature Range	Package Description	Package Option
AD75019JPZ	0°C to 70°C	44-Lead Plastic Leaded Chip Carrier [PLCC]	P-44
AD75019JPZ-REEL	0°C to 70°C	44-Lead Plastic Leaded Chip Carrier [PLCC]	P-44

<sup>1</sup> Z = RoHS Compliant Part.

#### **REVISION HISTORY**

10/2018—Rev. C to Rev. D
Changes to Temperature Range Parameter,
AD75019—Specifications Table2
Moved Outline Dimensions and Ordering Guide5
Updated Outline Dimensions5
Changes to Ordering Guide5

©2018 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. D16744-0-10/18(D)



Rev. D | Page 5 of 5

### **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Analog Devices Inc.: <u>AD75019JP</u> <u>AD75019JPZ</u> <u>AD75019JPZ-REEL</u>