



1261H.SR - Non sparking sledgehammers



Description:

- Special non sparking and anti-magnetic Copper-Beryllium alloy.
- For safety purposes, FACOM uses wooden handles to prevent any risk of sparks. This is not the case of certain bi-material plastic handles.
- To avoid any risk of sparks, the design of the hammer heads is specific, without sharp edges.



	Length L [mm]	Length L1 [mm]	Height H [mm]	Weight [g]
1261H.100SR	250.0	39.0	102.0	1300.0
1261H.150SR	250.0	42.5	122.0	1800.0
1261H.180SR	250.0	46.5	122.0	2100.0
1261H.200SR	250.0	48.0	130.0	2300.0
1261H.220SR	250.0	49.0	134.0	2500.0
1261H.250SR	258.0	50.0	146.0	3400.0
1261H.300SR	700.0	53.0	156.0	3900.0
1261H.400SR	800.0	59.0	168.0	4900.0
1261H.45SR	250.0	29.0	79.0	610.0
1261H.540SR	800.0	65.0	187.0	6300.0
1261H.640SR	800.0	69.0	197.0	7310.0
1261H.820SR	900.0	76.0	208.0	9100.0