

5 CONTACTS BLUE FEMALE HOUSING FOR WIRE INSULATION Ø1.30 TO Ø1.70

THIS IS A C.A.D. GENERATED DRAWING TOLERANCE UNLESS OTHERWISE SPECIFIED DO NOT MAKE MANUAL REVISIONS TO MASTER.

$\land \Box$	Ļ
X I D	l
	┝
	l
	l
	L

ISSUE NUMBER ORIGINAL (1)






.X ±0.38 .XX ±0.25 .XXX ±0.13



NOTE: **ELECTRICAL SPECIFICATIONS: VOLTAGE RATING:** 250V MAX. **CURRENT RATING:** 3A per CONTACT CONTACT RESISTANCE: $15m\Omega$ MAX. **INSULATOR RESISTANCE:** 1000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC(RMS) **OPERATING TEMPERATURE:** -40°C ~ 105°C

MATERIAL & FINISH: HOUSING: PBT, UL94V-0 CONTACTS: PHOSPHOR BRONZE, TIN PLATED SEALS: SILICONE RUBBER

	ACAD REFERENCE NO.: 560 Assembly						
		DRAWN: C.B	DATE: July 23, 2020				
		CHECKED:		DATE:			ļ
EDAC INC TORONTO, ONTARIO CANADA OUR CONNECTION TO QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 2:1		SHEET 1	OF	1	
		DRAWING NUMBER:	R: 560 Assembly			ISSUE	
		PART NUMBER:	560-005-0	00-411		1	





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

