



BT/Wi-Fi 2.4 GHz EMBEDDED CHIP ANTENNA

Part Numbers: 2108832-1


FEATURES & BENEFITS

- Wi-Fi 2.4 GHz, Bluetooth, ZigBee
- Embedded Ceramic Chip Antenna
- On Board SMD Antenna
- Available in tape & reel
- The following data is based on 50 x 50 mm ground size

SPECIFICATIONS

Frequency Range (MHz)	2400 - 2500			
VSWR	< 2.8:1			
Average Efficiency	82 %			
Peak Gain	1.8 dBi			
Average Gain	-1.9 dBi			
Feed Point Impedance	50 ohms			
Polarization	Linear			
Size	3.0 mm x 1.5 mm x 1.2 mm			
Weight	< 0.02 g			
Mounting	Surface mount			
Mating Connector	N/A			
Cable	N/A			
Operating Temperature	-40 to +85°C			
Storage Temperature	-40 to +85°C			
Hazardous Materials	A certificate of conformance is available from the product page on TE website.			


RF DATA








RADIATION PATTERN



MOUNTING GUIDE




- NOTES: 1. No copper allowed in designated area on all PCB layers
 - Measured with above matching circuit condition.
 For more information please call TE.


Dimension: mm Diagrams is not to scale

KEEP OUT AREA

DIMENSIONS




PACKAGING



Item	Spec.	Item	Spec.	Item	Spec.
A0	1.80 ±0.10	PO	4.00 ±0.10	E	1.75 ±0.10
B0	3.30 ±0.10	P1	4.00 ±0.10	F	5.50 ±0.10
K0	1.35 ±0.10	P2	2.00 ±0.10	W	12.00 ±0.30
D0	1.55 ±0.05			t	0.30 ±0.05


2,500pcs/1Reel Ø7" x 12 mm



7,500pcs/3 Reel 3 Reel/1 Inner box

365.00

37,500pcs/5 Inner box 5 Inner box/I Outer box #1



105,000pcs/14 Inner box 14 Inner box/I Outer box #2

TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 +52 (0) 55-1106-0800 Mexico: Latin/S. America: +54 (0) 11-4733-2200 +49 (0) 6251-133-1999 Germany: UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

For phone numbers in other countries, go to te.com/support-center

te.com

TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.

05/2021

