


PRODUCT SPECIFICATION

**Carl
Kammerling**
International

| | |
|-------------------------|-----------------|
| Brand | C.K |
| Product Range | Soldering Irons |
| Catalogue number | 950 |
| Date | 01/02/2016 |

| | |
|--|--|
| <p>Range Description Soldering Irons</p> <hr/> <p>Features</p> <ul style="list-style-type: none"> • Heavy duty construction – for professional use • GS & VDE approved – independently certified • Long life tip – suitable for use with lead free solder • Support stand included |  |
|--|--|

| Item Number | Item Description | EAN No | Commodity code | Carton Qty |
|-------------|---------------------------|---------------|----------------|------------|
| 495009 | 25w Soldering Iron UK | 5051074950093 | 85151100 | 1 |
| 495010 | 40w soldering Iron UK | 5051074950109 | 85151100 | 1 |
| 495011 | 25w Soldering Iron Euro | 5051074950116 | 85151100 | 1 |
| 495012 | 40w Soldering Iron Euro | 5051074950123 | 85151100 | 1 |
| 495013 | Spare tip 25w (Pack of 2) | 5051074950130 | 85151100 | 1 |
| 495014 | Spare tip 40w (Pack of 2) | 5051074950147 | 85151100 | 1 |

| <p>Technical product information</p> | <p>Materials Handle – Injection moulded thermo-setting polyurethane Heating element – Heater wire (chrome nickel steel) Shaft – Stainless steel Tip – Copper with nickel Iron plating</p> <p>25w Soldering Iron 25w output Voltage 220 – 240v AC Current 0.1 amp Fuse rating 3 amp Tip width 2.7mm</p> <p>40w Soldering Iron 40w output Voltage 220 – 240v AC Current 0.17 amp Fuse rating 3 amp Tip width 3.5mm</p> <table border="1" data-bbox="354 877 1620 1108"> <thead> <tr> <th>Item</th> <th>Output power</th> <th>min.operating temp °C</th> <th>max.operating temp °C</th> </tr> </thead> <tbody> <tr> <td>495009</td> <td>25W</td> <td>22~30W</td> <td>350</td> <td>430</td> </tr> <tr> <td>495010</td> <td>40W</td> <td>36~44W</td> <td>450</td> <td>530</td> </tr> <tr> <td>495011</td> <td>25W</td> <td>22~30W</td> <td>350</td> <td>430</td> </tr> <tr> <td>495012</td> <td>40W</td> <td>36~44W</td> <td>450</td> <td>530</td> </tr> </tbody> </table> | Item | Output power | min.operating temp °C | max.operating temp °C | 495009 | 25W | 22~30W | 350 | 430 | 495010 | 40W | 36~44W | 450 | 530 | 495011 | 25W | 22~30W | 350 | 430 | 495012 | 40W | 36~44W | 450 | 530 |
|---|--|-----------------------|-----------------------|-----------------------|-----------------------|--------|-----|--------|-----|-----|--------|-----|--------|-----|-----|--------|-----|--------|-----|-----|--------|-----|--------|-----|-----|
| Item | Output power | min.operating temp °C | max.operating temp °C | | | | | | | | | | | | | | | | | | | | | | |
| 495009 | 25W | 22~30W | 350 | 430 | | | | | | | | | | | | | | | | | | | | | |
| 495010 | 40W | 36~44W | 450 | 530 | | | | | | | | | | | | | | | | | | | | | |
| 495011 | 25W | 22~30W | 350 | 430 | | | | | | | | | | | | | | | | | | | | | |
| 495012 | 40W | 36~44W | 450 | 530 | | | | | | | | | | | | | | | | | | | | | |
| <p>Standards compliance</p> | <p>VDE approved product</p> | | | | | | | | | | | | | | | | | | | | | | | | |
| <p>User health and safety information</p> | <p>Users are directed to carefully read and observe the operating instructions</p> | | | | | | | | | | | | | | | | | | | | | | | | |
| <p>RoHS/WEEE compliance</p> | <p>RoHS – these products are implicated within the scope of the legislation, Carl Kammerling International hold evidence of compliance, available on request</p> <p>Carl Kammerling International is a registered producer of RoHS compliant products</p> <p>WEEE - markings on C.K soldering Irons are compliant with WEEE directives</p> | | | | | | | | | | | | | | | | | | | | | | | | |
| <p>Material safety data</p> | <p>None applicable</p> | | | | | | | | | | | | | | | | | | | | | | | | |
| <p>Warranty</p> | <p>C.K soldering irons are guaranteed for life against imperfect materials or workmanship</p> | | | | | | | | | | | | | | | | | | | | | | | | |
| <p>Country of origin</p> | <p>Germany</p> | | | | | | | | | | | | | | | | | | | | | | | | |

Dimensional details

| Item | Product only | | | | Product on primary packaging | | | |
|--------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|----------------|
| | Width mm | Depth mm | Height mm | Net weight g | Width mm | Depth mm | Height mm | Gross weight g |
| 495009 | 45 | 45 | 1600 | 193 | 70 | 40 | 350 | 270 |
| 495010 | 45 | 45 | 1600 | 193 | 70 | 40 | 350 | 270 |
| 495011 | 45 | 45 | 1600 | 193 | 70 | 40 | 350 | 270 |
| 495012 | 45 | 45 | 1600 | 193 | 70 | 40 | 350 | 270 |
| 495013 | 4 | 4 | 65 | 5 | 80 | 6 | 145 | 22 |
| 495014 | 5 | 5 | 75 | 10 | 80 | 6 | 145 | 32 |

| Item | Shelf box (secondary packaging) | | | | Euro Pallet data Wi x Hi | |
|--------|---------------------------------|----------|-----------|----------------|-----------------------------|---------------------|
| | Width mm | Depth mm | Height mm | Gross weight g | No of cartons on base | Number of rows high |
| 495009 | | | | | | |
| 495010 | | | | | | |
| 495011 | | | | | | |
| 495012 | | | | | | |
| 495013 | | | | | | |
| 495014 | | | | | | |

Packaging waste details

| Item | Primary Packaging | | | | Secondary packaging | | | |
|--------|-------------------|---------|--------|--------------|---------------------|-----|--------|-----|
| | Plastic g | Use | Card g | Use | Plastic g | Use | Card g | Use |
| 495009 | | | 77 | Box | | | | |
| 495010 | | | 77 | Box | | | | |
| 495011 | | | 77 | Box | | | | |
| 495012 | | | 77 | Box | | | | |
| 495013 | 2 | Blister | 10 | Backing card | | | | |
| 495014 | 2 | Blister | 10 | Backing card | | | | |