

Switch Mode Power Supplies Single Output AC/DC Power Supply

AWSP60-24

Description:

The AWSP60-24 is a single output power supply. This power supply is designed for a wide variety applications where high reliability is desired, including applications for the industrial and telecommunications markets. Excellent performance specifications are provided, together with compliance to European EMC (EN55022, Class B and EN61000-3-2), and Low Voltage directive (TUV EN60950).

Specifications (@25C)

Input Characteristics:

Input Voltage: Input Frequency Range: Max Input Current: Max Inrush Current: Leakage Current: 85-264Vac 47-63Hz 1.3A @ Vin (rated) 20A@110Vac, 40A@220Vac at cold start <3.5mA/240Vac

24Vdc

2.5A

60W

±10%

100mV

±0.5%

±0.5%

45kHz

2 years

160x98x38mm

450g net, 490g gross

Natural Convection

<0.03%/°C (10-50°C)

300ms max @ 230VAc

20ms min, 100% Load@230Vac

300ms max, 100% Load@230Vac

At Load>120% 115/230Vac, Shutdown

Zener clamping at Vo>110%, Non auto recovery

Short circuit protection available. Avoid short circuit >30 sec.

81%

Output Characteristics:

Output Voltage: Output Current: Output Power: Adjustable Output Range: Ripple & Noise: Load Regulation: Line Regulation: Efficiency: Temperature Drift: Start-up Time: Hold-up Time: Rise-up Time: Over Current Protection: Over Voltage Protection: Short Circuit Protection:

General Specifications:

Switching Frequency: Dimension (LxWxH): Weight: Cooling: Isolation Resistance: Dielectric Strength: Warranty:

Environmental Specifications:

Operating Temperature: Operating Humidity: Storage Temperature: Storage Humidity: Vibration: -10° to 60°C 20 to 90% RH, non-condensing -25 to 75°C 10 to 95% RH, non-condensing 10-55Hz, 2G 1min/cycle, period of 60min, each X, Y & Z axis

//P—O/P, //P—FG, O/P—FG: 500VDC/100Mohms //P—O/P: 4.3KVdc; I/P—FG: 2.5KVac; O/P—FG: 0.5KVac

EMC & Safety Specifications:

EMC Emissions:


ESD Susceptibility: Radiated Susceptibility: Fast Burst: Surge: Safety Approval:




Web: www.TriadMagnetics.com Phone 951-277-0757 Fax 951-277-2757


Conforms to EN55022,VCCI,CISPR22 Class B (Conducted & Radiated); IEC-61000-4-2, 61000-4-4, 61000-4-5, 61000-4-11 EN61000-4-2 (15kV/8kV) EN61000-4-3 (3Vm¹) EN61000-4-3 (3Vm¹) EN61000-4-4 (2kV) EN61000-4-5 (1kV/2kV) UL 60950 (UL File No: E204980) TUV EN60950 (TUV No: 50058679)

460 Harley Knox Blvd. Perris, California 92571










Mounting B




Publish Date: April 15, 2019




Switch Mode Power Supplies Single Output AC/DC Power Supply

Outline Dimensions (mm):



Derating Curve:



Connector Types:

Input: Screw Terminals Output: Screw Terminals

RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.

| Web: www.TriadMagnetics.com | | |
|-----------------------------|--------------------------|-------------------------------|
| Phone 951-277-0757 | 460 Harley Knox Blvd. | Publish Date: April 15, 2019 |
| Fax 951-277-2757 | Perris, California 92571 | 1 ublish Date. April 13, 2019 |