

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347290120

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Receptacle Housing, 12 Circuits, Dual Row, Polarization A, Black, Tray



Documents:	
3D Model (PDF)	Application Specification AS-34729-020-001 (PDF)
3D Model	Packaging Specification PK-31301-201-001 (PDF)
Drawing (PDF)	Brochure (PDF)
Product Specification PS-34729-020-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 347290200-AS-CH-000 (PDF)	

General	
Product Family	Crimp Housings
Series	34729
Application	Automotive, Signal, Wire-to-Board
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Polarization	A
Product Name	Stac64
UPC	884982006614
Physical	
Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Net Weight	5.300/g
Number of Rows	2
Packaging Type	Tray
Panel Mount	N/A
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	10.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	347290200-AS-CH-000, AS-34729-020-001
Packaging Specification	PK-31301-201-001
Product Specification	PS-34729-020-001
Sales Drawing	SD-34729-020

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image
ELV
Compliant

Not Contained

Search Parts in this Series
34729 Series

Mates With
34690 2.54mm Pitch Stac64 Vertical Header, 34691 2.54mm Pitch Stac64 Right Angle Header

Use With
34803 CTX64 Female Terminal

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34729-0120](#)