


[Request Samples](#)
[Check Inventory](#)


FEATURES

- AEC-Q200 Qualified
- Shielded construction
- Soft saturation
- Low DCR per cubic mm
- Designed for switching frequencies between 100KHz-5MHz



ELECTRICAL SPECIFICATIONS @ 25°C

PART NUMBER*	INDUCTANCE (uH)	TOLERANCE (%)	IRMS (A)	ISAT (A)	DC RESISTANCE (mΩ)		TYPE
					TYP	MAX	
AMDLA4020Q-R12MT	0.12	20	12	17	4.2	5.0	Lead Frame
AMDLA4020Q-R22MT	0.22	20	11	15	7.0	8.0	Lead Frame
AMDLA4020Q-R33MT	0.33	20	9.0	13	7.79	9.5	Lead Frame
AMDLA4020Q-R47MT	0.47	20	8.5	8.0	9.2	14.0	Lead Frame
AMDLA4020Q-R68MT	0.68	20	7.0	7.5	11.2	13.5	Lead Frame
AMDLA4020Q-1R0MT	1	20	5.5	7.0	17.0	21.0	Lead Frame
AMDLA4020Q-1R5MT	1.5	20	4.0	5.4	22.0	26.0	Lead Frame
AMDLA4020Q-2R2MT	2.2	20	4.2	4.2	31.5	38.0	Lead Frame
AMDLA4020Q-3R3MT	3.3	20	3.0	3.5	47.5	55.0	Lead Frame
AMDLA4020Q-4R7MT	4.7	20	2.2	3.2	56.7	70.0	Lead Frame
AMDLA4020Q-6R8MT	6.8	20	2.4	2.6	114.0	138.0	Lead Frame
AMDLA4020Q-100MT	10	20	1.8	2.1	170.0	190.0	Lead Frame
AMDLA4020Q-150MT	15	20	1.2	1.6	220.0	275.0	Lead Frame
AMDLA4020Q-220MT	22	20	0.9	1.4	277.0	460.0	Lead Frame

* Please refer to Part Builder section

Test Conditions

Inductance: 1 MHz, 1 V, 0 Adc

Humidity Range: 65% RH

Temperature Rise Current: Current measured at Δ T of 40°C

Saturation Current: Current measured at Δ L of 30%

GENERAL SPECIFICATIONS

Operating Temperature:

-55°C to +125°C with (40°C rise) Irms current.

Maximum Part Temperature: +125°C

Components Storage Temperature:

-55°C to +125°C

Tape and Reel Packaging

Temperature: -20°C to +65°C

MSL: Level 1

MATERIALS

Core: Metal Alloy

Wire: Copper

Terminal: Tin Plating

Ink: Black

PART BUILDER




1. Tolerance: M = 20%

2. Packaging: B = Bulk


T = Tape and Reel (3,000pcs/reel)

*Refer to Electrical Specification table


PRODUCT DIMENSIONS



RECOMMENDED LANDING PATTERN




RECOMMENDED REFLOW PROFILE




ZONE	DESCRIPTION	TEMPERATURE	TIMES
1	Preheat	$T_{smin} \sim T_{smax}$ 150°C ~ 180°C	60 ~ 120 sec.
2	Reflow	T_L 230°C	30 ~ 40 sec.
3	Peak Heat	T_p 250°C+0/-5°C	10 sec. MAX

PACKAGING

Tape and Reel: 3,000 pcs



TYPE	A	B	C	D
13" x 12 mm	12.4 +2/-0	100.0 ± 0.5	13.0 +0.5/-0.2	330.0



B ₀	A ₀	K ₀	P	W	F	T	D
4.85 ± 0.1	4.45 ± 0.1	2.3 ± 0.1	8.0 ± 0.1	12.0 ± 0.3	5.5 ± 0.1	0.3 ± 0.05	1.5

Dimensions: mm

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[AMDLA4020Q-100MT](#) [AMDLA4020Q-1R0MT](#) [AMDLA4020Q-1R5MT](#) [AMDLA4020Q-2R2MT](#) [AMDLA4020Q-3R3MT](#)
[AMDLA4020Q-4R7MT](#) [AMDLA4020Q-6R8MT](#) [AMDLA4020Q-R47MT](#) [AMDLA4020Q-R68MT](#) [AMDLA4020Q-150MT](#)
[AMDLA4020Q-220MT](#) [AMDLA4020Q-R12MT](#) [AMDLA4020Q-R22MT](#) [AMDLA4020Q-R33MT](#)