




### Three level sensor terminal blocks without ground connection

Compression clamp


 DIN 3

End stop th. 9,1 mm **BAMH** 0114 836.00  
 Other end stops : See Accessories section  
 Rail  35 x 7,5 x 1 **PR30** prepunched 0173 220.05  
 Rail  35 x 15 x 2,3 **PR4** 0168 500.12  
 Rail  35 x 15 x 1,5 **PR5** prepunched 0101 598.26  
 Other rails : See Accessories section  
 Other accessories : See Accessories section


#### Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.

#### Accessories




1 End section	grey
2 Assembled jumper bar	22 A
2 Assembled jumper bar (without IP20 protection)	22 A
3 Connector plate	22 A
4 IDC jumper	24 A

 R See section on markers marking method

#### D 2,5/6.DA


Spacing 6 mm + 0,05 (.238")




Three level block for power


#### D 2,5/6.DAL

Spacing 6 mm + 0,05 (.238")



Three level sensor block with LED indicator between upper and middle level (red 24V=)

Color	Type	Part numbers
Grey	 <b>D 2,5/6.DA</b>	<b>0115 541.11</b>

Color	Type	Part numbers
Grey	 <b>D 2,5/6.DAL</b>	<b>0115 535.03</b>

#### Characteristics

Wire size

	NFC DIN	UL	CSA
Compression Solid wire	0,2-2,5 mm <sup>2</sup>	20-12 AWG	22-14 AWG
clamp Stranded wire	0,22-2,5 mm <sup>2</sup>	20-12 AWG	22-14 AWG

Voltage	380 V Gr.C	300 V	300 V
Rated			
Pulse			
Pollution degree			
Current	22 A	20 A	20 A
Rated			
Wire size	2,5 mm <sup>2</sup>	12 AWG	14 AWG
Rated / Gauge			
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
6 mm	3,5 mm	0,4-0,6 Nm	IP20
.24"	.138"	3.5-5.3 lb.in	NEMA 1

#### Characteristics



Wire size

	NFC DIN	UL	CSA
Compression Solid wire	0,2-2,5 mm <sup>2</sup>	20-12 AWG	22-14 AWG
clamp Stranded wire	0,22-2,5 mm <sup>2</sup>	20-12 AWG	22-14 AWG

Voltage	380 V Gr.C	300 V (1)	300 V (1)
Rated			
Pulse			
Pollution degree			
Current	22 A	20 A	20 A
Rated			
Wire size	2,5 mm <sup>2</sup>	12 AWG	14 AWG
Rated / Gauge			
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
6 mm	3,5 mm	0,4-0,6 Nm	IP20
.24"	.138"	3.5-5.3 lb.in	NEMA 1

Type	Part numbers
<b>FED3E</b> th. 3,0 mm	<b>0116 771.20</b>
<b>BJD6</b> 2 poles	<b>0178 024.25</b>
<b>BJD6</b> 3 poles	<b>0178 025.26</b>
<b>BJD6</b> 4 poles	<b>0178 026.27</b>
<b>BJD6</b> 5 poles	<b>0178 027.20</b>
<b>BJD6</b> 10 poles	<b>0178 032.25</b>
<b>BJD6</b> 20 poles	<b>0178 033.26</b>
<b>EL61</b>	<b>0177 812.17</b>
<b>AD2,5</b>	<b>0114 205.20</b>

Type	Part numbers
<b>FED3E</b> th. 3,0 mm	<b>0116 771.20</b>
<b>BJD6</b> 2 poles	<b>0178 024.25</b>
<b>BJD6</b> 3 poles	<b>0178 025.26</b>
<b>BJD6</b> 4 poles	<b>0178 026.27</b>
<b>BJD6</b> 5 poles	<b>0178 027.20</b>
<b>BJD6</b> 10 poles	<b>0178 032.25</b>
<b>BJD6</b> 20 poles	<b>0178 033.26</b>
<b>EL61</b>	<b>0177 812.17</b>
<b>AD2,5</b>	<b>0114 205.20</b>



⑤ <b>RC65</b> red - blank	<b>0103 776.01</b>
<b>RC65</b> blue - blank	<b>0103 775.00</b>

⑤ <b>RC65</b> red - blank	<b>0103 776.01</b>
<b>RC65</b> blue - blank	<b>0103 775.00</b>

Note : (1) 24 V DC on LED circuit.