


Metal Oxide Film Resistors Axial Connections



High safety standard, high purity ceramic core

Excellent non-flame coating

Stable performance in diverse environment, meet EIAJ-RC2655A requirements

Too low or too high ohmic value can be supplied on a case to case basis

Solderability: 95%

Temperature Cycling: $\pm(2.0\% + 0.05\Omega)$ Max, with no evidence of mechanical damage

Original package: 5000 pcs

PT 52 mm

SPECIFICATION:

Tolerance	$\pm 5\%$
Temperature coefficient	350 ppm/ $^{\circ}\text{C}$
Max. over load voltage	400 V
Housing type	Axial
Resistance range	0.3 Ω -50K Ω
Max. working voltage	250 V

PRODUCT RANGE:

Art. Nr.	Resistance	Rated output	Diameter	Length
RND 155MOR0W2J0101A10	100 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0102A10	1 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J010JA10	1 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0153A10	15 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0182A10	1.8 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0221A10	220 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0224A10	220 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J022JA10	2.2 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0333A10	33 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0334A10	330 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J043JA10	4.3 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0473A10	47 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J047JA10	4.7 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J047KA10	0.47 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0503A10	50 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J050KA10	0.5 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0513A10	51 k Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J062KA10	0.62 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0680A10	68 Ω	0.5 W	3.5 mm	10 mm
RND 155MOR0W2J0682A10	6.8 k Ω	0.5 W	3.5 mm	10 mm

PRODUCT RANGE:

Art. Nr.	Resistance	Rated output	Diameter	Length
RND 155MOROW4J0101A50	100 Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0102A50	1 k Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0103A50	10 k Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0105A50	1 M Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0202A50	2 k Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0332A50	3.3 k Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0391A50	390 Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0470A50	47 Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0471A50	470 Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0472A50	4.7 k Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0473A50	47 k Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0474A50	470 k Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0560A50	56 Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0561A50	560 Ω	0.25 W	2.5 mm	7.5 mm
RND 155MOROW4J0821A50	820 Ω	0.25 W	2.5 mm	7.5 mm