Wirewound Resistors

Fusible & Flame-Proof Type


Normal & Miniature Style [FKN Series]

FEATURES

Power Rating	1/2W, 1W, 2W, 3W, 4W, 5W, 7W
Resistance Tolerance	±1%, ±5%
T.C.R.	±350ppm/°C
Flameproof Multi-layer Coating Meets	UL-94V-0
Flameproof Feature Meets Overload Test	UL-1412

DERATING CURVE

For resistors operated in ambient temperatures above 40°C, power rating must be derated in accordance with the curve below.



Ambient Temperature (°C)

Unit: mm

FUSING CHARACTERISTICS

 $R{\leq}2.0\Omega~$ Fusing time within 60 seconds at 36 times of rated power

R>2.0 Ω Fusing time within 60 seconds at 25 times of rated power

Fusing residual resistive value at least 100 times rated resistance

	STYLE	DIMENSION				
	Normal	Miniature	L	øD	Н	ød
	-	FKN50S/FKN1SS	6.3±0.5	2.5±0.3	28±2.0	0.55±0.05
d	FKN-50	FKN I WS/FKN2SS	9.0±0.5	3.5±0.3	26±2.0	0.55±0.05
	FKN100	FKN2WS	.5± .0	4.6±0.5	35±2.0	0.8±0.05
	FKN200	FKN3WS	15.5±1.0	5.2±0.5	33±2.0	0.8±0.05
	FKN300			(2) 05		
	FKN400	— FKN5WS	17.5±1.0	6.2±0.5	32±2.0	0.8±0.05
	FKN500	FKN7WS	24.5±1.0	8.2±0.5	38±2.0	0.8±0.05

INTRODUCTION

The resistor element is a resistive wire which is wound in a single layer on a ceramic rod, with tinned connecting wires of electrolytic copper welded to the end-caps. The ends of the resistive wire are connected to the caps by welding. The resistors are coated with layers of green color flame-proof lacquer. Overload protection without risk of fire. Wide range of overload currents.

5th color code: white



ELECTRICAL CHARACTERISTICS

NORMAL STYLE

STYLE	FKN-50	FKN100	FKN200	FKN300	FKN400	FKN500
Power Rating at 40°C				3W	4W	5W
Power Rating at 70°C	1/2W	IW	2₩			
Maximum working voltage	√P×R					
Voltage Proof on Insulation	300V					
Resistance Range (±1%)		0.5Ω - 100Ω	0.47Ω - 150Ω	0.56Ω - 330Ω		ΙΩ - 620Ω
Resistance Range (±5%)	0.5Ω - 47Ω	0.5Ω - 100Ω	0.47Ω - 150Ω	0.56Ω - 330Ω		ΙΩ - 620Ω
Operating Temp. Range	-40°C to +155°	с				
Temperature Coefficient	±350ppm/°C					

Note: Special value is available on request

MINIATURE STYLE

STYLE	FKN50S	FKNIWS/FKNISS	FKN2WS/FKN2SS	FKN3WS	FKN5WS	FKN7WS
Power Rating at 40°C					5₩	7W
Power Rating at 70°C	1/2W	IW	2W	3W		
Maximum working voltage	√P×R					
Voltage Proof on Insulation	200V	300V				
Resistance Range (±1%)		0.47Ω - 100Ω	0.47Ω - 150Ω	0.47Ω - 240Ω	0.56Ω - 330Ω	ΙΩ - 620Ω
Resistance Range (±5%)	2.5Ω - 22Ω	0.47Ω - Ι00Ω	0.47Ω - 150Ω	0.47Ω - 240Ω	0.56Ω - 330Ω	IΩ - 620Ω
Operating Temp. Range	-40°C to +155°C					
Temperature Coefficient	±350ppm/°C					

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	10 times rated power for 5 Sec.	±2.0%+0.05Ω
Voltage Proof on Insulation	IEC 60115-14.7	In V-Block for 60 sec., test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -40°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.	>100MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min, with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±5.0%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV (or Umax., Whichever less) for 1,000 Hr. (1.5Hr.on, 0.5Hr. Off)	±5.0%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇔ Room Temp. ⇔ +155°C ⇔ Room Temp. (5 cycles)	±1.0%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±1.0%+0.05Ω
Accidental Overload Test	IEC 60115-1 4.26	4 times RCWV for 1 Min.	No evidence of flaming or arcing

Note: Rated Continuous Working Voltage (RCWV) = $\sqrt{Power Rating \times Resistance Value}$ or Max. working voltage listed above, whichever less.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

FKN1WSJR-52-8R2 FKN1WSJR-52-10R FKN2WSJR-73-2R2 FKN2WSJT-73-100R FKN200JR-73-8R2 FKN2WSJT-73-22R FKN50SJR-52-1R FKN200JR-73-0R1 FKN2WSJR-73-0R5 FKN50SJR-52-10R FKN3WSJT-73-10R FKN3WSJT-73-22R FKN3WSJT-73-47R FKN2WSJT-73-0R5 FKN1WSJT-52-10R FKN3WSJT-73-100R FKN1WSJR-52-4R7 FKN2WSJR-73-100R FKN1WSJR-52-39R FKN1WSJR-52-3R9 FKN50SJR-52-2R2 FKN-50JR-52-33R FKN100JR-73-10R FKN50SJR-52-22R FKN5WSJR-73-56R FKN100JR-73-33R FKN1WSJR-52-15R FKN2WSJR-73-10R FKN1WSJT-52-39R FKN-50JR-52-39R FKN-50JR-52-1R5 FKN3WSJR-73-9R1 FKN3WSJR-73-100R FKN2WSJT-52-22R FKN3WSJR-73-47R FKN100JR-73-100R FKN-50JR-52-10R FKN-50JR-52-9R1 FKN2WSJR-73-9R1 FKN3WSJT-73-20R FKN3WSJR-73-1R5 FKN3WSJR-73-10R FKN5WSJR-73-3R3 FKN100JR-73-39R FKN50SJR-52-4R7 FKN5WSJR-73-10R FKN50SJR-52-5R6 FKN100JR-73-1R2 FKN100JR-73-18R FKN5WSJR-73-33R FKN100JR-73-47R FKN50SJR-52-9R1 FKN2WSJR-73-56R FKN-50JR-52-27R FKN50SJR-52-1R5 FKN2WSJT-52-33R FKN3WSJR-73-4R7 FKN1WSJT-52-22R FKN2WSJT-73-10R FKN5WSJR-73-27R FKN2WSJT-73-82R FKN3WSJT-73-91R FKN2WSJT-73-15R FKN3WSJR-73-15R FKN2WSJT-73-2R FKN3WSJR-73-33R FKN2WSJT-52-47R FKN2WSJT-73-43R FKN1WSJB-52-20R FKN1WSJB-52-2R2 FKN2WSJR-73-7R5 FKN1WSJB-52-5R1 FKN2WSJT-73-18R FKN3WSJT-73-1R FKN2WSJT-73-1R5 FKN2WSJT-73-33R FKN2WSJT-73-30R FKN5WSJR-73-100R FKN1WSJB-52-10R FKN2WSJT-73-12R FKN2WSJT-52-51R FKN2WSJT-73-4R7 FKN2WSJT-73-20R FKN2WSJT-73-47R FKN3WSJT-73-4R7 FKN2WSJR-73-8R2 FKN1WSJB-52-1R FKN5WSJR-73-68R FKN1WSJT-52-33R FKN2WSJT-52-68R FKN3WSJT-73-33R FKN2WSJT-73-68R FKN1WSJT-52-15R FKN1WSJB-52-15R FKN3WSJR-73-68R FKN1WSJR-52-47R FKN2WSJT-52-39R FKN1WSJT-52-30R FKN2WSJT-52-15R FKN1WSJT-52-47R