



6958 - STUD BRANCH TEE POLYMER MALE BSPP SS 316L EPDM SEA



maximum working pressure	16 bar 2 MPa 232 psi
working temperature	-10 to 95 °C 14 to 203 °F 263 to 368 °K
vacuum capability	755 mm Hg
body	BIO-BASED POLYMER
sub-base	STAINLESS STEEL 316L
'O'-rings	EPDM
gripping ring	STAINLESS STEEL

Part Nb	ØD (MM)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	L_2 (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
6958 04 10	4	G1/8	5	13	8.5	22	14	.009
6958 04 13	4	G1/4	5.5	16	8.5	22	14	.014
6958 06 10	6	G1/8	5	13	10.5	28.5	16	.011
6958 06 13	6	G1/4	5.5	16	10.5	28.5	16	.016
6958 08 10	8	G1/8	4.5	13	13.5	38	23	.019
6958 08 17	8	G3/8	5.5	21	13.5	36	23	.03
6958 10 13	10	G1/4	5.5	16	16	43	26.5	.032
6958 10 17	10	G3/8	5.5	21	16	43	26.5	.055
6958 10 21	10	G1/2	7.5	24	16	43	26.5	.051
6958 12 17	12	G3/8	5.5	21	19	45.5	31	.042
6958 12 21	12	G1/2	7	24	19	45.5	31	.049