



Fuse-link, high speed, 80 A, AC 690 V, DC 500 V, BS88, 19 x 77 mm, aR, BS, low let through

Catalog No. 80FE

Similar to illustration

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	80
Rated voltage			AC 690 V DC 500 V
Construction size			BS88
Size			19 x 77 mm
Utilization category			aR
Breaking Capacity		kA	200
usable for size/applications			protection of DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4 IEC 60269-4
Optional accessories			fuse-holder BH-0111

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (eci@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	80
Rated voltage		V	690
Voltage type			AC/DC
Rated switching capacity		kA	200
Utilization category			aR (accompanied semiconductor protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

### Assets (links)

**Declaration of CE Conformity**

00003218

### Additional product information (links)

High-speed full-line catalogue (pdf)	<a href="http://www1.cooperbusmann.com/pdf/dc416ece-4392-4b42-ab36-39df6058b353.pdf">http://www1.cooperbusmann.com/pdf/dc416ece-4392-4b42-ab36-39df6058b353.pdf</a>
--------------------------------------	---