
Vishay High Power Products

# Single Phase Rectifier Bridge, 8 A



PRODUCT SUMMARY		
I <sub>O(av)</sub>	8.0 A	
V <sub>RRM</sub>	50 to 1000 V	

## FEATURES

- Suitable for printed circuit board or chasis mounting
- Compact construction
- High surge current capability
- · Fully characterised data
- Wide temperature range
- RoHS compliant

## DESCRIPTION

The KBPC series of single phase rectifier bridge consists of four silicon junctions connected as a full bridge. These device are intended for general use in industrial and consumer equipment.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	VALUES	UNITS		
IO	$T_{C} = 50 \ ^{\circ}C$ , resistive load	8	A		
	$T_{C} = 50 \ ^{\circ}C$ , capacitive load	6.4			
I <sub>FSM</sub>	50 Hz	125	A		
	60 Hz	137			
l <sup>2</sup> t	50 Hz	110	A <sup>2</sup> s		
	60 Hz	100	A-S		
V <sub>RRM</sub>	Range	50 to 1000	V		
TJ		- 55 to 150	°C		

## **ELECTRICAL SPECIFICATIONS**

#### **VOLTAGE RATINGS V<sub>RRM</sub>, MAXIMUM REPETITIVE V<sub>RSM</sub>, MAXIMUM NON-REPETITIVE** PEAK REVERSE VOLTAGE PART NUMBER PEAK REVERSE VOLTAGE ۷ ۷ **KBPC8005** 50 80 KBPC801 100 150 KBPC802 200 300 KBPC804 400 500 KBPC806 600 700 KBPC808 800 900 KBPC810 1000 1100

For technical questions, contact: ind-modules@vishay.com






## **KBPC8** Series

Vishay High Power Products

## Single Phase Rectifier Bridge, 8 A



THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER	SYMBOL	VALUES	UNITS		
Operating and storage temperature range	T <sub>J</sub> , T <sub>Stg</sub>	- 55 to 150	°C		
Thermal resistance, junction to case	R <sub>thJC</sub>	6	K/W		
Approximate weight		6	g		
		0.21	0Z.		




Fig. 1 - Current Ratings




Fig. 2 - Non-Repetitive Surge Ratings

LINKS TO RELATED DOCUMENTS		
Dimensions	http://www.vishay.com/doc?95250	
	·	







**Vishay Semiconductors** 

**D-72** 

### DIMENSIONS in millimeters (inches): KBPC6, KBPC8



#### DIMENSIONS in millimeters (inches): KBPC1





Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.