


Slide DIP Switches with a height of 2.3mm and Half-pitch.

- Gold-plated twin contacts ensures high reliability.
- Washable, with seal tape available.
- Embossed taping available for small reel 100 pcs/ 500 pcs.



■ List of Models

Type	Flat actuator							
	With seal tape							
	Tube packaging	Embossed taping						
		Standard reel			Small reel			
No. of poles	Quantity per tube		Quantity per reel		Quantity per reel		Quantity per reel	
2	125	A6HF-2102	2,000	A6HF-2102-P	500	A6HF-2102-PM	100	A6HF-2102-R100
4	70	A6HF-4102		A6HF-4102-P		A6HF-4102-PM		A6HF-4102-R100
6	50	A6HF-6102		A6HF-6102-P		A6HF-6102-PM		A6HF-6102-R100
8	40	A6HF-8102		A6HF-8102-P		A6HF-8102-PM		A6HF-8102-R100
10	30	A6HF-0102		A6HF-0102-P		A6HF-0102-PM		A6HF-0102-R100

Note: Order in multiples of the package quantity.


■ Ratings/Characteristics

Rating (resistive load)		25 mA at 24 VDC 10 μ A (minimum current) at 3.5 VDC
Ambient operating temperature		-30 to +85 °C at 60% max. (with no icing or condensation)
Ambient operating humidity		35% to 95% (at +5 to +35 °C)
Insulation resistance		100 M Ω min. (at 100 VDC with insulation tester)
Contact resistance (initial value)		200 m Ω max.
Dielectric strength	Between terminals	300 VAC for 1 min
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude
Shock resistance	Malfunction	490 m/s ² min.
Durability	Electrical	1,000 operations min.
Washing		Possible
Degree of protection		IEC IP40
Operating force		0.29 to 4.9 N {30 to 500 gf}
Weight		0.08g (2 poles) 0.13g (4 poles) 0.19g (6 poles) 0.25 g (8 poles) 0.3g (10 poles)



■ Dimensions (Unit: mm)

● Flat Actuator With Seal Tape

- A6HF-□102
- A6HF-□102-P
- A6HF-□102-PM
- A6HF-□102-R100



Dimensions of PCB pad (Reference)
(Top View)




No. of poles	Models	A
2	A6HF-2102	3.67
4	A6HF-4102	6.21
6	A6HF-6102	8.75
8	A6HF-8102	11.29
10	A6HF-0102	13.83

Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

■ Internal Connections

Contact Form (Top View)



■ Precautions

Be sure to read the Safety precautions common to all DIP Switches for correct use.

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact

- Americas**
<https://components.omron.com/us>
- Asia-Pacific**
<https://components.omron.com/ap>
- Korea**
<https://components.omron.com/kr>

- Europe**
<https://components.omron.com/eu>
- China**
<https://components.omron.com.cn>
- Japan**
<https://components.omron.com/jp>

© OMRON Corporation 2007-2022 All Rights Reserved.
In the interest of product improvement, specifications are subject to change without notice.

Cat. No. A192-E1-07
1122 (0207)