

SIMATIC S7-1200, ANALOG OUTPUT, SM 1232, 4 AO, +/-10V, 14 BIT RESOLUTION, OR 0 - 20 MA/4 - 20 MA, 13 BIT RESOLUTION



Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> • 24 V DC 	Yes
Input current	
Current consumption, typ.	45 mA
from backplane bus 5 V DC, typ.	80 mA
Power loss	
Power loss, typ.	1.5 W
Analog outputs	
Number of analog outputs	4; Current or voltage
Output ranges, voltage	
<ul style="list-style-type: none"> • -10 V to +10 V 	Yes
Output ranges, current	
<ul style="list-style-type: none"> • 0 to 20 mA 	Yes
Load impedance (in rated range of output)	
<ul style="list-style-type: none"> • with voltage outputs, min. 	1 000 Ω
<ul style="list-style-type: none"> • with current outputs, max. 	600 Ω

Cable length	
• shielded, max.	100 m; shielded, twisted pair
Analog value generation for the outputs	
Integration and conversion time/resolution per channel	
• Resolution (incl. overrange)	Voltage: 14 bits; Current : 13 bits
Errors/accuracies	
Temperature error (relative to output range), (+/-)	25 °C ±0.3%, to 55 °C ±0.6% total measurement range
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to output range, (+/-)	0.3 %
• Current, relative to output range, (+/-)	0.3 %
Interference voltage suppression for $f = n \times (f_1 \pm 1 \%)$, f_1 = interference frequency	
• Common mode voltage, max.	12 V
Interrupts/diagnostics/status information	
Alarms	Yes
Diagnostic functions	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnostic messages	
• Monitoring the supply voltage	Yes
• Wire-break	Yes
• Short-circuit	Yes
Diagnostics indication LED	
• for status of the outputs	Yes
• for maintenance	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	-20 °C
• max.	60 °C
• horizontal installation, min.	-20 °C
• horizontal installation, max.	60 °C

• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Operation, min.	795 hPa
• Operation, max.	1 080 hPa
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
Relative humidity	
• Operation at 25 °C without condensation, max.	95 %
Pollutant concentrations	
• SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
Connection method	
required front connector	Yes
Mechanics/material	
Enclosure material (front)	
• Plastic	Yes
Dimensions	
Width	45 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	180 g
last modified:	11/28/2017