

## OmniVS 230V 800VA 475W Line-Interactive UPS, USB port, C13 Outlets

MODEL NUMBER: **OMNIVSINT800**



### Highlights

- 800VA tower 230V line interactive UPS
- Corrects brownouts as low as 159V without using battery power
- USB port, TEL/DSL protection
- C14 input and 4 C13 outlets

### Package Includes

- OMNIVSINT800 line interactive UPS
- 2 C13 to C14 interconnection cables
- USB and phone line cables
- Owner's manual with warranty information

### Description

Tripp Lite's OMNIVSINT800 line interactive UPS system offers voltage regulation, surge suppression and long lasting battery support for personal computers, internetworking equipment and other sensitive electronics. Internal UPS circuits support entry level PC systems for up to 40 minutes during power failures so that connected equipment can be shut down without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 159 volts back to usable levels without using battery power. Offers complete desktop power protection in an attractive black tower configuration. Includes 4 outlets with battery support and AC surge suppression. USB port enables optional unattended system shutdown without data loss in the case of extended power failure, USB cable included. PowerAlert software available via free download. Built-in single line RJ phone suppression jacks protect modem, fax machine, cordless phone or other peripheral with a standard dialup/DSL phone connection. Built-in audible alarm and 4 front panel LEDs indicate line power status, battery power status, battery low/replace status and UPS overload. 800VA power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Supports battery replacement via built-in access panel.

### Features

- OMNIVSINT800 Uninterruptible Power Supply offers voltage regulation, surge suppression and long lasting battery support
- Supports entry level PCs up to 40 minutes during blackouts to enable shutdown without data loss
- Regulates brownouts as low as 159 volts back to usable levels without using battery power
- 4 IEC320 C13 outlets with complete AC surge suppression
- C14 inlet accepts user-supplied AC power cord with country specific plug
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)
- Single line phone suppression protects standard dialup/DSL phone connection
- Audible alarm and 4 front panel LEDs offer complete UPS and line power status information



- 800VA power handling ability supports a variety of sensitive electronic equipment
- 4.3 minutes full load runtime (800VA), 10.8 minutes half load runtime (400VA)
- Supports battery replacement via built-in access panel
- Optional PDUBHV10 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Attractive full color retail packaging

## Specifications

OVERVIEW	
UPC Code	037332120960
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	2.4A
Nominal Input Voltage(s) Supported	230V AC
UPS Input Connection Type	C14 inlet
UPS Input Connection Description	Attached 15cm line cord with C14 inlet. The C14 accepts a user-supplied AC power cord with country-specific plug.
UPS Input Cord Length (ft.)	0.5
UPS Input Cord Length (m)	0.2
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	800
Output Watt Capacity (Watts)	475
Nominal Voltage Details	230V nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Battery Mode)	+/- 5%
Included Output Power Cables	Includes 2 C13 to C14 output power cables
Hot-Swap PDU options	PDUBHV10 (2U / 8 C13 outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Output Receptacles	(4) C13
Individually Controllable Load Banks	No



<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	4.3 min. (475w)
Half Load Runtime (min.)	10.8 min. (240w)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//www.tripplite.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 159
Undervoltage Correction	Input voltages between 159 and 199 are boosted by 14%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	340
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Primary Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (&nbsp;<a class="productLink" href="//www.tripplite.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems~UPSWM">UPSWM</a>&nbsp; - tower mounting kit)
Primary UPS Depth (mm)	191
Primary UPS Height (mm)	274



Primary UPS Width (mm)	132
Shipping Dimensions (hwd / cm)	24.64 x 19.05 x 34.80
Shipping Dimensions (hwd / in.)	9.70 x 7.50 x 13.70
Shipping Weight (kg)	9.94
Shipping Weight (lbs.)	21.92
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	27.43 x 13.21 x 19.05
UPS Power Module Dimensions (hwd, in.)	10.8 x 5.2 x 7.5
UPS Power Module Weight (kg)	8.85
UPS Power Module Weight (lbs.)	19.5
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
Battery Mode BTU / Hr. (Full Load)	458
AC Mode Efficiency Rating (100% Load)	97%
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management not supported
Communications Interface	USB
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	159
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic Voltage Regulation (AVR); Hot swappable batteries; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS



<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Tested to UL1778 (USA); CE; Tested to GOST (Russia); Tested to SASO (Saudi Arabia); Tested to IRAM (Argentina)
<b>WARRANTY</b>	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>