

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0151330705**  
**Status:** **Active**  
**Overview:** Pico-Clasp Wire-to-Board Connectors  
**Description:** Pico-Clasp-to-Pico-Clasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 450.00mm Length, 7 Circuits, White

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">3D Model</a>       | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">3D Model (PDF)</a> |  |

**General**

|                        |   |
|------------------------|---|
| Product Family         | Cable Assemblies                                    |
| Series                 | 15133   |
| Application            | Signal, Wire-to-Board                               |
| Assembly Configuration | Dual Ended Connectors                               |
| Connector to Connector | Pico-Clasp-to-Pico-Clasp                            |
| Overmolded             | No  |
| Overview               | <a href="#">Pico-Clasp Wire-to-Board Connectors</a> |
| Product Name           | Pico-Clasp  |
| Type                   | Discrete Wire Assembly                              |
| UPC                    | 191128140249  |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 450.00mm             |
| Circuits (Loaded)              | 7                    |
| Color - Resin                  | White                |
| Gender                         | Female-Female        |
| Lock to Mating Part            | Yes                  |
| Material - Metal               | Phosphor Bronze      |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Material - Resin               | Nylon                |
| Net Weight                     | 3.560/g              |
| Number of Rows                 | 1                    |
| Packaging Type                 | Bag                  |
| Pitch - Mating Interface       | 1.00mm               |
| Plating min - Mating           | 1.000µm              |
| Plating min - Termination      | 1.000µm              |
| Single Ended                   | No                   |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 0.60mm               |
| Wire Size AWG                  | 28                   |
| Wire/Cable Type                | UL 1571              |


**Electrical**

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 1.0A            |
| Voltage - Maximum             | 50V AC (RMS)/DC |

**Material Info**

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 2012341667-000 |
|---------------|----------------|



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

15133 Series

**Mates With**

Pico-Clasp Vertical Header [501331](#) , [504449](#)  
, [203556](#) , [203557](#) . Pico-Clasp Right-Angle  
Header [501568](#) , [202396](#) , [203558](#) , [203559](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15133-0705](#)