

TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796





Features:

- 3G/4G LTE antenna
- Fully SMT compatible
- RoHS compliant
- 40 x 7 x 3 mm
- Tape & Reel packing
- MSL-3
- Part numbers:
 - W3796
 - W3796NL (for no Pulse Logo Version)

Applications:

- Devices requiring high performance compact internal 3G/4G antenna
- Suitable for 2xMiMo use when mounting two pcs W3769 onto radio board

Issue: 2045

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

ELECTRICAL SPECIFICATIONS

Antenna Type	PCB, SMD
Frequency	698-960 / 1427.9-1660.5/
	1695-2200 / 2300-2700MHz
Nominal Impedance	$50~\Omega$
VSWR	3 : 1
Return loss	6dB
Total Efficiency (698-960MHz)	65%
Total Efficiency (1427.9-1660.5MHz)	55%
Total Efficiency (1695-2200MHz)	75%
Total Efficiency (2300-2700MHz)	70%
Average Peak Gain (698-960MHz)	1.5dBi
Average Peak Gain (1427.9-1660.5MHz)	2dBi
Average Peak Gain (1695-2200MHz)	5.5dBi
Average Peak Gain (2300-2700MHz)	5dBi
Average Gain (698-960MHz)	-2.5dBi
Average Gain (1427.9-1660.5MHz)	-3dBi
Average Gain (1695-2200MHz)	-2dBi
Average Gain (2300-2700MHz)	-1.5dBi
Maximum power input	5W

(*) All RF parameters measured on Pulse reference test PCB





TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

MECHANICAL SPECIFICATIONS

Color Black

Size 40mm(L) * 7mm(W) * 3mm(T)

Weight 1.65 g
Fixing system SMT

MSL (MOISTURE SENSITIVITY LEVEL) 3

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature -40 ~ +85° C

Storage Temperature

24 hrs at 85 ° C and 24 hrs at -40 ° C

per MIL STD 801G Method 501.5 (high)

Method 502.5 (low)

Humidity

RoHS Compliant

24hrs at 30 ° C and 93%RH

per MIL STD 810G

Method 507.5

Yes



TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

OTHER SPECIFICATIONS

1. W3796 Push Force Test

Project Name: W3796-K Test Item: Push Force>10N					
		Push Force>10N			
Sample #	Picture_Test Before	Test Setup	Picture_Test After	Test Value Antenna	Conclusion
1	@ Pulse			86.16	Pass
2		and the second		64	Pass
3				65.00	Pass
4		The state of the s		75	Pass
5				80.00	Pass
Conclusi on:	Antenna Push te	st passed.			





TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

OTHER SPECIFICATIONS

2.. W3796 Drop Test

The following sample/application is just for reference to show how to conduct the drop test when the PCB antennas W3796 is SMT on a PCB of a device.

Fig.1: Appearance photos of the samples before test.

Before assembly



assembled



Test Method: The whole assembly at 1 meter drop. A minimum of one drop per orientation - flat top, bottom, side and corner (a total of 4 drops). It's recommended to get one drop on flat top, bottom, all four flat sides and four top corners, a total of 10 drops. (Note: MIL STD and JASO D001-1994 cites to drop products on a 2 inch plywood backed by concrete floor)

P.S.:

When doing the structure design, please keep enough safe space between the W3796 and the housing, and also fix the PCB firmly in the housing to avoid any impact during the drop test.




TECHNICAL DATA SHEET


Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz


PART NUMBER: W3796

MECHANICAL DRAWING





Front View



Back View

All dimensions are measured in mm.



TECHNICAL DATA SHEET


Description: 698-960MHz, 1427.9-1660.5MHz,


1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

TEST SETUP

Pulse reference test PCB for W3796 antenna





Ground clearance dimensions (mm) and matching component values

Issue: 2045

RŏHS




TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

CHARTS



Recommended test board PCB layout for electrical characteristic measurement. Substrate material FR4.

All dimensions are in mm





TECHNICAL DATA SHEET


Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

CHARTS

Charts (free space measurements on Pulse reference test PCB)











TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

CHARTS







TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

CHARTS







TECHNICAL DATA SHEET


Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz


PART NUMBER: W3796

CHARTS


698-960MHz



Vertical plot, side view



Horizontal plot





TECHNICAL DATA SHEET


Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz


PART NUMBER: W3796


CHARTS

1427.9-1660.5MHz



Vertical plot, side view







In the effort to improve our products, we reserve th CONFIDENTIAL AND PROPRIETARY INFORMATION





TECHNICAL DATA SHEET


Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz


PART NUMBER: W3796

CHARTS


1695-2200MHz



Vertical plot, side view



Horizontal plot








TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,


1695-2200MHz, 2300-2700MHz


PART NUMBER: W3796

2300-2700MHz:



Vertical plot, side view









TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

Recommendation for reflow soldering process

Printing stencil thickness 0,15 - 0,25 mm is recommended for the solder paste. The maximum soldering temperature should not exceed 260°C. The temperature profile recommendations for reflow soldering process is presented in the Figures 1 and 2. The reflow profile

presented in figure 1 describes minimum reflow temperatures. The reflow profile presented in figure 2 describes maximum reflow temperatures. located at the center of the coverage area.

	Method of heat transfer	Controlled hot air convection
1	Average temperature gradient in preheating	2.5 °C/s
2	Soak time	2-3 minutes
3	Max temperature gradient in reflow	3 °C/s
4	Time above 217 °C	Max 30 sec
5	Peak temperature in reflow	230 °C for 10 seconds
6	Temperature gradient in cooling	Max -5 °C/s




Figure 1. Minimum temperature profile recommendation for reflow soldering process



TECHNICAL DATA SHEET

Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

Recommendation for reflow soldering process

	Method of heat transfer	Controlled hot air convection
1	Average temperature gradient in preheating	2.5 °C/s
2	Soak time	2-3 minutes
3	Max temperature gradient in reflow	3 °C/s
4	Time above 217 °C	Max 60 sec
5	Time above 230 °C	Max 50 sec
6	Time above 250 °C	Max 10 sec
7	Peak temperature in reflow	260 °C for 5 seconds
8	Temperature gradient in cooling	Max -5 °C/s




Figure 2. Maximum temperature profile recommendation for reflow soldering process



TECHNICAL DATA SHEET


Description: 698-960MHz, 1427.9-1660.5MHz,

1695-2200MHz, 2300-2700MHz

PART NUMBER: W3796

PACKAGING (TAPE & REEL)

1000pcs Antennas Per 1pcs 13" Tape & Reel 2 pcs 13" Tape & Reel (total 2000pcs Antennas) per 1 box



Issue: 2045

ROHS

18

PACKED IN ONE CARTON