
MAXLINEAR SP3223E / SP3223EB / SP3223EU

Intelligent +3.0V to +5.5V RS-232 Transceivers

FEATURES

- Meets true EIA/TIA-232-F Standards from a +3.0V to +5.5V power supply
- Interoperable with EIA/TIA-232 and adheres to EIA/TIA-562 down to a +2.7V power source
- AUTO ON-LINE[®] circuitry automatically wakes up from a 1µA shutdown
- Minimum 250Kbps data rate under load (EB)
- 1 Mbps data rate for high speed RS-232 (EU)
- Regulated Charge Pump Yields Stable RS-232 Outputs Regardless of V_{cc} Variations
- ESD Specifications: <u>+</u>15KV Human Body Model <u>+</u>15KV IEC61000-4-2 Air Discharge +8KV IEC61000-4-2 Contact Discharge



Now Available in Lead Free Packaging

DESCRIPTION

The **SP3223** products are RS-232 transceiver solutions intended for portable applications such as notebook and hand held computers. These products use an internal high-efficiency, charge-pump power supply that requires only 0.1μ F capacitors in 3.3V operation. This charge pump and **Exar's** driver architecture allow the **SP3223** series to deliver compliant RS-232 performance from a single power supply ranging from +3.3V to +5.0V. The **SP3223** is a 2-driver/2-receiver device ideal for laptop/notebook computer and PDA applications.

The AUTO ON-LINE[®] feature allows the device to automatically "wake-up" during a shutdown state when an RS-232 cable is connected and a connected peripheral is turned on. Otherwise, the device automatically shuts itself down drawing less than 1µA.

SELECTION TABLE

Device	Power Supplies	RS- 232 Drivers	RS-232 Receivers	AUTO ON-LINE ®	TTL 3-state	Data Rate (kbps)
SP3223E	+3.0V to +5.5V	2	2	YES	YES	120
SP3223EB	+3.0V to +5.5V	2	2	YES	YES	250
SP3223EU	+3.0V to +5.5V	2	2	YES	YES	1000

ABSOLUTE MAXIMUM RATINGS

These are stress ratings only and functional operation of the device at these ratings or any other above those indicated in the operation sections of the specifications below is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability and cause permanent damage to the device.

V _{cc}	0.3V to +6.0V
V+ (NOTE 1)	0.3V to +7.0V
V- (NOTE 1)	+0.3V to -7.0V
V+ + V- (NOTE 1)	+13V
I _{cc} (DC V _{cc} or GND current)	
Input Voltages	
TXIN, ONLINE,	
SHUTDOWN, EN0	.3V to Vcc + 0.3V
RxIN	<u>+</u> 15V

Output Voltages

TxOUT	<u>+</u> 13.2V
RXOUT, STATUS	0.3V to $(V_{cc} + 0.3V)$
Short-Circuit Duration	
TxOUT	Continuous
Storage Temperature	65°C to +150°C

Power Dissipation per package

20-pin SSOP (derate 9.25mW/°C above +70°C)..750mW 20-pin TSSOP (derate 11.1mW/°C above +70°C..900mW

ELECTRICAL CHARACTERISTICS

NOTE 1: V+ and V- can have maximum magnitudes of 7V, but their absolute difference cannot exceed 13V.

PARAMETER	MIN.	TYP.	MAX.	UNITS	CONDITIONS
DC CHARACTERISTICS Supply Current, AUTO ON-LINE®		1.0	10	μΑ	$\frac{\text{All RxIN open, ONLINE}}{\text{SHUTDOWN}} = \text{Vcc, TxIN} = \text{Vcc or}$ GND, Vcc = +3.3V, T _{AMB} = +25°C
Supply Current, Shutdown		1.0	10	μA	SHUTDOWN = GND, TxIN = Vcc or GND, Vcc = +3.3V, T _{AMB} = +25⁰C
Supply Current, AUTO ON-LINE® Disabled		0.3	1.0	mA	$\overline{\text{ONLINE}} = \overline{\text{SHUTDOWN}} = \text{Vcc}, \text{ No}$ Load, Vcc = +3.3V, T _{AMB} = +25°C
LOGIC INPUTS AND RECEIV	ER OUTPUT	S			
Input Logic Threshold LOW HIGH	GND 2.0		0.8 Vcc	v	Vcc = <u>3.3</u> V or 5.0V, TxIN, EN, SHUTDOWN, ONLINE
Input Leakage Current		+/-0.01	+/-1.0	μA	TxIN, EN, ONLINE, SHUTDOWN, T _{AMB} = +25°C, Vin = 0V to Vcc
Output Leakage Current		+/-0.05	+/-10	μA	Receivers disabled, Vout = 0V to Vcc
Output Voltage LOW			0.4	V	I _{оит} = 1.6mA
Output Voltage HIGH	Vcc - 0.6	Vcc - 0.1		V	I _{out} = -1.0mA

NOTE 2: C1 - C4 = 0.1µF. tested at 3.3V ±10%.

 $C1 = 0.047 \mu F$, $C2-C4 = 0.33 \mu F$, tested at 5V±10%.

ELECTRICAL CHARACTERISTICS

Unless otherwise noted, the following specifications apply for V_{cc} = +3.0V to +5.5V with T_{AMB} = T_{MIN} to T_{MAX} .	
Typical values apply at V_{cc} = +3.3V or +5.0V and T_{AMB} = 25°C (Note 2).	

PARAMETER	MIN.	TYP.	MAX.	UNITS	CONDITIONS
Driver Outputs Output Voltage Swing	+/-5.0	+/-5.4		v	All Driver outputs loaded with $3k\Omega$ to GND, T_{AMB} = +25°C
Output Resistance	300			Ω	Vcc = V+ = V- = 0V, Vout = +/-2V
Output Short-Circuit Current		+/-35	+/-60	mA	Vout = 0V
Output Leakage Current			+/-25	μA	Vcc = 0V or 3.0V to 5.5V, Vout = +/-12V, Driver disabled
RECEIVER INPUTS					
Input Voltage Range	-15		+15	V	
Input Threshold LOW	0.6	1.2		V	Vcc = 3.3V
Input Threshold LOW	0.8	1.5		V	Vcc = 5.0V
Input Threshold HIGH		1.5	2.4	V	Vcc = 3.3V
Input Threshold HIGH		1.8	2.4	V	Vcc = 5.0V
Input Hysteresis		0.3		V	
Input Resistance	3	5	7	kΩ	
AUTO ON-LINE® CIRCUITRY C	HARACTER	RISTICS (ONLINE =	GND, SH	IUTDOWN = Vcc)
STATUS Output Voltage LOW			0.4	V	I _{оит} = 1.6mА
STATUS Output Voltage HIGH	Vcc - 0.6			V	I _{оит} = -1.0mА
Receiver Threshold to Drivers Enabled (t_{ONLINE})		200		μs	Figure 15
Receiver Positive or Negative Threshold to STATUS HIGH (t_{STSH})		0.5		μs	Figure 15
Receiver Positive or Negative Threshold to STATUS LOW (t_{STSL})		20		μs	Figure 15

NOTE 2: C1 - C4 = 0.1µF, tested at 3.3V ±10%. C1 = 0.047µF, C2-C4 = 0.33µF, tested at 5V±10%.

_ TIMING CHARACTERISTICS

Unless otherwise noted, the following specifications apply for V_{CC} = +3.0V to +5.5V with T_{AMB} = T_{MIN} to T_{MAX}. Typical values apply at V_{CC} = +3.3V or +5.0V and T_{AMB} = 25°C.

PARAMETER	MIN.	TYP.	MAX.	UNITS	CONDITIONS	
Maximum Data Rate				•		
SP3223E	120	235			RL = $3k\Omega$, C _L = 1000pF, One	
SP3223EB	250			kbps	Driver active	
SP3223EU	1000				RL = $3k\Omega$, C _L = 250pF, One Driver active	
Receiver Propagation Delay	°	0	0		<u>^</u>	
$t_{_{PHL}}$ and $t_{_{PLH}}$		0.15		μA	Receiver input to Receiver output, $C_L = 150 pF$	
Receiver Output Enable Time		200		ns	Normal Operation	
Receiver Output Disable Time		200		ns	Normal Operation	
Driver Skew						
E, EB		100	500	ns	t _{PHL} - t _{PLH} , T _{AMB} = 25°C	
EU		50	100	ns		
Receiver Skew						
E, EB, EU		200	1000	ns	t _{PHL} - t _{PLH}	
Transition-Region Slew Rate						
E, EB			30		Vcc = 3.3V, RL = 3kΩ, T _{AMB} =	
EU		90		V/µs	25°C, measurements taken from -3.0V to +3.0V or +3.0V to -3.0V	




Figure 1. SP3223E Typical Operating Circuit

TYPICAL PERFORMANCE CHARACTERISTICS

Unless otherwise noted, the following performance characteristics apply for V_{cc} = +3.3V, 250Kbps data rate, all drivers loaded with 3k Ω , 0.1µF charge pump capacitors, and T_{AMB} = +25°C.




Figure 2. Transmitter Output Voltage VS. Load Capacitance for the SP3223EB




Figure 4. Supply Current VS. Load Capacitance when Transmitting Data for the SP3223EB




Figure 6. Transmitter Output Voltage VS. Supply Voltage for the SP3223EB




Figure 3. Slew Rate VS. Load Capacitance for the SP3223EB




Figure 5. Supply Current VS. Supply Voltage for the SP3223EB

TYPICAL PERFORMANCE CHARACTERISTICS

Unless otherwise noted, the following performance characteristics apply for V_{cc} = +3.3V, 1000Kbps data rate, all drivers loaded with $3k\Omega$, 0.1µF charge pump capacitors, and T_{AMB} = +25°C.




Figure 7. Transmitter Skew VS. Load Capacitance for the SP3223EU




Figure 8. Transmitter Output Voltage VS. Supply Voltage for the SP3223EU




Figure 9. Transmitter Output Voltage VS. Load Capacitance for the SP3223EU




Figure 10. Supply Current VS. Load Capacitance for the SP3223EU




Figure 11. Supply Current VS. Supply Voltage for the SP3223EU




Figure 12. Transmitter Output Voltage VS. Supply Voltage for the SP3223EU

PIN DESCRIPTION

Name	Function	Pin #			
EN	Receiver Enable, Apply logic LOW for normal operation. Apply logic HIGH to disable receiver outputs (high-Z state).	1			
C1+	Positive terminal of the voltage doubler charge-pump capacitor				
V+	Regulated +5.5V output generated by charge pump	3			
C1-	Negative terminal of the voltage doubler charge-pump capacitor	4			
C2+	Positive terminal of the inverting charge-pump capacitor	5			
C2-	Negative terminal of the inverting charge-pump capacitor	6			
V-	Regulated -5.5V output generated by charge pump	7			
T₂OUT	RS-232 Driver output	8			
R ₂ IN	RS-232 receiver input	9			
R₂OUT	TTL/CMOS receiver output	10			
STATUS	TTL/CMOS output indicating online and shutdown status	11			
T ₂ IN	TTL/CMOS driver input	12			
T₁IN	TTL/CMOS driver input	13			
ONLINE	Apply logic HIGH to override AUTO ON-LINE ® circuitry keeping drivers active (SHUTDOWN must also be logic HIGH, refer to table 2).	14			
R₁OUT	TTL/CMOS receiver output	15			
R₁IN	RS-232 receiver input	16			
T₁OUT	RS-232 Driver output	17			
GND	Ground	18			
Vcc	+3.0V to +5.5V supply voltage	19			
SHUTDOWN	Apply logic LOW to shut down drivers and charge pump. This overrides all AUTO ON-LINE ® circuitry and ONLINE (refer to table 2).	20			

Table 2. Pin Description

DESCRIPTION

The **SP3223** is a 2-driver/2-receiver device ideal for portable or handheld applications. The **SP3223** transceivers meet the EIA/TIA-232 and ITU-T V.28/V.24 communication protocols and can be implemented in battery-powered, portable, or handheld applications such as notebook or handheld computers. The **SP3223** devices feature **Exar's** proprietary on-board charge pump circuitry that generates ±5.5V RS-232 voltage levels from a single +3.0V to +5.5V power supply.

These devices are an ideal choice for power sensitive designs. Featuring **AUTOON-LINE**[®] circuitry, the **SP3223** reduces the power supply drain to a 1µA supply current. In many portable or handheld applications, an RS-232 cable can be disconnected or a connected peripheral can be turned off. Under these conditions, the internal charge pump and the drivers will be shut down. Otherwise, the system automatically comes online. This feature allows design engineers to address power saving concerns without major design changes.




Figure 13. Interface Circuitry Controlled by Microprocessor Supervisory Circuit

THEORY OF OPERATION

The **SP3223** series is made up of four basic circuit blocks:

1. Drivers, 2. Receivers, 3. The Exar proprietary charge pump, and 4. *AUTO ON-LINE*[®] circuitry.

Drivers

The drivers are inverting level transmitters that convert TTL or CMOS logic levels to 5.0V EIA/TIA-232 levels with an inverted sense relative to the input logic levels. Typically, the RS-232 output voltage swing is \pm 5.4V with no load and \pm 5V minimum fully loaded. The driver outputs are protected against infinite short-circuits to ground without degradation in reliability. These drivers comply with the EIA-TIA-232F and all previous RS-232 versions. Unused driver inputs should be connected to GND or V_{cc}.

The drivers can guarantee output data rates fully loaded with $3k\Omega$ in parallel with 1000pF, (SP3223EU, C_L= 250pF) ensuring compatibility with PC-to-PC communication software.

The slew rate of the driver output on the E and EB versions is internally limited to a maximum of $30V/\mu$ s in order to meet the EIA standards (EIARS-232D2.1.7, Paragraph5). The Slew Rate of EU version is not limited to enable higher speed data transfers. The transition of the loaded output from HIGH to LOW also meets the monotonicity requirements of the standard.

Figure 14 shows a loopback test circuit used to test the RS-232 Drivers. *Figure 15* shows the test results where one driver was active at 250kbps and all drivers are loaded with an RS-232 receiver in parallel with a 1000pF capacitor. RS-232 data transmission rate of 120kbps to 1Mbps provide compatibility with designs in personal computer peripherals and LAN applications.

Device: SP3223							
SHUTDOWN	EN	T _x OUT	R _x OUT				
0	0	High Z	Active				
0	1	High Z	High Z				
1	0	Active	Active				
1	1	Active	High Z				

Table 3. SHUTDOWN and EN Truth Tables Note: In AUTO ON-LINE[®] Mode where ONLINE = GND and SHUTDOWN = V_{cc} , the device will shut down if there is no activity present at the Receiver inputs.

Receivers

The receivers convert ±5.0V EIA/TIA-232 levels to TTL or CMOS logic output levels. Receivers have an inverting output that can be disabled by using the EN pin.

Receivers are active when the AUTO ON-LINE® circuitry is enabled or when in shutdown. During the shutdown, the receivers will continue to be active. If there is no activity present at the receivers for a period longer than 100 μ s or when SHUTDOWN is enabled, the device goes into a standby mode where the circuit draws 1 μ A. Driving EN to a logic HIGH forces the outputs of the receivers into high-impedance. The truth table logic of the **SP3223** driver and receiver outputs can be found in *Table 2*.

Since receiver input is usually from a transmission line where long cable lengths and system interference can degrade the signal, the inputs have a typical hysteresis margin of 300mV. This ensures that the receiver is virtually immune to noisy transmission lines. Should an input be left unconnected, an internal $5k\Omega$ pull-down resistor to ground will commit the output of the receiver to a HIGH state.




Figure 14. Loopback Test Circuit for RS-232 Driver Data Transmission Rates




Figure 15. Loopback Test Circuit result at 250Kbps (All Drivers Fully Loaded)

Charge Pump

The charge pump uses a unique approach compared to older less–efficient designs. The charge pump still requires four external capacitors, but uses a four–phase voltage shifting technique to attain symmetrical 5.5V power supplies. The internal power supply consists of a regulated dual charge pump that provides output voltages of +/-5.5V regardless of input voltage (V_{cc}) over the +3.0V to +5.5V range. This is important to maintain compliant RS-232 levels regardless of power supply fluctuations.

The charge pump operates in a discontinuous mode using an internal oscillator. If the output voltages are less than a magnitude of 5.5V, the charge pump is enabled. If the output voltages exceed a magnitude of 5.5V, the charge pump is disabled. This oscillator controls the four phases of the voltage shifting. A description of each phase follows.

Phase 1

— V_{ss} charge storage — During this phase of the clock cycle, the positive side of capacitors C₁ and C₂ are initially charged to V_{cc}. C₁⁺ is then switched to GND and the charge in C₁⁻ is transferred to C₂⁻. Since C₂⁺ is connected to V_{cc}, the voltage potential across capacitor C₂ is now 2 times V_{cc}.

Phase 2

— V_{ss} transfer — Phase two of the clock connects the negative terminal of C_2 to the V_{ss} storage capacitor and the positive terminal of C_2 to GND. This transfers a negative generated voltage to C_3 . This generated voltage is regulated to a minimum voltage of -5.5V. Simultaneous with the transfer of the voltage to C_3 , the positive side of capacitor C_1 is switched to V_{cc} and the negative side is connected to GND.

Phase 3

 $-V_{DD}$ charge storage — The third phase of the clock is identical to the first phase — the charge transferred in C₁ produces $-V_{CC}$ in the negative terminal of C₁, which is applied to the negative side of capacitor C₂. Since C₂⁺ is at V_{CC}, the voltage potential across C₂ is 2 times V_{CC}.

Phase 4

— V_{DD} transfer — The fourth phase of the clock connects the negative terminal of C_2 to GND, and transfers this positive generated voltage across C_2 to C_4 , the V_{DD} storage capacitor. This voltage is regulated to +5.5V. At this voltage, the internal oscillator is disabled. Simultaneous with the transfer of the voltage to C_4 , the positive side of capacitor C_1 is switched to V_{CC} and the negative side is switched to GND, allowing the charge pump cycle to begin again. The charge pump cycle will continue as long as the operational conditions for the internal oscillator are present.

Since both V⁺ and V⁻ are separately generated from V_{cc}, in a no–load condition V⁺ and V⁻ will be symmetrical. Older charge pump approaches that generate V⁻ from V⁺ will show a decrease in the magnitude of V⁻ compared to V⁺ due to the inherent inefficiencies in the design.

The Exar charge pump is designed to operate reliably with a range of low cost capacitors. Either polarized or non polarized capacitors may be used. If polarized capacitors are used they should be oriented as shown in the Typical Operating Circuit. The V+ capacitor may be connected to either ground or Vcc (polarity reversed.)

The charge pump operates with 0.1μ F capacitors for 3.3V operation. For other supply voltages, see table 4 for required capacitor values. Do not use values smaller than those listed. Increasing the capacitor values (e.g., by doubling in value) reduces ripple on the transmitter outputs and may slightly reduce power consumption. C2, C3, and C4 can be increased without changing C1's value.

For best charge pump efficiency locate the charge pump and bypass capacitors as close as possible to the IC. Surface mount capacitors are best for this purpose. Using capacitors with lower equivalent series resistance (ESR) and self-inductance, along with minimizing parasitic PCB trace inductance will optimize charge pump operation. Designers are also advised to consider that capacitor values may shift over time and operating temperature.




Figure 16. Charge Pump - Phase 1




Figure 17. Charge Pump - Phase 2




Figure 18. Charge Pump Waveforms




Figure 19. Charge Pump - Phase 3





Figure 20. Charge Pump - Phase 4

Minimum recommended charge pump capacitor value				
Input Voltage V _{cc} Charge pump capacitor value				
3.0V to 3.6V	C1 - C4 = 0.1µF			
4.5V to 5.5V	C1 = 0.047µF, C2-C4 = 0.33µF			
3.0V to 5.5V	C1 - C4 = 0.22µF			



AUTO ON-LINE® Circuitry

The **SP3223** device has **AUTO ON-LINE**[®] circuitry on board that saves power in applications such as laptop computers, PDA's, and other portable systems.

The SP3223 device incorporates an AUTO ON-LINE® circuit that automatically enables itself when the external transmitter is enabled and the cable is connected. Conversely. the AUTO ON-LINE® circuit also disables most of the internal circuitry when the device is not being used and goes into a standby mode where the device typically draws 1µA. This function is externally controlled by the ONLINE pin. When this pin is tied to a logic LOW, the AUTO ON-LINE® function is active. Once active, the device is enabled until there is no activity on receiver inputs. The receiver input typically sees at least ±3V, which are generated from the transmitter at the other end of the cable with a ±5V minimum. When the external transmitter is disabled or the cable is disconnected, the receiver input will be pulled down by its internal $5k\Omega$ resistor to ground. When this occurs over a period of time, the internal transmitters will be disabled and the device goes into a shutdown or standby mode. When the ONLINE pin is HIGH, the AUTO **ON-LINE[®]** mode is disabled.

The **AUTO ON-LINE**[®] circuit has two stages:

1) Inactive Detection
 2) Accumulated Delay

The first stage, shown in Figure 22, detects an inactive input. A logic HIGH is asserted on R_x INACT if the cable is disconnected or the external transmitters are disabled. Otherwise, R_x INACT will be at a logic LOW. This circuit is duplicated for each of the other receivers.

The second stage of the AUTO ON-LINE® circuitry, shown in Figure 23, processes the receiver's R_vINACT signal with an accumulated delay that disables the device to a 1µA typical supply current. The STATUS pin goes to a logic LOW when the cable is disconnected, the external transmitter is disabled, or the SHUTDOWN pin is invoked. The typical accumulated delay is around 20µs. When the SP3223 drivers and internal charge pump are disabled, the supply current is reduced to 1µA typical. This can commonly occur in handheld or portable applications where the RS-232 cable is disconnected or the RS-232 drivers of the connected peripheral are truned off. The AUTO ON-LINE® mode can be disabled by the SHUTDOWN pin. If this pin is a logic LOW, the AUTO ON-LINE® function will not operate regardless of the logic state of the ONLINE pin. Table 5 summarizes the logic of the AUTO ON-LINE® operating modes. The truth table logic of the SP3223 driver and receiver outputs can be found in Table 3.

The STATUS pin outputs a logic LOW signal if the device is shutdown. This pin goes to a logic HIGH when the external transmitter is enabled and the cable is connected.

When the **SP3223** device is shutdown, the charge pumps are turned off. V+ charge pump output decays to V_{cc} , the V- output decays to GND. The decay time will depend on the size of capacitors used for the charge pump. Once in shutdown, the time required to exit the shut down state and have valid V+ and V- levels is typically 200µs.

For easy programming, the STATUS can be used to indicate DTR or a Ring Indicator signal. Tying ONLINE and SHUTDOWN together will bypass the **AUTO ON-LINE**[®] circuitry so this connection acts like a shutdown input pin






Figure 21. AUTO ON-LINE® Timing Waveforms

RS-232 SIGNAL AT RECEIVER INPUT	SHUTDOWN	ONLINE	STATUS	TRANSCEIVER STATUS
YES	HIGH	LOW	HIGH	Normal Operation (AUTO ON-LINE©)
NO	HIGH	HIGH	LOW	Normal Operation
NO	HIGH	LOW	LOW	Shutdown (AUTO ON-LINE©)
YES	LOW	HIGH/LOW	HIGH	Shutdown
NO	LOW	HIGH/LOW	LOW	Shutdown

Table 5. AUTO ON-LINE® Logic







ESD TOLERANCE

The **SP3223** series incorporates ruggedized ESD cells on all driver output and receiver input pins. The ESD structure is improved over our previous family for more rugged applications and environments sensitive to electro-static discharges and associated transients. The improved ESD tolerance is at least ±15kV without damage nor latch-up.

There are different methods of ESD testing applied:

a) MIL-STD-883, Method 3015.7 b) IEC61000-4-2 Air-Discharge c) IEC61000-4-2 Direct Contact

The Human Body Model has been the generally accepted ESD testing method for semiconductors. This method is also specified in MIL-STD-883, Method 3015.7 for ESD testing. The premise of this ESD test is to simulate the human body's potential to store electro-static energy and discharge it to an integrated circuit. The simulation is performed by using a test model as shown in Figure 24. This method will test the IC's capability to withstand an ESD transient during normal handling such as in manufacturing areas where the IC's tend to be handled frequently.

The IEC-61000-4-2, formerly IEC801-2, is generally used for testing ESD on equipment and systems. For system manufacturers, they must guarantee a certain amount of ESD protection since the system itself is exposed to the outside environment and human presence. The premise with IEC61000-4-2 is that the system is required to withstand an amount of static electricity when ESD

is applied to points and surfaces of the equipment that are accessible to personnel during normal usage. The transceiver IC receives most of the ESD current when the ESD source is applied to the connector pins. The test circuit for IEC61000-4-2 is shown on Figure 25. There are two methods within IEC61000-4-2, the Air Discharge method and the Contact Discharge method. With the Air Discharge Method, an ESD voltage is applied to the equipment under test (EUT) through air. This simulates an electrically charged person ready to connect a cable onto the rear of the system only to find an unpleasant zap just before the person touches the back panel. The high energy potential on the person discharges through an arcing path to the rear panel of the system before he or she even touches the system. This energy, whether discharged directly or through air, is predominantly a function of the discharge current rather than the discharge voltage. Variables with an air discharge such as approach speed of the object carrying the ESD potential to the system and humidity will tend to change the discharge current. For example, the rise time of the discharge current varies with the approach speed.

The Contact Discharge Method applies the ESD current directly to the EUT. This method was devised to reduce the unpredictability of the ESD arc. The discharge current rise time is constant since the energy is directly transferred without the air-gap arc. In situations such as hand held systems, the ESD charge can be directly discharged to the equipment from a person already holding the equipment. The current is transferred on to the keypad or the serial port of the equipment directly and then travels through the PCB and finally to the IC.




Figure 24. ESD Test Circuit for Human Body Model




Figure 25. ESD Test Circuit for IEC61000-4-2

The circuit model in *Figures 24* and 25 represent the typical ESD testing circuit used for all three methods. The C_s is initially charged with the DC power supply when the first switch (SW1) is on. Now that the capacitor is charged, the second switch (SW2) is on while SW1 switches off. The voltage stored in the capacitor is then applied through R_s , the current limiting resistor, onto the device under test (DUT). In ESD tests, the SW2 switch is pulsed so that the device under test receives a duration of voltage.

For the Human Body Model, the current limiting resistor (R_s) and the source capacitor (C_s) are 1.5k Ω an 100pF, respectively. For IEC-61000-4-2, the current limiting resistor (R_s) and the source capacitor (C_s) are 330 Ω an 150pF, respectively.

The higher C_s value and lower R_s value in the IEC61000-4-2 model are more stringent than the Human Body Model. The larger storage capacitor injects a higher voltage to the test point when SW2 is switched on. The lower current limiting resistor increases the current charge onto the test point.






Figure 26. ESD Test Waveform for IEC61000-4-2

DEVICE PIN TESTED	HUMAN BODY MODEL	Air Discharge	IEC61000-4-2 Direct Contact	Level
Driver Outputs	±15kV	±15kV	±8kV	4
Receiver Inputs	±15kV	±15kV	±8kV	4

PACKAGE: 20 Pin TSSOP



PACKAGE: 20 Pin SSOP



ORDERING INFORMATION(1)


Part Number	Temperature Range	Package	Packaging Method	Lead-Free ⁽²⁾	
SP3223EB					
SP3223EBEY-L/TR	-40°C to +85°C	20-pin TSSOP	Tape and Reel	Yes	
SP3223E					
SP3223ECA-L/TR	0°C to +70°C	20-pin SSOP	Tape and Reel	Yes	
SP3223ECY-L	0°C to +70°C	20-pin TSSOP	Tube	Yes	
SP3223ECY-L/TR	0°C to +70°C	20-pin TSSOP	Tape and Reel	Yes	
SP3223EEA-L	-40°C to +85°C	20-pin SSOP	Tube	Yes	
SP3223EEA-L/TR	-40°C to +85°C	20-pin SSOP	Tape and Reel	Yes	
SP3223EEY-L	-40°C to +85°C	20-pin TSSOP	Tube	Yes	
SP3223EEY-L/TR	-40°C to +85°C	20-pin TSSOP	Tape and Reel	Yes	
SP3223EU					
SP3223EUEY-L/TR	-40°C to +85°C	20-pin TSSOP	Tape and Reel	Yes	

NOTES:

1. Refer to <u>www.maxlinear.com/SP3223EB</u>, <u>www.maxlinear.com/SP3223E</u>, and

www.maxlinear.com/SP3223EU for most up-to-date Ordering Information.

2. Visit <u>www.maxlinear.com</u> for additional information on Environmental Rating.



REVISION HISTORY

DATE	REVISION	DESCRIPTION	
10-06-06		Legacy Sipex data sheet	
Nov 2010	1.0.0	Convert to Exar data sheet format and remove EOL parts.	
June 2012	1.0.1	Correct type error on page 1 pin diagram. Pin 9 should be R2IN not R1IN, Change ESD protection levels to IEC61000-4-2.	
Mar 2020	1.0.2	Update to MaxLinear logo. Update Ordering Information.	



MaxLinear, Inc. 5966 La Place Court, Suite 100 Carlsbad, CA 92088 760.692.0711 p. 760.444.8598 f. www.maxlinear.com

The content of this document is furnished for informational use only, is subject to change without notice, and should not be construed as a commitment by MaxLinear, Inc. MaxLinear, Inc. assumes no responsibility or liability for any errors or inaccuracies that may appear in the informational content contained in this guide. Complying with all applicable copyright laws is the responsibility of the user. Without limiting the rights under copyright, no part of this document may be reproduced into, stored in, or introduced into a retrieval system, or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), or for any purpose, without the express written permission of MaxLinear, Inc.

Maxlinear, Inc. does not recommend the use of any of its products in life support applications where the failure or malfunction of the product can reasonably be expected to cause failure of the life support system or to significantly affect its safety or effectiveness. Products are not authorized for use in such applications unless MaxLinear, Inc. receives, in writing, assurances to its satisfaction that: (a) the risk of injury or damage has been minimized; (b) the user assumes all such risks; (c) potential liability of MaxLinear, Inc. is adequately protected under the circumstances.

MaxLinear, Inc. may have patents, patent applications, trademarks, copyrights, or other intellectual property rights covering subject matter in this document. Except as expressly provided in any written license agreement from MaxLinear, Inc., the furnishing of this document does not give you any license to these patents, trademarks, copyrights, or other intellectual property.

MaxLinear, the MaxLinear logo, and any MaxLinear trademarks, MxL, Full-Spectrum Capture, FSC, G.now, AirPHY and the MaxLinear logo are all on the products sold, are all trademarks of MaxLinear, Inc. or one of MaxLinear's subsidiaries in the U.S.A. and other countries. All rights reserved. Other company trademarks and product names appearing herein are the property of their respective owners.

© 2006 - 2020 MaxLinear, Inc. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MaxLinear:

<u>SP3223ECY-L</u> <u>SP3223EEA-L</u> <u>SP3223EEY-L</u> <u>SP3223ECA-L/TR</u> <u>SP3223EEA-L/TR</u> <u>SP3223EEY-L/TR</u> <u>SP3223EY-L/TR</u> <u>SP3223EEY-L/TR</u> <u>SP3223EEY-L/TR</u> <u>SP3223EY-L/TR</u> <u>SP32</u>