

# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

## Your advantages

- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

## Commercial data

Item number	1051003
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2112
Catalog page	Page 118 (C-3-2019)
GTIN	4017918015824
Weight per piece (including packing)	1.6 g
Weight per piece (excluding packing)	1.55 g
Customs tariff number	39269097
Country of origin	DE

# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

## Technical data

### Notes

General	Can be labeled with CMS
---------	-------------------------

### Product properties

Product type	Terminal marking
Pitch	6.2 mm
Type	high

### Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

### Dimensions

Width	6 mm
Pitch	6.2 mm

### Material specifications

Color	white
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Standards and regulations


Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	snapped
---------------	---------

Drawings

Schematic diagram



# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

## Classifications

### ECLASS

ECLASS-11.0	27281101
ECLASS-12.0	27281101
ECLASS-13.0	27281101

### ETIM

ETIM 9.0	EC000761
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

# ZB 6:UNBEDRUCKT - Zack marker strip

1051003

<https://www.phoenixcontact.com/us/products/1051003>




## Accessories

### PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/us/products/0804499>

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.




---

### CMS-P1-PLOTTER - Marking plotter

5144615

<https://www.phoenixcontact.com/us/products/5144615>

Marking plotter, weight: 8 kg, length: 0.66 m, width: 440 mm, height: 125 mm, color: silver



# ZB 6:UNBEDRUCKT - Zack marker strip



1051003

<https://www.phoenixcontact.com/us/products/1051003>

## CMS-P1-M/ZB - Magazine insert

5144699

<https://www.phoenixcontact.com/us/products/5144699>



Plastic magazines for CMS-P1-PLOTTER and PLOTMARK. For accommodating 22 zack marker strips

---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)