1-6437630-1 V ACTIVE



Alcoswitch

TE Internal #: 1-6437630-1

TE Internal Description: AWTS1504

View on TE.com >



Relays, Contactors & Switches > Switches > Toggle Switches



Configuration (Pole-Throw): Double Pole - Double Throw

Sealed: Yes

Contact Base Material: Brass

Switch Contact Plating Material: Silver Alloy

Seal Type: Waterproof

Features

Product Type Features

| Product Type | Switch |
|------------------|--------------|
| Sealed | Yes |
| Toggle Style | Baton |
| Switch Type | Power Toggle |
| Toggle Actuation | Vertical |

Configuration Features

| Configuration (Pole-Throw) | Double Pole - Double Throw |
|----------------------------|----------------------------|
| Operating Function | (On) Off (On) |

Electrical Characteristics

| Dielectric Strength | 1500 VAC |
|------------------------------|--------------------------|
| Insulation Resistance | 1000 MΩ |
| UL/CSA Current Rating (250V) | 20 A |
| Contact Resistance | 10 mΩ |
| Voltage Rating | 125 VAC, 250 VAC, 30 VDC |
| | |

Body Features

| Seal Type | Waterproof |
|---------------|------------|
| Bushing Style | Unthreaded |

Contact Features

| Contact Base Material | Brass |
|-----------------------|-------|
|-----------------------|-------|



| Silver Alloy |
|------------------------------------|
| 20 A |
| |
| .25 x .032 Quick Connect Terminals |
| |
| Panel |
| |
| 17.48 mm[.688 in] |
| |
| (ON) - OFF - (ON) |
| |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
|---|---|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201) Pb (3.7% in Component Part) |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201) |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished



product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

































Customers Also Bought





TE Model / Part #160300 PLASTI-GRIP 12-10 RING M10



TE Model / Part #5-6437630-0 AWTR1504 = POWER TOGGLE



AWTN1504 = POWER TOGGLE





TE Model / Part #5-1393302-8 V23134A1052C643-EV-CBOX



TE Model / Part #1-1337416-0 N Str Plg Hex 50Ohm Silver Pltd RG58C/U,



N Str Plg Hex 50Ohm Silver Pltd PSF 1 /4M







Documents

Product Drawings

AWTS1504

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-6437630-1_B_c-1-6437630-1-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-6437630-1_B_c-1-6437630-1-b.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-6437630-1_B_c-1-6437630-1-b.3d_igs.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English

AW_SERIES_SWITCHES_QUICK_REF_GUIDE_1-1773458-8

English

Product Environmental Compliance

REACH Substance Communication Document

English