

6-Outlet Industrial Surge Protector, 6 ft. (1.83 m) Cord, 900 Joules, 12.5 in. length

MODEL NUMBER: **PM6NS**



Highlights

- 6 outlets/6-ft. (1.83 m) cord
- 900 joules

Package Includes

- PM6NS Power Strip
- Warranty information
- Instruction manual

Description

The Weber-by-Tripp Lite PM6NS Power Strip offers a convenient method of power distribution and surge suppression in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles, 6-ft. (1.83 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built in surge suppression rated at 900 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15 amp resettable circuit breaker and attractive beige housing with black output receptacles and power cord.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip with surge suppression

SUPPRESSION - 900 joules AC suppression

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1449 3rd Edition (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6-ft. (1.83 m) AC line cord
- 900 joule rating
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications



OVERVIEW	
UPC Code	037332100948
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	45000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and lighted two position power switch controls power to all outlets
Diagnostic LED Details	Protection present (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	900
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Up to 20 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Metal
Antimicrobial	No
Power Cord Color	Black
Housing Color	Beige
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	165mm
Outlets Measurement (Center to Center)	38.89mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	34.80 x 5.72 x 14.99
Shipping Dimensions (hwd / in.)	13.70 x 2.25 x 5.90
Shipping Weight (kg)	0.77
Shipping Weight (lbs.)	1.70
Unit Dimensions (hwd / cm)	3.81 x 31.75 x 6.35
Unit Dimensions (hwd / in.)	1.5 x 12.5 x 2.5
Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.2
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>