


# Proximity Magnetic Sensors Rectangular Body, MM series



- Plastic rectangular case
- Extremely small dimensions
- High sensibility contacts
- NO or CO output functions

## Product Description

The micro-miniature types are characterized by extremely small dimensions.

The MM.A.6 model contains, in a very small case, a very high sensibility contact, with

low hysteresis.

The two fixing holes, suited for M3 screws, allow simple mounting procedure over a large variety of applications.

## Ordering Key

**MM.A.3**

Type \_\_\_\_\_  
 Output Function \_\_\_\_\_  
 Reed contact Type \_\_\_\_\_

## Type Selection

Output function	External dimensions	Output connection	Reference
NO	14 x 23,5 x 6,1	Twin lead cable	MM.A.6
	7 x 27 x 11	PVC Cable	MM.A.3
Change-over			MM.S.1

## General specification

Case	Plastic
Protection degree	IP67
Operating temperature	-25 to +75 °C


## Electrical specifications

Contacts	3	6	S.1
Max switching voltage	500 Vac	100 Vdc	100 Vac
Max switching current	0,5 A	1 A	0,25 A
Max switching power	10 VA	10 VA	5 VA


## Operating distance

Magnetic Units	CL.1	CL.2	CL.3	CL.4
MM.S.1, MM.A.3	10	15	22	35
MM.A.6	14	20	30	40

## Dimensions



## Wiring Diagrams



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[MMA3](#) [MMFR15](#) [MNFR15](#) [MNFT15](#) [MMFT15](#) [MMS1](#) [MM.A.6](#) [MM.S1](#) [MMA6](#)