

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1068000064](#)
Status: **Active**
Overview: Polymicro Optical Fibers
Description: Polymicro Optical Fiber, Low OH, VIS-NIR, 600um, FIP600660710

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Optical Fiber
Series	106800
Application	Industrial, Medical, Research, Scientific, and other
Catalog	www.molex.com/polymicro/catalog
Fiber Series	FIP
More Detailed Tech Information	www.molex.com/polymicro/fi
Overview	Polymicro Optical Fibers
Polymicro	Yes
Product Name	FIP Optical Fiber
UPC	883906617493
White Paper-Published Articles	www.molex.com/polymicro/whitepapers
Wire/Cable Type	Silica Optical Fiber

Physical

Buffer Diameter	710µm
Buffer Tolerance	± 10µm
Clad Diameter	660µm
Cladding Tolerance	± 10µm
Cladding Type	Doped Silica
Core Diameter	600µm
Core Tolerance	± 10µm
Glass Characteristic	Ultra Low -OH
Long-Term Bend Radius	N/A
Material - Buffer	Polyimide
Material - Glass	Synthetic Fused Silica
Net Weight	0.830/g
Numerical Aperture	0.22±0.02
Packaging Type	Spool
Proof Tested @ Minimum 100kpsi	100% for Strength
Short-Term Bend Radius	N/A
Temperature Range - Operating	-65° to +300°C
Wavelength Range	380nm - 2200nm

Material Info

Engineering Number	2000064
--------------------	---------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[106800 Series](#)

Use With

Ferrules, Sleeves, SMA Connectors, and
Custom Connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106800-0064](#)