




38M3050AA0606



Part Number: 38M3050AA0606

Material Grade	M3
Sheet Size	60 x 60 mm
Ferrite Thickness	0.5 mm
Total Thickness	0.53 mm





	Typical Shielding Effectiveness (dB): Test Method as noted → **, ***					
PARTNUMBER	Material	1MHz**	6.78MHz**	13.56MHz**	100MHz***	300MHz***
38M3050AA0606	M3	9	9	9	9.3	6.1

** Shielding Effectiveness (SE) at 1 -50MHz : measured using IEC 6233-2 Rde Inter Decoupling Ratio method (loop to loop distance= 6mm).
 This method is meaningful as a measure of decoupling effectiveness circuit to circuit or to metal surfaces (plane to plane).

*** Shielding Effectiveness (SE) at 100MHz+ : measured using IEC 6233-2 Rrs Radiation Suppression Ratio method (50-ohm Microstripline).
 This method is meaningful as a measure of shielding for radiated emissions of “antennas”.

Equipment Used:

E5072A Vector Network Analyzer (30kHz – 8.5 GHz)
HP4291A RF Impedance/Material Analyzer (1MHz-3GHz)
E4991A with 16453A Dielectric Test Fixture
HP4284A for Temperature testing
25mm diameter slotted loop antennas
50-ohm Micro-Stripline Test Fixture



Fair-Rite Products Corp. • One Commercial Row, Wallkill, New York 12589-0288
888-324-7748 • 845-895-2055 • Fax: 845-895-2629 • ferrites@fair-rite.com • www.fair-rite.com