


Vishay Roederstein

DC Film Capacitors MKT Axial Type








HALOGEN FREE GREEN

(5-2008)



APPLICATIONS

Blocking, bypassing, filtering, timing, coupling and decoupling, interference suppression in low voltage applications.

QUICK REFERENCE DATA		
Capacitance range (E12 series)	470 pF to 22 μF	
Capacitance tolerance	± 20 %, ± 10 %, ± 5 %	
Climatic testing class according to IEC 60068-1	55/100/56	
Maximum application temperature	100 °C	
Reference specifications	IEC 60384-2	
Dielectric	Polyester film	
Electrodes	Metallized	
Construction	Mono and internal series construction	
Encapsulation	Plastic-wrapped, epoxy resin sealed, flame retardant	
Leads	Tinned wire	
Marking	C-value; tolerance; rated voltage; manufacturer's type; code for dielectric material; manufacturer location; manufacturer's logo; year and week	
Rated DC voltage	63 V _{DC} , 100 V _{DC} , 250 V _{DC} , 400 V _{DC} , 630 V _{DC} , 1000 V _{DC}	
Rated AC voltage	40 V _{AC} , 63 V _{AC} , 160 V _{AC} , 200 V _{AC} , 220 V _{AC}	
Pull test on leads	Minimum 20 N in direction of leads according to IEC 60068-2-21	
Bent test on leads	2 bends through 90° combined with 10 N tensile strength	
Reliability	Operational life > 300 000 h (40 °C/0.5 U _R) Failure rate < 2 FIT (40 °C/0.5 U _B)	


Note

• For more detailed data and test requirements, contact dc-film@vishay.com

DIMENSIONS in millimeters					
Ø d V A0.0 ± 5.0 L Max. 40.0 ± 5.0 Max.					
LEAD DIAMETER d	D				
0.6	≤ 5.0				
0.7	> 5.0 ≤ 7.0				
0.8	> 7.0 < 16.5				
1.0	≥ 16.5				



COMPOSITION OF CATALOG NUMBER



Note

• For detailed tape specifications refer to "Packaging Information" www.vishay.com/doc?28139 or end of catalog

SPECIFIC RE	FERENCE DA	TA				
DESCRIPTION					VALUE	
Tangent of loss an	igle:			at 1 kHz	at 10 kHz	at 100 kHz
$C = 0.1 \mu F$			80 x 10 ⁻⁴	150 x 10 ⁻⁴	250 x 10 ⁻⁴	
$0.1 \ \mu F \le C = 1.0 \ \mu$	F			80 x 10 ⁻⁴	150 x 10 ⁻⁴	-
$C \geq 1.0 \; \mu F$				100 x 10 ⁻⁴	-	-
CAPACITOR		MA	XIMUM PULSE RIS	SE TIME (dU/dt) _R [V/	/µs]	
LENGTH (mm)	63 V _{DC}	100 V _{DC}	250 V _{DC}	400 V _{DC}	630 V _{DC}	1000 V _{DC}
11	12	18	32	56	84	-
14	11	13	22	37	66	175
19	7	8	13	21	33	65
26.5	4	5	8	13	19	34
31.5	3	4	6	10	15	25
41.5	2	3	5	7	10	17
	If the maximum p	ulse voltage is less th	nan the rated voltage	e higher dU/dt values	can be permitted.	
R between leads,	for $C \le 0.33 \mu F$ and	$U_R \leq 100 \; V$			> 15 0	00 MΩ
R between leads, for C \leq 0.33 μF and $U_R > 100 \ V$					> 30 000 MΩ	
RC between leads, for C > 0.33 μF and $U_R \leq 100 \ V$					> 5000 s	
RC between leads, for C > 0.33 μF and $U_R > 100 \ V$					> 10 000 s	
R between leads a	and case, 100 V; (fo	il method)			> 30 0	00 MΩ
Withstanding (DC)	voltage (cut off cur	rent 10 mA); rise time	e 100 V/s		1.6 x U _R	_{DC} , 1 min
Maximum applicat	tion temperature				100) °C



LECTRICAL	DATA					
U _{RDC}	CAP.	CAPACITANCE	VOLTAGE	V _{AC}	DIMEN	SIONS
(V)	(μF)	CODE	CODE	▼ AC	D	L
	0.15	415			5.0	11.0
	0.22	422			5.0	11.0
					-	-
	0.33	433			6.0	14.0
					-	-
	0.47	447			7.0	14.0
					- 6.5	- 10.0
	0.68	468			6.5	19.0
	1.0	510			7.5	19.0
	1.0	310			8.5	19.0
63	1.5	515	06	40	-	-
					8.5	26.5
	2.2	522			7.5	19.0 ⁽²⁾
					10.0	26.5
	3.3	533			8.5	19.0 ⁽²⁾
	4.7	E 4.7			11.5	26.5
	4.7	547			-	-
	6.8	568			12.0	31.5
	10.0	610			14.5	31.5
					-	-
	15.0	615			18.0	31.5
	22.0	622			17.5	41.5
	0.068	368			5.0	11.0
	0.10	410			5.0	11.0
	0.15	44.5			-	- 11.0
	0.15	415			5.5 6.0	11.0 14.0
	0.22	422			-	-
					6.0	19.0
	0.33	433			-	-
					6.5	19.0
	0.47	447			-	-
	2.22	400			7.0	19.0
	0.68	468			-	-
100	1.0	510	01	63	8.5	19.0
	1.5	515			8.0	26.5
	1.5	010			8.0	19.0 ⁽²⁾
	2.2	522			9.5	26.5
					9.5	19.0 ⁽²⁾
	3.3	533			11.5	26.5
					- 12.0	- 21.5
	4.7	547			12.0	31.5
	6.8	568			14.0	31.5
					16.5	31.5
	10.0	610			13.5	31.5 ⁽²⁾
		1				00





LECTRICAI	DATA					
U _{RDC}	CAP.	CAPACITANCE	VOLTAGE	V _{AC}	DIMEN	ISIONS
(V)	(μF)	CODE	CODE	▼ AC	D	L
	0.015	315			5.0	11.0
	0.022	322			5.0	11.0
	0.033	333			5.0	11.0
	0.047	347			6.0	14.0
	0.068	368			6.0	14.0
	0.10	410			6.0	14.0
	0.15	415			7.0	14.0
	0.22	422			7.0	19.0
	0.33	433			8.0	19.0
					-	-
	0.47	447			9.0	19.0
250	0.68	468	25	160	8.5	26.5
					9.0	19.0 ⁽²⁾
	1.0	510			10.0	26.5
	1.5	515			11.0	31.5
					13.0	31.5
	2.2	522			-	-
		500			15.5	31.5
	3.3	533			14.0	26.5 ⁽²⁾
	4.7	E 4.7			15.5	41.5
	4.7	547			14.5	31.5 ⁽²⁾
	6.8	568			17.5	41.5
	10.0	610			21.0	41.5
	0.0068	268			5.0	11.0
	0.010	310			5.0	11.0
	0.015	315			6.0	14.0
	0.022	322			6.0	14.0
	0.033	333			6.0	14.0
	0.047	347			7.0	14.0
	0.068	368			8.0	14.0
	0.10	410			7.0	19.0
	0.15	415			8.5	19.0
					8.0	26.5
400	0.22	422	40	200	8.0	19.0 ⁽²⁾
	0.33	433			9.5	26.5
					9.5	19.0 ⁽²⁾
	0.47	447			11.0	26.5
	0.68	468			11.5	31.5
	1.0	510			13.5	31.5
					14.0	41.5
	1.5	515			13.0	31.5 (2)
	0.0	500			16.5	41.5
	2.2	522			-	-



Vishay Roederstein

U _{RDC}	CAP.	CAPACITANCE	VOLTAGE		DIMEN	ISIONS
(V)	(μ F)	CODE	CODE	V _{AC}	D	L
	0.00047	147			5.0	11.0
	0.00068	168			5.0	11.0
	0.0010	210			5.0	11.0
	0.0015	215			5.0	11.0
	0.0022	222			5.0	11.0
	0.0033	233			5.0	11.0
	0.0047	247			5.0	11.0
	0.0068	268			6.0	14.0
	0.010	310			6.0	14.0
	0.015	315			6.5	14.0
	0.022	322			7.5	14.0
	0.033	333			6.5	19.0
630	0.047	347	63 ⁽¹⁾	220	7.5	19.0
030	0.068	368	03 (1)	220	8.5	19.0
	0.10	410			10.5	19.0
	0.10	410			9.5	19.0 ⁽²⁾
	0.15	415			10.0	26.5
	0.22	422			11.5	26.5
	0.22	422			-	-
	0.33	433			13.5	26.5
	0.55	433			-	-
	0.47	447			14.5	31.5
	0.47	447		14.0	26.5 ⁽²⁾	
	0.68	468		14.5	41.5	
	0.00	400			-	-
	1.0	510			16.5	41.5
	0.0010	210			5.5	14.0
	0.0015	215			6.0	14.0
	0.0022	222			6.0	14.0
	0.0033	233			7.0	14.0
	0.0047	247			6.0	19.0
	0.0068	268			6.0	19.0
	0.010	310			6.5	19.0
	0.015	315			7.5	19.0
	0.022	322			9.0	19.0
	0.033	333			10.5	19.0
1000	0.047	347	10 (1)	220	12.0	19.0
	0.068	368			11.0	26.5
	0.10	410			13.0	26.5
	0.15	415			13.5	31.5
	0.22	422			16.0	31.5
	3.22				-	-
	0.33	433			16.0	41.5
					19.0	41.5
	0.47	447			-	-

Notes

- Pitch = L + 3.5
- (1) Not suitable for mains applications
- (2) For the smaller size please add "-M" at the end of the type designation (e.g. MKT1813-510/255-M)



Vishay Roederstein

RECOMMENDED PACKAGING						
PACKAGING CODE	TYPE OF PACKAGING	REEL DIAMETER (mm)	ORDERING CODE EXAMPLES			
G	Ammo	=	MKT1813-422-014-G	х		
R	Reel	350	MKT1813-422-014-R	х		
-	Bulk	-	MKT1813-422-014	х		

Note

• Attention: Capacitors with L > 31.5 mm only as bulk available

EXAMPLE OF ORDERING CODE					
TYPE	CAPACITANCE CODE	VOLTAGE CODE	TOLERANCE CODE (1)	PACKAGING CODE	
MKT1813	410	06	5	G	

Note

(1) Tolerance codes: 4 = 5 % (J); 5 = 10 % (K); 6 = 20 % (M)

MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to packaging information: www.vishav.com/doc?28139 or end of catalog.

Specific Method of Mounting to Withstand Vibration and Shock


In order to withstand vibration and shock tests, it must be ensured that the capacitor body is in good contact with the printed-circuit board:

- For $L \le 19$ mm capacitors shall be mechanically fixed by the leads.
- For larger pitches the capacitors shall be mounted in the same way and the body clamped.
- The maximum diameter and length of the capacitors are specified in the "Dimensions" table.
- · Eccentricity as shown in the drawing below.

Space Requirements on Printed-Circuit Board

The maximum length and width of film capacitors is shown in the drawing:

- Eccentricity as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.
- Product height with seating plane as given by "IEC 60717" as reference: h_{max.} ≤ h + 0.4 mm or h_{max.} ≤ h' + 0.4 mm



Storage Temperature

T_{sta} = - 25 °C to + 35 °C with RH maximum 75 % without condensation

Ratings and Characteristics Reference Conditions


Unless otherwise specified, all electrical values apply to an ambient temperature of 23 °C \pm 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % \pm 2 %.


For reference testing, a conditioning period shall be applied over 96 h \pm 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.





CHARACTERISTICS


PERMISSIBLE AC VOLTAGE VS. FREQUENCY



















CHARACTERISTICS




Nominal voltage (AC and DC) as a function of temperature $U=f(T_A),\,T_{LL}\leq T_A\leq T_{UL}$




Capacitance as function of frequency $\Delta C/C = f(f)$, 100 Hz $\leq f \leq$ 1 MHz




Insulation resistance as a function of temperature $R_{is} = f(T_A), \ T_{LL} \leq T_A \leq T_{UL}$



Capacitance as a function of temperature $\Delta C/C = f(T_A), \ T_{LL} \leq T_A \leq T_{UL}$




Dissipation factor as function of temperature $\Delta tan \ \delta / tan \ \delta = f(T_A), \ T_{LL} \le T_A \le T_{UL}$



Dissipation factor as a function of frequency $\Delta \tan \delta / \tan \delta = f(f)$, 100 Hz $\leq f \leq 1$ MHz_L



CHARACTERISTICS



Maximum allowed component temperature rise (ΔT) as a function of the ambient temperature (T_{amb})

D _{max} .	HEAT CONDUCTIVITY (mW/°C)							
(mm)	L = 11 mm	L = 14 mm	L = 19 mm	L = 26.5 mm	L = 31.5 mm	L = 41.5 mm		
5.0	2	-	-	=	-	-		
5.5	2	3	-	-	-	-		
6.0	-	3	4	=	-	-		
6.5	-	3	5	-	-	-		
7.0	-	4	5	-	-	-		
7.5	-	-	6	-	-	-		
8.0	-	4	-	8	-	-		
8.5	-	-	6	9	-	-		
9.0	-	-	7	-	-	-		
9.5	-	-	-	10	-	-		
10.0	-	-	-	11	-	-		
10.5	-	-	8	-	-	-		
11.0	-	-	-	12	14	-		
11.5	-	-	-	13	15	-		
12.0	-	-	9	-	16	-		
12.5	-	-	-	-	-	-		
13.0	-	-	-	14	17	-		
13.5	-	-	-	15	18	-		
14.0	-	-	-	16	19	-		
14.5	-	-	-	-	19	-		
15.0	-	-	-	-	-	-		
15.5	-	-	-	-	21	-		
16.0	-	-	-	-	-	29		
16.5	-	-	-	-	22	30		
17.0	-	-	-	-	-	-		
17.5	-	-	-	-	-	31		
18.0	-	-	-	-	24	-		
18.5	-	-	-	-	-	-		
19.0	-	-	-	-	-	34		
20.0	-	-	-	-	-	-		
20.5	-	-	-	-	28	-		
21.0	_	_	_	_	-	38		

Vishay Roederstein

POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free ambient temperature.


The power dissipation can be calculated according type detail specification "HQN-384-01/101: Technical Information Film Capacitors".

The component temperature rise (ΔT) can be measured (see section "Measuring the component temperature" for more details) or calculated by $\Delta T = P/G$:

- ΔT = Component temperature rise (°C)
- P = Power dissipation of the component (mW)
- G = Heat conductivity of the component (mW/°C)

MEASURING THE COMPONENT TEMPERATURE

A thermocouple must be attached to the capacitor body as in:



The temperature is measured in unloaded (T_{amb}) and maximum loaded condition (T_C).

The temperature rise is given by $\Delta T = T_C - T_{amb}$.

To avoid radiation or convection, the capacitor should be tested in a wind-free box.

APPLICATION NOTE AND LIMITING CONDITIONS

These capacitors are not suitable for mains applications as across-the-line capacitors without additional protection, as described hereunder. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

To select the capacitor for a certain application, the following conditions must be checked:

- 1. The peak voltage (U_P) shall not be greater than the rated DC voltage (U_{RDC})
- 2. The peak-to-peak voltage (U_{P-P}) shall not be greater than $2\sqrt{2} \times U_{RAC}$ to avoid the ionization inception level
- 3. The voltage peak slope (dU/dt) shall not exceed the rated voltage pulse slope in an RC-circuit at rated voltage and without ringing. If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by URdc and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_{0}^{T} \left(\frac{dU}{dt}\right)^{2} \times dt < U_{RDC} \times \left(\frac{dU}{dt}\right)_{rated}$$

T is the pulse duration.

The rated voltage pulse slope is valid for ambient temperatures up to 85 °C. For higher temperatures a derating factor of 3 % per K shall be applied.

- 4. The maximum component surface temperature rise must be lower than the limits (see figure "Max. allowed component temperature rise").
- 5. Since in circuits used at voltages over 280 V peak-to-peak the risk for an intrinsically active flammability after a capacitor breakdown (short circuit) increases, it is recommended that the power to the component is limited to 100 times the values mentioned in the table "Heat Conductivity".
- 6. When using these capacitors as across-the-line capacitor in the input filter for mains applications or as series connected with an impedance to the mains the applicant must guarantee that the following conditions are fulfilled in any case (spikes and surge voltages from the mains included).



www.vishay.com Vishay Roederstein

VOLTAGE CONDITIONS FOR 6 ABOVE					
ALLOWED VOLTAGES	T _{amb} ≤ 85 °C	85 °C < T _{amb} ≤ 100 °C			
Maximum continuous RMS voltage	U _{RAC}	0.8 x U _{RAC}			
Maximum temperature RMS-overvoltage (< 24 h)	1.25 x U _{RAC}	U _{RAC}			
Maximum peak voltage (V _{O-P}) (< 2 s)	1.6 x U _{RDC}	1.3 x U _{RDC}			

Example

C = 3300 nF - 100 V used for the voltage signal shown in next figure.


 $U_{P-P} = 80 \text{ V}$; $U_P = 70 \text{ V}$; $T_1 = 0.5 \text{ ms}$; $T_2 = 1 \text{ ms}$

The ambient temperature is 35 °C

Checking conditions:

- 1. The peak voltage $U_P = 70 \text{ V}$ is lower than 100 V_{DC}
- 2. The peak-to-peak voltage 80 V is lower than $2\sqrt{2}$ x 63 V_{AC} = 178 U_{P-P}
- 3. The voltage pulse slope (dU/dt) = $80 \text{ V}/500 \,\mu\text{s} = 0.16 \,\text{V}/\mu\text{s}$ This is lower than $8 \,\text{V}/\mu\text{s}$ (see "Specific Reference Data" for each version)
- 4. The dissipated power is 60 mW as calculated with fourier terms
 The temperature rise for W_{max.} = 11.5 mm and pitch = 26.5 mm will be 60 mW/13 mW/°C = 4.6 °C
 This is lower than 15 °C temperature rise at 35 °C, according figure "Maximum allowed component temperature rise"
- 5. Not applicable
- 6. Not applicable

Voltage Signal





Vishay Roederstein

INSPECTION REQUIREMENTS

General Notes

Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 60384-2 and Specific Reference Data".

SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1		
4.1 Dimensions (detail)		As specified in Chapters "General data" of this specification
4.3.1 Initial measurements	Capacitance Tangent of loss angle: For $C \le 470$ nF at 100 kHz or for $C > 470$ nF at 10 kHz	
4.3 Robustness of terminations	Tensile: Load 10 N; 10 s Bending: Load 5 N; 4 x 90°	No visible damage
4.4 Resistance to soldering heat	Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s	
4.14 Component solvent resistance	Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: Min. 1 h, max. 2 h	
4.4.2 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 2$ % of the value measured initial
	Tangent of loss angle	Increase of tan δ ≤ 0.005 for: $C \leq 100$ nF or ≤ 0.010 for: 100 nF $< C \leq 220$ nF or ≤ 0.015 for: 220 nF $< C \leq 470$ nF and ≤ 0.003 for: $C > 470$ nF Compared to values measured in 4.3.1
SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1		
4.6.1 Initial measurements	Capacitance Tangent of loss angle: For C ≤ 470 nF at 100 kHz or for C > 470 nF at 10 kHz	
4.6 Rapid change of temperature	θA = - 55 °C θB = + 100 °C 5 cycles Duration t = 30 min	
	Visual examination	No visible damage
4.7 Vibration	Mounting: See section "Mounting" of this specification Procedure B4 Frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s² (whichever is less severe) Total duration 6 h	
4.7.2 Final inspection	Visual examination	No visible damage



SUB-CI	LAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GI	ROUP C1B PART OF SAMPLE	CONSTITUTE	
OF SUE 4.9	Shock	Mounting: See section "Mounting" of this specification Pulse shape: Half sine Acceleration: 490 m/s² Duration of pulse: 11 ms	
4.9.3	Final measurements	Visual examination	No visible damage
		Capacitance	$ \Delta C/C \le 3$ % of the value measured in 4.6
		Tangent of loss angle	Increase of tan δ ≤ 0.005 for: $C \leq 100$ nF or ≤ 0.010 for: 100 nF $< C \leq 220$ nF or ≤ 0.015 for: 220 nF $< C \leq 470$ nF and ≤ 0.003 for: $C > 470$ nF Compared to values measured in 4.6.1
		Insulation resistance	As specified in section "Insulation Resistance" of this specification
	ROUP C1 COMBINED SAMPLE CIMENS OF SUB-GROUPS ID C1B		
4.10	Climatic sequence		
4.10.2	Dry heat	Temperature: + 100 °C Duration: 16 h	
4.10.3	Damp heat cyclic Test Db, first cycle		
4.10.4	Cold	Temperature: - 55 °C Duration: 2 h	
4.10.6	Damp heat cyclic Test Db, remaining cycles		
4.10.6.2	Prinal measurements	Voltage proof = U _{RDC} for 1 min within 15 min after removal from testchamber	No breakdown of flash-over
		Visual examination	No visible damage Legible marking
		Capacitance	$\left \Delta C/C\right \leq 5$ % of the value measured in 4.4.2 or 4.9.3
		Tangent of loss angle	Increase of $\tan\delta$ ≤ 0.007 for: $C \leq 100$ nF or ≤ 0.010 for: 100 nF < $C \leq 220$ nF or ≤ 0.015 for: 220 nF < $C \leq 470$ nF and ≤ 0.005 for: $C > 470$ nF Compared to values measured in 4.3.1 or $4.6.1$
		Insulation resistance	≥ 50 % of values specified in section "Insulation resistance" of this specification
SUB-GI	ROUP C2		·
4.11	Damp heat steady state	56 days, 40 °C, 90 % to 95 % RH	
4.11.1	Initial measurements	Capacitance Tangent of loss angle at 1 kHz	



SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
	CONDITIONS	PERFORMANCE REQUIREMENTS
4.11.3 Final measurements	Wallian and Hardenia Milata at the	No level de la Contraction
	Voltage proof = U _{RDC} for 1 min within 15 min after removal from testchamber	No breakdown of flash-over
	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 5$ % of the value measured in 4.11.
	Tangent of loss angle	Increase of tan $\delta \le 0.005$ Compared to values measured in 4.11.1
	Insulation resistance	≥ 50 % of values specified in section "Insulation resistance" of this specification
SUB-GROUP C3		
4.12 Endurance	Duration: 2000 h 1.25 x U _{RDC} at 85 °C 1.0 x U _{RDC} at 100 °C	
4.12.1 Initial measurements	Capacitance Tangent of loss angle: For C ≤ 470 nF at 100 kHz or for C > 470 nF at 10 kHz	
4.12.5 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 5$ % compared to values measured in 4.12.1
	Tangent of loss angle	$\begin{array}{l} \text{Increase of } \tan \delta \\ \leq 0.005 \text{ for: } C \leq 100 \text{ nF or} \\ \leq 0.010 \text{ for: } 100 \text{ nF < C} \leq 220 \text{ nF or} \\ \leq 0.015 \text{ for: } 220 \text{ nF < C} \leq 470 \text{ nF and} \\ \leq 0.003 \text{ for: } C > 470 \text{ nF} \\ \text{Compared to values measured in } 4.12.1 \end{array}$
	Insulation resistance	≥ 50 % of values specified in section "Insulation resistance" of this specification
SUB-GROUP C4		
4.13 Charge and discharge	10 000 cycles Charged to U_{RDC} Discharge resistance: $R = \frac{U_R}{C \times 2.5 \times (dU/dt)_R}$	
4.13.1 Initial measurements	Capacitance Tangent of loss angle: For C ≤ 470 nF at 100 kHz or for C > 470 nF at 10 kHz	
4.13.3 Final measurements	Capacitance	$ \Delta C/C \le 3$ % compared to values measured in 4.13.1
	Tangent of loss angle	Increase of $\tan \delta$ ≤ 0.005 for: $C \leq 100$ nF or ≤ 0.010 for: 100 nF < $C \leq 220$ nF or ≤ 0.015 for: 220 nF < $C \leq 470$ nF and ≤ 0.003 for: $C > 470$ nF Compared to values measured in 4.13.1
	Insulation resistance	≥ 50 % of values specified in section "Insulation resistance" of this specification



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

 MKT1813610014-25R
 MKT1813447405
 MKT1813510255R
 MKT1813368635G
 MKT1813410635G

 MKT1813368405
 MKT1813510065
 MKT1813610015
 MKT1813233635G
 MKT1813410405R
 MKT1813347405G

 MKT1813447255G
 MKT1813510065G
 MKT1813368014R
 MKT1813568255G
 MKT1813322405G
 MKT18131147635

 MKT1813322635G
 MKT1813610065G
 MKT1813468405
 MKT1813433015
 MKT1813310405G
 MKT1813533065

 MKT1813347255G
 MKT1813347405
 MKT1813433065
 MKT1813510405G
 MKT1813268635G
 MKT1813322405

 MKT1813422405
 MKT1813533255
 MKT1813468065
 MKT1813547255G
 MKT1813347635G

 MKT181340405G
 MKT1813447405G
 MKT1813447405G
 MKT1813310635G
 MKT1813447065G

 MKT1813410405G
 MKT181334547065
 MKT1813547065G
 MKT1813547065G
 MKT1813410406
 MKT1813422405G

 MKT1813515065
 MKT18133210635G
 MKT18132247635G
 MKT1813410406
 MKT1813422265G

 MKT1813315255
 MKT1813415635G
 MKT1813433405
 MKT1813515255
 MKT1813415405M

 MKT18133433405
 MKT181343330405
 MKT18134333014