

# Standard break stem blind rivets


Domed head



## Material

Body: Aluminum, 3.5% magnesium

Mandrel: Steel galvanized



3-D Data: <http://kvt.partcommunity.com>

Rivet-Ø	Length nominal	Grip range	Order description	Hole size Ø				
2.4	3.5	- 0.8	TAPD 31 BS	2.5		500	400	1.42
	5.0	0.8 - 2.4	TAPD 33 BS					
	7.5	2.4 - 4.8	TAPD 36 BS					
3.0	5.0	- 2.0	SNAD 3050 BS	3.1		1000	800	1.83
	6.5	2.0 - 3.5	SNAD 3065 BS					
	8.0	3.5 - 5.0	SNAD 3080 BS					
	10.0	5.0 - 7.0	SNAD 3100 BS					
	12.0	7.0 - 9.0	SNAD 3120 BS					
3.2	4.5	- 1.6	TAPD 42 BS	3.3		1200	800	1.83
	6.0	1.6 - 3.2	TAPD 44 BS					
	8.0	3.2 - 4.8	TAPD 46 BS					
	9.7	4.8 - 6.4	TAPD 48 BS					
	11.5	6.4 - 7.9	TAPD 410 BS					
	13.5	7.9 - 9.5	TAPD 412 BS					
	15.0	9.5 - 11.1	TAPD 414 BS					
	17.0	11.1 - 12.7	TAPD 416 BS					
	18.5	12.7 - 14.3	TAPD 418 BS					
	20.0	14.3 - 16.7	TAPD 421 BS					
24.0	16.7 - 20.7	TAPD 425 BS						
4.0	7.0	- 3.2	TAPD 54 BS	4.1		1910	1330	2.29
	8.5	3.2 - 4.8	TAPD 56 BS					
	10.5	4.8 - 6.4	TAPD 58 BS					
	12.2	6.4 - 7.9	TAPD 510 BS					
	14.0	7.9 - 9.5	TAPD 512 BS					
	15.7	9.5 - 11.1	TAPD 514 BS					
	17.5	11.1 - 12.7	TAPD 516 BS					
	18.5	12.7 - 13.5	TAPD 517 BS					
	20.2	13.5 - 15.9	TAPD 520 BS					
	22.5	15.9 - 17.4	TAPD 522 BS					
	24.7	17.4 - 19.8	TAPD 525 BS					