
Vishay General Semiconductor

Miniature Glass Passivated Fast Recovery Surface Mount Bridge Rectifier



TO-269AA (MBS)

PRIMARY CHARACTERISTICS					
Package	TO-269AA (MBS)				
I _{F(AV)}	0.5 A				
V _{RRM}	200 V, 400 V, 600 V				
I _{FSM}	35 A				
I _R	5 μΑ				
V_F at $I_F = 0.4$ A	1.0 V				
T _J max.	150 °C				
Diode variations	Quad				

FEATURES

- UL recognition, file number E54214
- · Saves space on printed circuit boards
- Ideal for automated placement
- High surge current capability



- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
 KOHS COMPLIANT
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

General purpose use in AC/DC bridge full wave rectification for power supply, lighting ballaster, battery charger, home appliances, office equipment, and telecommunication applications.

MECHANICAL DATA

Case: TO-269AA (MBS)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: As marked on body

MAXIMUM RATINGS (T_A = 25 °C unless otherwise noted) PARAMETER SYMBOL MB2S MB4S MB6S UNIT 2 4 6 Device marking code Maximum repetitive peak reverse voltage 200 400 600 V V_{RRM} Maximum RMS voltage 140 280 420 ٧ V_{RMS} Maximum DC blocking voltage 600 V_{DC} 200 400 V on glass-epoxy PCB (1) 0.5 Maximum average forward output I_{F(AV)} A rectified current (fig. 1) on aluminum substrate (2) 0.8 Peak forward surge current 8.3 ms single half sine-wave 35 A **I**ESM superimposed on rated load Rating for fusing (t < 8.3 ms) l²t 5.0 A²s Operating junction and storage temperature range T_J, T_{STG} - 55 to + 150 °C

Notes

 $^{(1)}\,$ On glass epoxy PCB mounted on 0.05" x 0.05" (1.3 mm x 1.3 mm) pads

(2) On aluminum substrate PCB with an area of 0.8" x 0.8" (20 mm x 20 mm) mounted on 0.05" x 0.05" (1.3 mm x 1.3 mm) solder pad

www.vishay.com



www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS	SYMBOL	MB2S	MB4S	MB6S	UNIT
Maximum instantaneous forward voltage per diode	I _F = 0.4 A	V _F		1.0		V
Maximum DC reverse current at rated DC blocking voltage per diode	T _A = 25 °C	I_	5.0		μA	
	T _A = 125 °C	IR				
Typical junction capacitance per diode	4.0 V, 1 MHz	CJ		13		pF

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)						
PARAMETER	SYMBOL	MB2S	MB4S	MB6S	UNIT	
	R _{0JA} ⁽¹⁾	85			°C/W	
Typical thermal resistance	R _{0JA} ⁽²⁾	70				
	R _{0JL} ⁽¹⁾	20				

Notes

⁽¹⁾ On glass epoxy PCB mounted on 0.05" x 0.05" (1.3 mm x 1.3 mm) pads

(2) On aluminum substrate PCB with an area of 0.8" x 0.8" (20 mm x 20 mm) mounted on 0.05" x 0.05" (1.3 mm x 1.3 mm) solder pad

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
MB2S-E3/45	0.22	45	100	Tube		
MB2S-E3/80	0.22	80	3000	13" diameter paper tape and reel		

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25$ °C unless otherwise noted)




Fig. 1 - Derating Curve for Output Rectified Current





Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Diode

Document Number: 88661

Vishay General Semiconductor



www.vishay.com

SHAY

Fig. 3 - Typical Forward Voltage Characteristics Per Diode





Fig. 4 - Typical Reverse Leakage Characteristics Per Diode

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Revision: 19-Aug-13

3

Document Number: 88661

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




Fig. 5 - Typical Junction Capacitance Per Diode



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

MB2S/45 MB2S-E3/45 MB2S-E3/80 MB4S-E3/45 MB4S-E3/80 MB6S-E3/45 MB6S-E3/80