


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT1M-186	.13 (3.3)	.87 (22)	.044 (1.1)	.098 (2.5)	.159 (4.0)	.186 (4.7)	.188 (4.8)	3.9 (100)	15 (67)	MINIATURE	CURVED	.06 (28)
PLT2I-186	.13 (3.3)	2.00 (51)	.047 (1.2)	.135 (3.4)	.200 (5.1)	.180 (4.6)	.240 (6.1)	8.0 (203)	18 (80)	INTERMEDIATE	CURVED	.18 (81)
PLT2S-186	.13 (3.3)	1.85 (47)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	7.30 (186)	30 (133)	STANDARD	CURVED	.30 (138)
PLT3S-186	.13 (3.3)	3.00 (76)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	11.50 (291)	30 (133)	STANDARD	CURVED	.47 (213)
PLT4S-186	.13 (3.3)	4.00 (102)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	14.40 (366)	30 (133)	STANDARD	CURVED	.60 (274)
PLT3H-186	.25 (6.4)	3.00 (76)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	11.10 (282)	60 (267)	LIGHT-HEAVY	STRAIGHT	.99 (448)
PLT4H-186	.25 (6.4)	4.00 (102)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	14.40 (366)	60 (267)	LIGHT-HEAVY	STRAIGHT	1.20 (544)

NOTES:

- \*1) SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.
- 2) COMPOSED OF METAL DETECTABLE POLYPROPYLENE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	MATERIAL:	DRAWING NUMBER:
							PAN-TY CABLE TIES PLT METAL DETECTABLE POLYPROPYLENE SERIES CUSTOMER DRAWING	W10001CI/01	W10001CI-DC/01 - SS-27604_REV01	METAL DETECTABLE POLYPROPYLENE COLOR: BLUE	SS-27604
01	11/21/16	BWG	MPH	JADE	REVISED CHART AND UPDATED TITLE BORDER. SEE ECN DOCUMENT FOR COMPLETE DETAILS.	011038/01					
R	8/18/08	ERW			DRAWING RELEASED	27604/R					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± ----- .xxx ± .020 (.51) .xx ± .02 (.5) ANGLES ± -----				
							THIRD ANGLE PROJECTION				
							DRAWN BY: ERW DATE: 8/18/08 CHK: NONE SCALE: NONE				SHT 1 OF 1

D10100DA/20

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLT1M-C186](#) [PLT3H-L186](#) [PLT3S-C186](#)