



PANDUIT* PART #	BUNDLE DIA.		A IN (mm)	B IN (mm)	C IN (mm)	D IN (mm)	E IN (mm)	F IN (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs. (g) / 100 pcs.
	MIN. IN (mm)	MAX. IN (mm)										
PLT1M-M39	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	18 (80)	MINIATURE	CURVED	.07 (32)

**NOTES:**  
SEE [www.panduit.com](http://www.panduit.com) FOR ANY THIRD PARTY CERTIFICATION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE PAN-TY CABLE TIE - PLT SERIES						
							CUSTOMER DRAWING						
							ITEM REVISION NAME 00162NBS/00						
							DATASET FILE NAME 00162NBS_DC/00 - 00162NBS_DC_REV00						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± --- .xxx ± .020 (.51) .xx ± .02 (.5) ANGLES ± ---						
							MATERIAL: NATURAL HEAT STABILIZED NYLON 6.6						
							DRAWING NUMBER: 00162NBS_DC						
00	9/26/18	BWG	MPH	JADE	DRAWING RELEASED.		041349/00						
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY BWG	DATE 9/26/18	CHK MPH	SCALE NONE	SHT 1 OF 1	SIZE A

D10100DX/16

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLT1M-M120](#) [PLT1M-M39](#)