15 Rcpt Solder Cup, Gold Flash ACTIVE



AMPLIMITE

TE Part # 5-747909-2 TE Internal #: 5-747909-2

View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Connectors > Solder D-Sub Connectors











Connector Style: Receptacle

Connector System: Cable-to-Board

Number of Positions: 15

Contact Size: 20 Shell Size: 2

Features

Product Type Features

Grade	Standard
Grounding Indents	Without
Product Type	Connector
Shell Type	Full Metal Shell
Connector Style	Receptacle
Connector System	Cable-to-Board
Shell Size	2
Shielded	Yes
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Configuration Features	
Preloaded	Yes
Number of Positions	15
Body Features	

Steel

Shell Material



Color	Black
Insert Material	Thermoplastic
Shell Plating Material	Tin
Contact Features	
Contact Type	Socket
	.8 μin
Contact Mating Area Plating Material	Gold Flash
Contact Underplating Material	Nickel
Contact Configuration	Solder Cup
PCB Contact Termination Area Plating Material	Tin-Copper
Contact Base Material	Phosphor Bronze
Contact Size	20
Contact Current Rating (Max)	3 A
Termination Features	
Termination Method to Wire & Cable	Solder
Mechanical Attachment	
Mounting Angle	Straight
PCB Mount Retention Type	None
Mating Connector Lock	With
Mating Connector Lock Type	Mounting Holes
Connector Mounting Type	Board Mount
Housing Features	
Enclosure	Without
Centerline (Pitch)	2.77 mm[.11 in]
Dimensions	
Wire Size	.5 – .6 mm²
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Insert Flammability Rating	UL 94V-0

TE Part # 5-747909-2 TE Internal #: 5-747909-2



UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought









TE Part # 5-747909-2 TE Internal #: 5-747909-2





TE Part #5748676-1
DIE CAST CBL CLMP KIT,
SZ 1



TE Part #5205817-3
FEMALE SCREWLOCK KIT



TE Part #5205817-1
KIT SCREWLOCK FEMALE





TE Part #1658670-2 PIN CONTACT,22-28 AWG, 22 DF, AMPLIMITE



Documents

Product Drawings

15 Rcpt Solder Cup, Gold Flash

English

CAD Files

Customer View Model

ENG_CVM_CVM_5-747909-2_V.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-747909-2_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-747909-2_V.3d_stp.zip

English

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

Product Specifications

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English

15 Rcpt Solder Cup, Gold Flash

TE Part # 5-747909-2 TE Internal #: 5-747909-2



Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English

UL Report

English