

## Starrett Carbide Tipped Deep Cut Hole saw (CTD)



**Diameters – 15mm to 100mm**

**Kit availability –**

KCT08001 (16mm, 20mm, 22mm, 25mm, 32mm, 40mm, 51mm, 64mm)

KCT07001 (16mm, 20mm, 22mm, 25mm, 32mm, 40mm, 50mm)

### **Description**

The perfect solution for repeated intense drilling in mild and stainless steel, cast iron, aluminium and copper of all thicknesses up to 25mm (1"). Featuring three different angles ground on to the cutting face of each tooth on the saw. This 3-Ply tooth grind delivers a fast cut, minimal snag when the saw begins the cut, efficient swarf removal minimising heat build up and maximum saw life.

### **Advantages**

- 3-Ply tooth grind on each tooth delivers maximum performance and makes the saw much more robust than 2-Ply equivalents
- Supplied as one piece with no need for assembly
- Ejector spring to aid ejection of the core from the saw.