Single and Quad Low Voltage, Rail-to-Rail Operational Amplifiers

The LMV821 and LMV824 are operational amplifiers with low input voltage offset and drift vs. temperature. In spite of low quiescent current requirements these devices have 5 MHz bandwidth and 1.4 V/µs slew rate. In addition they provide rail–to–rail output swing into 600 Ω loads. The input common–mode voltage range includes ground, and the maximum input offset voltage is only 3.5 mV. Substantially large capacitive loads can be driven by simply adding a pullup resistor or isolation resistor.

The LMV821 (single) is available in a space–saving SC70–5 while the quad comes in SOIC and TSSOP packages.

Features


- Low Offset Voltage: 3.5 mV
- Very low Offset Drift: 1.0 µV/°C
- High Bandwidth: 5 MHz
- Rail-to-Rail Output Swing into a 600 Ω load
- Capable of driving highly capacitive loads
- Small Packages:
 - LMV821 in SC-70

LMV824 in SOIC-14 and TSSOP-14

• These Devices are Pb-Free and are RoHS Compliant

Typical Applications


- Notebook Computers
- PDAs
- Modem Transmitter/ Receivers





ON Semiconductor®


www.onsemi.com




TSSOP-14 CASE 948G

ORDERING AND MARKING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 2 of this data sheet.




MARKING DIAGRAMS



SOIC-14						
14 .	Ħ	Ħ	A	A	A	A
	L	M	/82	240	3	
0	A	١W	LY۱	٨٧	V	
_1₩	H	ß	H	H	H	H

LMV824	= Specific Device Code
А	= Assembly Location
WL	= Wafer Lot
Y	= Year
WW	= Work Week
G	= Pb-Free Package




= Assembly Location А L = Wafer Lot Y = Year = Work Week W • = Pb-Free Package

(Note: Microdot may be in either location)


PIN CONNECTIONS

IN B-


SC70-5



SOIC-14







ORDERING INFORMATION

Order Number	Number of Channels	Specific Device Marking	Package Type	Shipping [†]
LMV821SQ3T2G	Single	AAE	SC–70 (Pb–Free)	3000 / Tape & Reel
LMV824DR2G	Quad	LMV824	SOIC-14 (Pb-Free)	2500 / Tape & Reel
LMV824DTBR2G	Quad	LMV 824	TSSOP-14 (Pb-Free)	2500 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MAXIMUM RATINGS

Symbol	Rating	Value	Unit
VS	Supply Voltage (Operating Range $V_S = 2.7 V$ to 5.5 V)	5.5	V
V _{IDR}	Input Differential Voltage	\pm Supply Voltage	V
V _{ICR}	Input Common Mode Voltage Range	–0.5 to (V+) +0.5	V
	Maximum Input Current	10	mA
t _{SO}	Output Short Circuit (Note 1)	Continuous	
TJ	Maximum Junction Temperature (Operating Range –40°C to 85°C)	150	°C
θ_{JA}	Thermal Resistance		°C/W
	SC-70	280	
	SOIC-14	156	
	TSSOP-14	190	
T _{STG}	Storage Temperature	-65 to 150	°C
	Mounting Temperature (Infrared or Convection – 20 sec)	235	°C
V _{ESD}	ESD Tolerance Machine Model Human Body Model	200 2000	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.
 Continuous short-circuit operation to ground at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Output currents in excess of 45 mA over long term may adversely affect reliability. Shorting output to either V+ or V- will adversely affect reliability.

2.7V DC ELECTRICAL CHARACTERISTICS Unless otherwise noted, all min/max limits are guaranteed for $T_A = 25^{\circ}$ C, V+ = 2.7 V, V- = 0 V, V_{CM} = V+/2, V_O = V+/2 and R_L > 1 M Ω . Typical specifications represent the most likely parametric norm. Min/Max specifications are guaranteed by testing, characterization, or statistical analysis.

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Input Offset Voltage	V _{IO}			1	3.5	mV
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			4	
Input Offset Voltage Average Drift	TCV _{OS}			1		μV/°C
Input Bias Current	I _B			105	210	nA
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			315	
Input Offset Current	I _{IO}			0.5	30	nA
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			50	
Common–Mode Rejection	CMRR	$0 \text{ V} \leq \text{V}_{\text{CM}} \leq 1.7 \text{ V}$	70	85		dB
Ratio		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	68			
Power Supply Rejection Ratio	PSRR	$\begin{array}{l} 1.5 \; V \leq V + \leq 4 \; V, V - = -1 \; V, \; V_{O} = 0 \; V, \\ V_{CM} = 0.0 \; V \end{array}$	75	85		dB
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	70			
Input Common–Mode Voltage Range	V _{CM}	For CMRR \ge 53 dB and T _A = -40°C to +85°C	-0.2	-0.3 to 2.0	1.9	V
Large Signal Voltage Gain	AV	$\rm R_L$ = 600 $\Omega,~\rm V_O$ = 0.5 V to 2.5 V	80	95		dB
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	70]
		R_L = 2 kΩ, V_O = 0.5 V to 2.5 V	83	89		
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	80			
Output Swing	V _{OH}	R_L = 600 Ω to 1.35 V	2.5	2.58		V
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	2.4			
	V _{OL}	R_L = 600 Ω to 1.35 V		0.13	0.21	
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.3	
	V _{OH}	$R_L = 2 \ k\Omega$ to 1.35 V	2.6	2.66		
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	2.5			
	V _{OL}	$R_L = 2 k\Omega$ to 1.35 V		0.08	0.12	
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.2	
Output Current	Ι _Ο	Sourcing, $V_O = 0 V$	12			mA
		Sinking, $V_0 = 2.7 V$	12	26		
Supply Current	I _{CC}	LMV821 (Single)		0.242	0.3	mA
	[$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.5]
	[LMV824 (All Four Channels)		1	1.3]
	[$T_A = -40^{\circ}C$ to $+85^{\circ}C$			1.5	

2.5V DC ELECTRICAL CHARACTERISTICS Unless otherwise noted, all min/max limits are guaranteed for T _A = 25°C, V+ = 2.5 V,
V- = 0 V, V _{CM} = V+/2, V _O = V+/2 and R _L > 1 M Ω . Typical specifications represent the most likely parametric norm. Min/Max
specifications are guaranteed by testing, characterization, or statistical analysis.

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Input Offset Voltage	V _{IO}	$T_A = -40^{\circ}C$ to $+85^{\circ}C$		1	3.5	mV
					4	
Output Swing	V _{OH}	$\rm R_L$ = 600 Ω to 1.25 V	2.3	2.37		V
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	2.2			
	V _{OL}	$\rm R_L$ = 600 Ω to 1.25 V		0.13	0.20	
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.3	
	V _{OH}	$R_L = 2 \text{ k}\Omega \text{ to } 1.25 \text{ V}$	2.4	2.46		
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	2.3			
	V _{OL}	$R_L = 2 k\Omega$ to 1.25 V		0.08	0.12	
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	1		0.20	1

2.7V AC ELECTRICAL CHARACTERISTICS Unless otherwise specified, all limits are guaranteed for $T_A = 25^{\circ}C$, V+ = 2.7 V, V- = 0 V, V_{CM} = 1.0 V, V_O = V+/2 and RL > 1 M Ω . Typical specifications represent the most likely parametric norm. Min/Max specifications are guaranteed by testing, characterization, or statistical analysis.

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Slew Rate	SR	(Note 2)		1.5		V/uS
Gain Bandwidth Product	GBWP			5		MHz
Phase Margin	$\theta_{\sf m}$			55		0
Gain Margin	G _m			12.9		dB
Input–Referred Voltage Noise	e _n	$f = 1 \text{ kHz}, \text{ V}_{CM} = 1 \text{ V}$		12		nV/√Hz
Input–Referred Current Noise	i _n	f = 1kHz		0.2		pA/√Hz
Total Harmonic Distortion	THD	f = 1 kHz, AV = –2, R_L = 10 $k\Omega$, V_O = 1.8 V_{PP}		0.023		%
Amplifier-to-Amplifier Isolation		(Note 3)		135		dB

Connected as voltage follower with input step from 0.5 V to 1.5 V. Number specified is the average of the positive and negative slew rates.
 Input referred, R_L = 100 kΩ connected to V+/2. Each amp excited in turn with 1kHz to produce V_O = 3 V_{PP}. For Supply Voltages < 3 V, V_O = V+.

5V DC ELECTRICAL CHARACTERISTICS Unless otherwise noted, all min/max limits are guaranteed for $T_A = 25^{\circ}C$, V+ = 5 V,V- = 0 V, VCM = V+/2, V_O = V+/2 and R_L > 1 M Ω . Typical specifications represent the most likely parametric norm. Min/Max specifications are guaranteed by testing, characterization, or statistical analysis.


Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Input Offset Voltage	V _{IO}			1	3.5	mV
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			4	
Input Offset Voltage Average Drift	TCV _{OS}			1		μV/°C
Input Bias Current	Ι _Β			119	245	nA
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			380	
Input Offset Current	I _{IO}			0.5	30	nA
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			50	
Common–Mode Rejection	CMRR	$0~V~\leq~V_{CM}~\leq~4.0~V$	72	90		dB
Ratio		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	70			
Power Supply Rejection Ratio	PSRR	$\begin{array}{l} 1.7 \; V \leq V + \leq 4 \; V \! , V - = 1 \; V \! , V_{O} = 0 \; V \! , \\ V_{CM} = 0.0 \; V \end{array}$	75	85		dB
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	70			
Input Common–Mode Voltage Range	V _{CM}	For CMRR \ge 58 dB and T _A = - 40°C to +85°C	-0.2	-0.2 to 4.3	4.2	V
Large Signal Voltage Gain	A _V	$R_L = 600 \ \Omega$, $V_O = 1.0 \ V$ to 4.0 V	87	100		dB
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	73			
		R_L = 2 kΩ, V_O = 1.0 V to 4.0 V	84	99		
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	82			
Output Swing	V _{OH}	${\sf R}_{\sf L}$ = 600 Ω to 2.5 V	4.75	4.84		V
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	4.7			
	V _{OL}	${\sf R}_{\sf L}$ = 600 Ω to 2.5 V		0.17	0.33	
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.4	
	V _{OH}	RL = 2 k Ω to 2.5 V	4.85	4.9		
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	4.8			
	V _{OL}	$R_L = 2 \ k\Omega$ to 2.5 V		0.1	0.15	
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.2	
Output Current	Ι _Ο	Sourcing, Vo = 0 V	20	45		mA
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	10			
		Sinking, Vo = 5 V	20	40		
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$	15			
Supply Current	I _{CC}			0.3	0.4	mA
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.6	1
		LMV822 (Both Applications)		0.5	0.7	1
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$			0.9	1
		LMV824 (All Four Applications)		1	1.3	1
		$T_A = -40^{\circ}C$ to $+85^{\circ}C$		1	1.5	1

5V AC ELECTRICAL CHARACTERISTICS Unless otherwise specified, all limits are guaranteed for $T_A = 25^{\circ}C$, V+ = 5 V, V- = 0 V, V_{CM} = 2.0 V, V_{O} = V+/2 and R_{L} > 1 M Ω . Typical specifications represent the most likely parametric norm. Min/Max specifications are guaranteed by testing, characterization, or statistical analysis.

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Slew Rate	SR	(Note 4)		2		V/μS
Gain Bandwidth Product	GBWP			5.6		MHz
Phase Margin	θ_{m}			63		0
Gain Margin	G _m			11.7		dB
Input–Referred Voltage Noise	e _n	f = 1 kHz, V _{CM} = 1 V		11		nV/√Hz
Input–Referred Current Noise	i _n	f = 1 kHz		0.21		pA/√ Hz
Total Harmonic Distortion	THD	f = 1 kHz, A_V = -2, R_L = 10 k\Omega , V_O = 4.11 VPP		0.012		%
Amplifier-to-Amplifier Isolation		(Note 5)		135		dB

4. Connected as voltage follower with input step from 0.5 V to 3.5 V. Number specified is the average of the positive and negative slew rates. 5. Input referred, $R_L = 100 \text{ k}\Omega$ connected to V+/2. Each amp excited in turn with 1 kHz to produce $V_O = 3 V_{PP}$. (For Supply Voltages < 3 V, $\dot{V_0} = V+$).

TYPICAL PERFORMANCE CHARACTERISTICS



TYPICAL PERFORMANCE CHARACTERISTICS




Figure 9. Gain vs. Frequency



Figure 10. Non–Inverting Large Signal Step Response




Figure 11. Non–Inverting Small Signal Step Response




Figure 12. Inverting Large Signal Step Response






APPLICATIONS INFORMATION













Figure 16. Comparator with Hysteresis



Given: f_o = center frequency $A(f_o)$ = gain at center frequency

Choose value f_o, C
Then: R3 =
$$\frac{Q}{\pi f_0 C}$$


R1 = $\frac{R3}{2 A(f_0)}$
R2 = $\frac{R1 R3}{4Q^2 R1 - R3}$

For less than 10% error from operational amplifier, (($Q_O f_O$)/BW) < 0.1 where f_o and BW are expressed in Hz. If source impedance varies, filter may be preceded with voltage follower buffer to stabilize filter parameters.

Figure 17. Multiple Feedback Bandpass Filter


PACKAGE DIMENSIONS


SC-88A (SC-70-5/SOT-353) CASE 419A-02 ISSUE L




- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. 419A-01 OBSOLETE. NEW STANDARD 419A-02.
 4. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

	INC	HES	MILLIM	ETERS
DIM	MIN	MAX	MIN	MAX
Α	0.071	0.087	1.80	2.20
В	0.045	0.053	1.15	1.35
С	0.031	0.043	0.80	1.10
D	0.004	0.012	0.10	0.30
G	0.026	BSC BSC	0.65 BSC	
Н		0.004		0.10
J	0.004	0.010	0.10	0.25
Κ	0.004	0.012	0.10	0.30
Ν	0.008 REF		0.20	REF
S	0.079	0.087	2.00	2.20







SOLDER FOOTPRINT



PACKAGE DIMENSIONS

SOIC-14 CASE 751A-03 ISSUE K






DETAIL A

- NOTES: 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: MILLIMETERS. 3. DIMENSION & DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE PROTRUSION SHALL BE 0.13 TOTAL IN EXCESS OF AT MAXIMUM MATERIAL CONDITION. 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD PROTRUSIONS. 5. MAXIMUM MOLD PROTRUSION 0.15 PER SIDE.

	MILLIMETERS		INC	HES
DIM	MIN	MAX	MIN	MAX
Α	1.35	1.75	0.054	0.068
A1	0.10	0.25	0.004	0.010
A3	0.19	0.25	0.008	0.010
b	0.35	0.49	0.014	0.019
D	8.55	8.75	0.337	0.344
Е	3.80	4.00	0.150	0.157
е	1.27	BSC	0.050	BSC
Н	5.80	6.20	0.228	0.244
h	0.25	0.50	0.010	0.019
L	0.40	1.25	0.016	0.049
Μ	0 °	7 °	0 °	7 °






h

X 45 °

– M




DIMENSIONS: MILLIMETERS

DETAIL A

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS



ON Semiconductor and the unarrest are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

INCHES

0.200

0.047

5.10 0.193

1.20

4.50 0.169 0.177

0.15 0.002 0.006

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: LMV824DR2G LMV824DTBR2G LMV821SQ3T2G