

## Stamp Specifications (revised 04/05)

Released Products	Rev.Dx / BS1-IC	BS2-IC	BS2e-IC	BS2sx-IC
Package	PCB w/Proto / 14-pin SIP	24-pin DIP	24-pin DIP	24-pin DIP
Package Size (L x W x H)	2.5" x 1.5" x .5" / 1.4" x .6" x .1"	1.2" x 0.6" x 0.4"	1.2" x 0.6" x 0.4"	1.2" x 0.6" x 0.4"
Environment *	0° - 70° C (32° - 158° F) **	0° - 70° C (32° - 158° F) **	0° - 70° C (32° - 158° F)	0° - 70° C (32° - 158° F)
Microcontroller	Microchip PIC16C56a	Microchip PIC16C57c	Ubicom SX28AC	Ubicom SX28AC
Processor Speed	4 MHz	20 MHz	20 MHz	50 MHz
Program Execution Speed	~2,000 instructions/sec.	~4,000 instructions/sec.	~4,000 instructions/sec.	~10,000 instructions/sec.
RAM Size	16 Bytes (2 I/O, 14 Variable)	32 Bytes (6 I/O, 26 Variable)	32 Bytes (6 I/O, 26 Variable)	32 Bytes (6 I/O, 26 Variable)
Scratch Pad RAM	N/A	N/A	64 Bytes	64 Bytes
EEPROM (Program) Size	256 Bytes, ~80 instructions	2K Bytes, ~500 instructions	8 x 2K Bytes, ~4,000 inst.	8 x 2K Bytes, ~4,000 inst.
Number of I/O pins	8	16 + 2 Dedicated Serial	16 + 2 Dedicated Serial	16 + 2 Dedicated Serial
Voltage Requirements	5 - 15 vdc	5 - 15 vdc	5 - 12 vdc	5 - 12 vdc
Current Draw @ 5V	1 mA Run / 25 µA Sleep	3 mA Run / 50 µA Sleep	25 mA Run / 200 µA Sleep	60 mA Run / 500 µA Sleep
Source / Sink Current per I/O	20 mA / 25 mA	20 mA / 25 mA	30 mA / 30 mA	30 mA / 30 mA
Source / Sink Current per unit	40 mA / 50 mA	40 mA / 50 mA per 8 I/O pins	60 mA / 60 mA per 8 I/O pins	60 mA / 60 mA per 8 I/O pins
PBASIC Commands***	32	42	45	45
PC Programming Interface	Serial (w/BS1 Serial Adapter)	Serial (9600 baud)	Serial (9600 baud)	Serial (9600 baud)
Windows Text Editor	Stampw.exe (v2.1 and up)	Stampw.exe (v1.04 and up)	Stampw.exe (v1.096 and up)	Stampw.exe (v1.091 and up)

Released Products	BS2p24-IC	BS2p40-IC	BS2pe-IC	BS2px-IC	Javelin Stamp
Package	24-pin DIP	40-pin DIP	24-pin DIP	24-pin DIP	24-pin DIP
Package Size (L x W x H)	1.2" x 0.6" x 0.4"	2.1" x 0.6" x 0.4"	1.2" x 0.6" x 0.4"	1.2" x 0.6" x 0.4"	1.24" x 0.60" x 0.45"
Environment *	0° - 70° C (32° - 158° F)	0° - 70° C (32° - 158° F)	0° - 70° C (32° - 158° F)	0° - 70° C (32° - 158° F)	0° - 70° C (32° - 158° F)
Microcontroller	Ubicom SX48AC	Ubicom SX48AC	Ubicom SX48AC	Ubicom SX48AC	Ubicom SX48AC
Processor Speed	20 MHz Turbo	20 MHz Turbo	8 MHz Turbo	32 MHz Turbo	25 MHz Turbo
Program Execution Speed	~12,000 instructions/sec.	~12,000 instructions/sec.	~6000/sec.	~19,000 instructions/sec.	~8,500 instructions/sec.
RAM Size	38 Bytes (12 I/O, 26 Variable)	38 Bytes (12 I/O, 26 Variable)	38 Bytes (12 I/O, 26 Variable)	38 Bytes (12 I/O, 26 Variable)	32768 Bytes
Scratch Pad RAM	128 Bytes	128 Bytes	128 Bytes	128 Bytes	N/A
EEPROM (Program) Size	8 x 2K Bytes, ~4,000 inst.	8 x 2K Bytes, ~4,000 inst.	16 x 2K Bytes (16 K for source)	8 x 2K Bytes, ~4,000 inst.	32768 Bytes
Number of I/O pins	16 + 2 Dedicated Serial	32 + 2 Dedicated Serial	16 + 2 Dedicated Serial	16 + 2 Dedicated Serial	16
Voltage Requirements	5 - 12 vdc	5 - 12 vdc	5 - 12 vdc	5 - 12 vdc	5 - 24 vdc
Current Draw @ 5V	40 mA Run / 350 µA Sleep	40 mA Run / 350 µA Sleep	15 mA Run / 36 µA Sleep	55 mA Run / 450 µA Sleep	80 mA Run / No Sleep
Source / Sink Current per I/O	30 mA / 30 mA	30 mA / 30 mA	30 mA / 30 mA	30 mA / 30 mA	30 mA / 30 mA
Source / Sink Current per unit	60 mA / 60 mA per 8 I/O pins	60 mA / 60 mA per 8 I/O pins	60 mA / 60 mA per 8 I/O pins	60 mA / 60 mA per 8 I/O pins	60 mA / 60 mA per 8 I/O pins
PBASIC Commands***	61	61	61	63	0 (Java)
PC Programming Interface	Serial (9600 baud)	Serial (9600 baud)	Serial (9600 baud)	Serial (19200 baud)	Serial (28800 baud)
Windows Text Editor	Stampw.exe (v1.1 and up)	Stampw.exe (v1.1 and up)	Stampw.exe (v1.33 and up)	Stampw.exe (v2.2 and up)	Javelin Stamp IDE

\* 70% Non-Condensing Humidity

\*\* Industrial Models Available, -40° - 85° C (-40° - 185° F). Contact Parallax Sales for information.

\*\*\* Using PBASIC 2.5 for BS2-type models.