

# AP851 50 Watts TO-220 High Power Resistors



A high power TO-220 style resistor package designed for high frequency emitter circuits in switching power supplies. Also used in voltage regulation and low energy pulse loading.

- 50 Watts at 25°C case temperature on heat sink
- Single screw mounting to heat sink
- Moulded case for protection and easy to mount
- Non-inductive design
- Electrically isolated case
- RoHS Compliant



## Characteristics


Power rating:	2.25 Watts in free air
Operating voltage:	420V max
Dielectric strength:	1800Vac
Insulation resistance:	10GΩ min
Temperature coefficient:	As specified, referenced to 25°C, ΔR taken at +105°C
Short time overload:	ΔR ±0.3%, 2 times rated power with applied voltage not to exceed 1.5 times maximum continuous operating voltage for 5 seconds
Load life:	ΔR ±1.0%, 2000 hours at rated power
Damp heat with load:	ΔR ±0.5%, 40 ±2°C, 90 - 95% R.H max working voltage for 1000 hours with 1.5 hours "ON" and 0.5 hours "OFF"
Solderability:	90% min coverage, 245 ±5°C for 3 seconds
Thermal shock:	ΔR ±0.3%, -65°C - 150°C, 100 cycles
Terminal strength:	ΔR ±0.2%, 2.4 N
Vibration and high frequency:	ΔR ±0.2%, 20g peak

## Electrical Specifications

Resistance Value Range	Available Tolerance & Pref. Value Ranges	Available TCR
R1 - 1R	J (±5%) K (±10%)	Not specified
1R02 - 3R	F (±1%) , J (±5%) , K (±10%)	±300ppm/°C
3R01 - 10R		±100ppm/°C ±200ppm/°C
10R2 - 10K	D (±0.5%) F (±1%) J (±5%) K (±10%)	±50ppm/°C ±100ppm/°C ±200ppm/°C

Preferred value ranges:  
F (±1%) - E96 , J (±5%) - E24, K (±10%) - E12

## Derating Curve



ARCOL UK Limited,  
Threemilestone Ind. Estate,  
Truro, Cornwall, TR4 9LG, UK.  
T +44 (0) 1872 277431  
F +44 (0) 1872 222002  
E sales@arcolresistors.com

[www.arcolresistors.com](http://www.arcolresistors.com)


The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL.

# AP851 50 Watts TO-220 High Power Resistors



## Dimensions (mm)



ARCOL UK Limited,  
Threemilestone Ind. Estate,  
Truro, Cornwall, TR4 9LG, UK.  
T +44 (0) 1872 277431  
F +44 (0) 1872 222002  
E sales@arcolresistors.com

[www.arcolresistors.com](http://www.arcolresistors.com)

The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Ohmite:

[AP851 1K F 50PPM](#) [AP851 5K J 100PPM](#) [AP851 39R F 50PPM](#) [AP851 2K7 F 50PPM](#) [AP851 1K5 J 100PPM](#)  
[AP851 180R F 50PPM](#) [AP851 R2 J](#) [AP851 R3 J](#) [AP851 1R8 J](#) [AP851 470R F 50PPM](#) [AP851 39R J 100PPM](#)  
[AP851 2K2 J 100PPM](#) [AP851 3K9 J 100PPM](#) [AP851 100R J 100PPM](#) [AP851 68R J 100PPM](#) [AP851 5R F 100PPM](#)  
[AP851 2R2 F](#) [AP851 25R J 100PPM](#) [AP851 18R F 50PPM](#) [AP851 10R J 100PPM](#) [AP851 8K2 F 50PPM](#) [AP851](#)  
[220R J 100PPM](#) [AP851 120R J 100PPM](#) [AP851 4K7 F 50PPM](#) [AP851 27R F 50PPM](#) [AP851 82R J 100PPM](#) [AP851](#)  
[2R7 J](#) [AP851 27R J 100PPM](#) [AP851 R5 J](#) [AP851 3K9 F 50PPM](#) [AP851 1R8 F](#) [AP851 R4 J](#) [AP851 2K5 J 100PPM](#)  
[AP851 5K F 50PPM](#) [AP851 10R F 100PPM](#) [AP851 680R J 100PPM](#) [AP851 R7 J](#) [AP851 R8 J](#) [AP851 330R F 50PPM](#)  
[AP851 22R J 100PPM](#) [AP851 4K7 J 100PPM](#) [AP851 560R F 50PPM](#) [AP851 5K6 J 100PPM](#) [AP851 150R J 100PPM](#)  
[AP851 100R F 50PPM](#) [AP851 R6 J](#) [AP851 6R8 F 100PPM](#) [AP851 5R6 J 100PPM](#) [AP851 5K6 F 50PPM](#) [AP851](#)  
[2K7 J 100PPM](#) [AP851 1K8 F 50PPM](#) [AP851 50R J 100PPM](#) [AP851 1K5 F 50PPM](#) [AP851 270R F 50PPM](#) [AP851](#)  
[8R2 J 100PPM](#) [AP851 470R J 100PPM](#) [AP851 6K8 J 100PPM](#) [AP851 10K F 50PPM](#) [AP851 680R F 50PPM](#) [AP851](#)  
[1R5 F](#) [AP851 120R F 50PPM](#) [AP851 5R6 F 100PPM](#) [AP851 2R5 J](#) [AP851 15R J 100PPM](#) [AP851 47R J 100PPM](#)  
[AP851 12R J 100PPM](#) [AP851 18R J 100PPM](#) [AP851 22R F 50PPM](#) [AP851 1K8 J 100PPM](#) [AP851 3K3 J 100PPM](#)  
[AP851 8R2 F 100PPM](#) [AP851 270R J 100PPM](#) [AP851 2R2 J](#) [AP851 6K8 F 50PPM](#) [AP851 390R F 50PPM](#) [AP851](#)  
[150R F 50PPM](#) [AP851 820R J 100PPM](#) [AP851 1K2 F 50PPM](#) [AP851 820R F 50PPM](#) [AP851 330R J 100PPM](#)  
[AP851 3R9 J 100PPM](#) [AP851 47R F 50PPM](#) [AP851 1R2 F](#) [AP851 10K J 100PPM](#) [AP851 3R3 J 100PPM](#) [AP851 4R7](#)  
[J 100PPM](#) [AP851 390R J 100PPM](#) [AP851 25R F 50PPM](#) [AP851 56R F 50PPM](#) [AP851 68R F 50PPM](#) [AP851 1K J](#)  
[100PPM](#) [AP851 R1 J](#) [AP851 1K2 J 100PPM](#) [AP851 3K3 F 50PPM](#) [AP851 56R J 100PPM](#) [AP851 6R8 J 100PPM](#)  
[AP851 33R J 100PPM](#) [AP851 220R F 50PPM](#) [AP851 560R J 100PPM](#) [AP851 R9 J](#)