



219.3237

PLUG

32A 3P+N+E 6h 346-415V 50Hz 60Hz II 2GD
Screw terminals Low temperature [-50°C]

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	OPTIMA-EX[GD] Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	PLUG	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	PLUG		
Mounting version	PORTABLE		
Rated current	32A	EN 60309-1/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Poles	3P+N+E	EN 60309-2/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Hour position	6h		
Rated voltage (range)	250-400V	EN 60309-1/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Rated voltage	346-415V		
Working frequency	60Hz	EN 60309-2/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Working frequency	50Hz		
Colour	RED	EN 60079-0 (2012)	[European Standard] Explosive atmospheres. General requirements.
Material	THERMOPLASTIC	IEC 60079-0 (2011)	[International Standard] Electrical Apparatus for Explosive Gas Atmospheres - Part 0: General Requirements.
Protection degree	Splash proof	EN 60079-31 (2014)	[European Standard] Explosive atmospheres. Equipment dust ignition protection by enclosure "t"
Protection degree IP	IP66		
Types of available outlets	STRAIGHT	IEC 60079-31 (2013)	[International Standard] Explosive atmospheres - Part 31: Equipment dust ignition protection by enclosure "t"
Terminals	Screw terminals	EN 60079-0/A11 (2013)	[European Standard] Explosive atmospheres. General requirements.
Cable outlet	CABLE GLAND	EN 60079-1 (2014)	[European Standard] Electrical apparatus for explosive gas atmospheres - Part 1:

Group and categories EX	II 2GD		Flameproof enclosures 'd'
Ambient temperature Ta min	-50 °C	EN 60079-7 (2015)	[European Standard] Explosive atmospheres. Equipment protection by increased safety "e"
Ambient temperature Ta max	60 °C	IEC 60079-1 (2014)	[International Standard] Explosive atmospheres - Part 1: Equipment protection by flameproof enclosures "d".
Options	Low temperature [-50°C]	IEC 60079-7 (2015)	[International Standard] Explosive atmospheres - Part 7: Equipment protection by increased safety "e".
		DIRECTIVE ATEX 2014/34/UE	[European Directives] Atmosphere Explosive