NOT RECOMMENDED FOR NEW DESIGN **USE MB10S or MB10F**



HD01 - HD06


0.8A SURFACE MOUNT GLASS PASSIVATED BRIDGE RECTIFIER

Features and Benefits

- Glass Passivated Die Construction
- Low Forward Voltage Drop
- Surge Overload Rating to 30A Peak
- Ideally Suited for Automated Assembly
- Miniature Package Saves Space on PC Boards
- UL Listed Under Recognized Component Index, File Number E94661
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)

Mechanical Data

- Case: MiniDIP
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Tin. Plated Leads, Solderable per MIL-STD-202, Method 208 @3
- Polarity: As Marked on Case
- Marking: Product Type Marking Code, Date Code & Polarity
- Weight: 0.125 grams (Approximate)



Equivalent Circuit

Ordering Information (Note 3)


Part Number*	Packaging	Shipping
HDxx-T	MiniDIP	3k/Tape & Reel, 13-inch

^{*}xx = Device type, e.g. HD02-T or HD04-T, etc.

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and
- 3. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



HDxx = Product Type Marking Code (ex: HD04)

YM = Date Code Marking Y = Last Digit of the Year

M = See Month/Code Table Below

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D

NOT RECOMMENDED FOR NEW DESIGN USE MB10S or MB10F

HD01 - HD06

Maximum Ratings (@ $T_A = +25$ °C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Characteristic	Symbol	HD01	HD02	HD04	HD06	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RMM} V _{RWM} V _{DC}	100	200	400	600	V
RMS Reverse Voltage	V _{RMS}	70	140	280	420	V
Average Forward Rectified Current (Note 4) @T _A = +40°C	Io		0	.8		Α
Non-Repetitive Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I _{FSM}		3	0		Α

Thermal Characteristics


Characteristic	Symbol	Value	Unit
Typical Thermal Resistance, Junction to Ambient (Note 4)	$R_{ hetaJA}$	75	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C


Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Instantaneous Voltage Drop @ 0.4A (Per Element)	V_{F}	1.0	V
Peak Reverse Current at Rated @T _A = +25°C	lp.	5.0	μA
DC Blocking Voltage (Per Element) @T _A = +125°C	IR	500	μΛ
Typical Total Capacitance (Per Element) (Note 5)	Ст	10	pF

Notes:

- 4. Mounted on PC Board.
- 5. Measured at 1.0MHz and applied reverse voltage of 4.0V.






V_F, INSTANTANEOUS FORWARD VOLTAGE (V) Fig. 2 Typical Forward Characteristics (per element)



NOT RECOMMENDED FOR NEW DESIGN USE MB10S or MB10F

HD01 - HD06



NUMBER OF CYCLES AT 60 Hz Fig. 3 Maximum Peak Forward Surge Current (per element)





Fig. 4 Typical Total Capacitance (per element)




PERCENT OF RATED PEAK REVERSE VOLTAGE (%) Fig. 5 Typical Reverse Characteristics (per element)



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

MiniDIP




MiniDIP					
Dim	Min	Max			
Α		3.00			
A1	-	0.20			
A2	2.30	2.70			
A2a	1.20	1.60			
Ь	0.50	0.80			
C	0.15	0.35			
D	4.50	4.90			
ш		7.00			
E1	3.60	4.00			
е	2.30	2.70			
L	0.70	1.10			
L1	1.10	2.12			
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

MiniDIP



Dimensions	Value (in mm)
С	2.50
X	1.65
Υ	1.80
V1	6.00



NOT RECOMMENDED FOR NEW DESIGN USE MB10S or MB10F

HD01 - HD06

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

HD04-T HD06-T HD02-T HD01-T