



ENGLISH

Datasheet

RS Pro Black Rubber Tyred Wheel, 100kg

RS Stock No: **680-3858**



Product Details

RS Pro black rubber castor wheel weighs 100 kg. This is used to replace pneumatic tyred wheels in the market and has closed cell tyre construction that does not absorb water, freeze or crack. It has shore hardness that offers shock absorbance and 'ride' characteristics of a pneumatic wheel.

Features and Benefits

- Used to replace pneumatic tyred wheels in the market
- No requirement for re-inflation
- No costly downtime, service or repairs
- Puncture-proof
- Tyre life up to 4 times that of a pneumatic tyre
- Closed cell tyre construction does not absorb water, freeze or crack
- Shore hardness offers shock absorbance and 'ride' characteristics of a pneumatic wheel
- Polypropylene wheel hub, rubber tyre



Specifications:

Bore Diameter	20 mm
Bore Length	60 mm
Colour	Black
Features	Puncture Proof
Hub Bearing Type	Roller Bearing
Hub Diameter	60 mm
Hub Material	PP
Load Capacity	100 kg
Tyre Material	Rubber
Tyre Type	Pneumatic
Wheel Diameter	200 mm
Wheel Width	50 mm