




DATASHEET Part No. 1002289 Product: LTE / Cellular FPC Embedded Antenna

Part No.1002289

LTE / Cellular Wide Band FPC Embedded Antenna

700 / 750 / 850 / 900 / 1800 / 1900 / 2100 / 2700 MHz

Supports: Broadband LTE (OCTA-BAND), LTE CAT-M, NB-IoT, SigFox, LoRa, Cellular LPWA, RPMA, Firstnet



LTE / Cellular FPC Embedded Antenna

Low Band : 698 - 960 MHz High Band: 1710 - 2690 MHz

KEY BENEFITS Reduced Costs and Time-to-Market

Standard antenna eliminates design fees and cycle time associated with a custom solution; getting products to market faster.

Greater Flexibility with

Unique Form Factors

KYOCERA AVX technology helps you deliver more advanced ergonomic designs without adverse impact on product performance.

RoHS Compliant

Products are the latest RoHS version compliant.

APPLICATIONS

•	Medical	•	Automotive
	applications	•	Healthcare
•	Home	•	Point of Sale
	automation	•	Tracking
•	Smart	•	NB-loT
	metering	•	Sigfox
•	M2M,	•	LoRa
	Industrial	•	Cellular
	devices		LPWA
•	loT	•	RPMA
•	Firstnet	•	I TE CAT-M

KYOCERA AVX LTE cellular embedded antenna 1002289 address the challenges facing today's product designers. Based on a flexible substrate for easier integration, high performance and isolation characteristics, this antenna offers better connectivity. In addition, 1002289 supports all the worldwide cellular bands for LTE with backward compatibility.

The 1002289 is offered in many standard cable lengths ranging up to 200mm. Ordering part number guide is located at end of document for selection ease.

Electrical Specifications

Typical Characteristics, using 75 x 140 mm ground plane with 7.6 mm cable. Antenna is mounted directly on plastic material.

Frequency (MHz)	698 - 960 MHz	1710 – 2690 MHz	
Average Efficiency (Longer Edge)	74%	58%	
Average Efficiency (Shorter Edge)	67%	63%	
Peak Gain (Longer Edge)	2.9 dBi	4.3 dBi	
Peak Gain (Shorter Edge)	1.8 dBi	4.2 dBi	
VSWR Match	2.5:1 max		
Feed Point Impedance	50 ohms unbalanced		
Polarization	Linear		
Power Handling	2 Watts CW		
Radiation Pattern	Omni-directional		

Mechanical Specifications & Ordering Part Number

Ordering Part #	1002289		
Dimensions (mm)	53.6 x 25.1 x 0.2 (1.6 high at cable solder connection)		
Weight (grams)	0.86		
Connector / Cable (mm)	U.FL compatible connector Length: 7.6, Cable diameter: 1.13, Color: Black		
Mounting	using 3M468 Adhesive		

*Additional variations with different cable lengths, colors and connectors are available.

9/27/2021





Test Setup

Typical performance with 7.6 mm cable

Antenna Location 1

Antenna located at the end of the long edge of the PCB







In this position, the antenna is located 3 mm away from the PCB and 3 mm above the PCB

Antenna Location 2

Antenna located at the end of the short edge of the PCB.






In this position, the antenna is located 2 mm away from the PCB and 3 mm above the PCB

© 2021 KYOCERA AVX




VSWR, Efficiency and Peak Gain Plots


Typical performance with 7.6 mm (Location 1 & Location 2)




Low Band Efficiency





Low Band Peak Gain





High Band Efficiency





© 2021 KYOCERA AVX

Downloaded from Arrow.com.


tel +(1) 858.550.3820 email: <u>eth.info@KYOCERA-AVX.com</u>




Radiation Patterns


Typical performance with 7.6 mm cable


Antenna Location 1





Antenna Location 2





© 2021 KYOCERA AVX




Mechanical Dimensions

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)
1002289	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	7.6 ± 3.0	1.6 (max)	25 ± 3.0

*Total Height of 1.6 mm includes the cable solder connection *Height "C" of 0.2 mm includes FPC + adhesive thicknesses



© 2021 KYOCERA AVX



Ordering Part Numbers

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	D (mm) Cable Length	E (mm)	F (mm)
1002289	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	7.6 ± 3.0	1.6 (max)	25 ± 3.0
1002289F0-AA10L0025	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	25.0 ± 3.0	1.6 (max)	42.4 ± 3.0
1002289F0-AA10L0050	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	50.0 ± 3.0	1.6 (max)	67.4 ± 3.0
1002289F0-AA10L0065	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	65.0 ± 3.0	1.6 (max)	82.4 ± 3.0
1002289F0-AA10L0075	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	75.0 ± 3.0	1.6 (max)	92.4 ± 3.0
1002289F0-AA10L0080	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	80.0 ± 3.0	1.6 (max)	97.4 ± 3.0
1002289F0-AA10L0100	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	100.0 ± 3.0	1.6 (max)	117.4 ± 3.0
1002289F0-AA10L0110	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	110.0 ± 3.0	1.6 (max)	127.4 ± 3.0
1002289F0-AA10L0120	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	120.0 ± 3.5	1.6 (max)	137.4 ± 3.0
1002289F0-AA10L0150	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	150.0 ± 4.0	1.6 (max)	167.4 ± 3.0
1002289F0-AA10L0160	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	160.0 ± 4.0	1.6 (max)	177.4 ± 3.0
1002289F0-AA10L0200	53.6 ± 0.3	25.1 ± 0.3	0.2 ± 10%	200.0 ± 4.0	1.6 (max)	217.4 ± 3.0

*Total Height of 1.6 mm includes the cable solder connection *Height "C" of 0.2 mm includes FPC + adhesive thicknesses