

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 2 of 9

Hazard components for labelling

Hydrocarbons, C6, isoalkanes, <5% n-hexane
propan-2-ol; isopropyl alcohol; isopropanol
1-Methoxy-2-propanol
butanone; ethyl methyl ketone

Signal word: Danger**Pictograms:****Hazard statements**

H222 Extremely flammable aerosol.
H229 Pressurised container: May burst if heated.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.
H411 Toxic to aquatic life with long lasting effects.

Precautionary statements

P211 Do not spray on an open flame or other ignition source.
P210 Keep away from heat. No Smoking.
P251 Do not pierce or burn, even after use.
P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P403 Store in a well-ventilated place.
P271 Use only outdoors or in a well-ventilated area.
P273 Avoid release to the environment.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 3 of 9

Hazardous components

CAS No	Chemical name			Quantity
	EC No	Index No	REACH No	
	GHS Classification			
	Hydrocarbons, C6, isoalkanes, <5% n-hexane <0,1% Benzol			25-50%
	931-254-9		01-2119484651-34	
	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H315 H336 H304 H411			
67-63-0	propan-2-ol; isopropyl alcohol; isopropanol			25-50 %
	200-661-7	603-117-00-0		
	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336			
927-356-8	Hydrocarbons, C9-C11, n-alkane, isoalkane, cyclic, <2% aromatic			10-25%
			01-2119463258-33	
	Flam. Liq. 3, STOT SE 3, Asp. Tox. 1; H226 H336 H304			
107-98-2	1-Methoxy-2-propanol			10-25 %
	203-539-1		01-2119457435-35	
	Flam. Liq. 3, STOT SE 3; H226 H336			
124-38-9	Carbondioxide			2,5-10 %
	204-696-9			
	Compressed gas; H280			
78-93-3	butanone; ethyl methyl ketone			2,5-10 %
	201-159-0	606-002-00-3		
	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336 EUH066			

Full text of H and EUH statements: see section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

After inhalation

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

If product gets into the eye, keep eyelid open and rinse immediately with large quantities of water, for at least 5 minutes. Subsequently consult an ophthalmologist.

After ingestion

If swallowed, immediately drink: Water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Foam. Carbon dioxide (CO₂). Extinguishing powder.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 4 of 9

Unsuitable extinguishing media

Water with tenside additive. Water.

5.2. Special hazards arising from the substance or mixture

Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Use water spray jet to protect personnel and to cool endangered containers. Suppress gases/vapours/mists with water spray jet. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed.

Hints on joint storage

Do not store together with: Material, rich in oxygen, oxidizing.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
107-98-2	1-Methoxypropan-2-ol	100	375		TWA (8 h)	WEL
		150	560		STEL (15 min)	WEL
78-93-3	Butan-2-one (methyl ethyl ketone)	200	600		TWA (8 h)	WEL
		300	899		STEL (15 min)	WEL
124-38-9	Carbon dioxide	5000	9150		TWA (8 h)	WEL
		15000	27400		STEL (15 min)	WEL
67-63-0	Propan-2-ol	400	999		TWA (8 h)	WEL
		500	1250		STEL (15 min)	WEL

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 5 of 9

Biological Monitoring Guidance Values (EH40)

CAS No	Substance	Parameter	Value	Test material	Sampling time
78-93-3	Butan-2-one	butan-2-one	70 µmol/L	urine	Post shift

8.2. Exposure controls



Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: NBR (Nitrile rubber) For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. NBR (Nitrile rubber)

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection. Combination filter device (DIN EN 141).. Filter AX

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Aerosol
Colour:	farblos
Odour:	characteristic

Changes in the physical state

Initial boiling point and boiling range:	60 °C
Flash point:	<0 °C
Lower explosion limits:	1,2 vol. %
Upper explosion limits:	13,1 vol. %
Ignition temperature:	270 °C
Density (at 20 °C):	0,72 g/cm ³
Solvent content:	95%

SECTION 10: Stability and reactivity

10.1. Reactivity

No data available

10.2. Chemical stability

No data available

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 6 of 9

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane <0,1% Benzol				
	oral	LD50 >1000 mg/kg	Fisch 1		

Irritation and corrosivity

Irritating to eyes. Vapours may cause drowsiness and dizziness. After skin contact: irritant.

SECTION 12: Ecological information

12.1. Toxicity

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h] [d]	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane <0,1% Benzol					
	Acute algae toxicity	ErC50 >1000 mg/l	72 h	Alge		
	Acute crustacea toxicity	EC50 >1000 mg/l	48 h	Daphnia pulex (water flea)		

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 7 of 9

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information**Land transport (ADR/RID)**

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 625
Limited quantity: 1 L
Transport category: 2
Tunnel restriction code: D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)

E0

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 8 of 9

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number:	UN1950
14.2. UN proper shipping name:	AEROSOLS, flammable
14.3. Transport hazard class(es):	2.1
Hazard label:	2.1
Special Provisions:	A145 A167
Limited quantity Passenger:	30 kg G
IATA-packing instructions - Passenger:	203
IATA-max. quantity - Passenger:	75 kg
IATA-packing instructions - Cargo:	203
IATA-max. quantity - Cargo:	150 kg

**Other applicable information (air transport)**E0
: Y203**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: yes



Danger releasing substance: Hydrocarbons

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 28: Hydrocarbons, C6, isoalkanes, <5% n-hexane <0,1% Benzol

2004/42/EC (VOC): 44,1 % (317,52 g/l)

National regulatory information

Water contaminating class (D): 2 - clearly water contaminating

SECTION 16: Other information**Relevant H and EUH statements (number and full text)**

H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
EUH066	Repeated exposure may cause skin dryness or cracking.



Safety Data Sheet

according to Regulation (EC) No 1907/2006

Spraywash

Revision date: 18.11.2019

Product code: 105

Page 9 of 9

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)