

CHARACTERISTICS

MATERIALS

HOUSING : ABS+PC
 HOUSING COLOR : GREY
 BOOT/SLEEVE : THERMOPLASTIC POLYURETHANE
 CONTACTS : COPPER ALLOY
 CONTACT PLATING : 7µ" GOLD PLATED OVER 196µ" NICKEL MIN.
 INSULATOR : PPS (HIGH TEMPERATURE)

MECHANICAL

DURABILITY: 2000 CYCLES
 OPERATING TEMP. RANGE: -20° C ~ +120° C
 PROCESS TEMPERATURE : 260°C FOR 5 SECONDS
 MAX. TORQUE VALUE: 0.5Nm [4.4 IN/LBS]

IP RATING: 50

CHART B

COLLET SIZE	WIRE DIAMETER
42	2.20 [0.087] ~ 4.00 [0.157]
52	4.00 [0.157] ~ 5.00 [0.197]
62	5.00 [0.197] ~ 6.00 [0.236]




CHART A

● = KEY LOCATION

VIEW FROM TERMINATION END

2 POSITION 22 AWG MAX. 10 AMP MAX. PIN Ø = 1.30 [0.051]	3 POSITION 22 AWG MAX. 10 AMP MAX. PIN Ø = 1.30 [0.051]	4 POSITION 22 AWG MAX. 8 AMP MAX. PIN Ø = 0.90 [0.035]	5 POSITION 22 AWG MAX. 7 AMP MAX. PIN Ø = 0.90 [0.035]	6 POSITION 24 AWG MAX. 6 AMP MAX. PIN Ø = 0.70 [0.028]	7 POSITION 24 AWG MAX. 5 AMP MAX. PIN Ø = 0.70 [0.028]	8 POSITION 24 AWG MAX. 5 AMP MAX. PIN Ø = 0.70 [0.028]	9 POSITION 26 AWG MAX. 3 AMP MAX. PIN Ø = 0.50 [0.020]	10 POSITION 26 AWG MAX. 3 AMP MAX. PIN Ø = 0.50 [0.020]
CONTACT RESISTANCE = 5 mΩ TEST VOLTAGE = 1200V WORKING VOLTAGE = 400V	CONTACT RESISTANCE = 5 mΩ TEST VOLTAGE = 1200V WORKING VOLTAGE = 400V	CONTACT RESISTANCE = 6 mΩ TEST VOLTAGE = 1200V WORKING VOLTAGE = 400V	CONTACT RESISTANCE = 6 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 10 mΩ TEST VOLTAGE = 850V WORKING VOLTAGE = 280V	CONTACT RESISTANCE = 10 mΩ TEST VOLTAGE = 850V WORKING VOLTAGE = 280V

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN: M. SIGMON

DATE: 10-04-16

SCALE: N.T.S.

SHEET 1 OF 1

REV: 2

DWG NO. 8P1PYYY17BYLYY1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

<u>8P1P00817BNL621</u>	<u>8P1P01417BJL421</u>	<u>8P1P01417BRL421</u>	<u>8P1P00717BVL621</u>	<u>8P1P00217BJL621</u>
<u>8P1P00217BGL521</u>	<u>8P1P00517BJL521</u>	<u>8P1P00917BVL421</u>	<u>8P1P00517BGL621</u>	<u>8P1P00617BNL621</u>
<u>8P1P00417BVL521</u>	<u>8P1P00317BAL421</u>	<u>8P1P00617BNL421</u>	<u>8P1P00517BRL421</u>	<u>8P1P00817BVL621</u>
<u>8P1P00217BJL521</u>	<u>8P1P00517BGL421</u>	<u>8P1P00817BRL421</u>	<u>8P1P00417BNL621</u>	<u>8P1P00617BVL521</u>
<u>8P1P00517BRL621</u>	<u>8P1P01017BAL521</u>	<u>8P1P00917BNL521</u>	<u>8P1P00817BAL421</u>	<u>8P1P01417BRL521</u>
<u>8P1P00517BAL421</u>	<u>8P1P00917BGL621</u>	<u>8P1P00717BJL521</u>	<u>8P1P01417BNL521</u>	<u>8P1P00517BVL421</u>
<u>8P1P00917BVL621</u>	<u>8P1P00317BRL521</u>	<u>8P1P00217BRL621</u>	<u>8P1P00317BAL621</u>	<u>8P1P00817BGL621</u>
<u>8P1P00517BNL421</u>	<u>8P1P00717BRL621</u>	<u>8P1P00817BAL621</u>	<u>8P1P00417BAL421</u>	<u>8P1P01017BNL621</u>
<u>8P1P00717BNL621</u>	<u>8P1P00617BRL621</u>	<u>8P1P00817BVL421</u>	<u>8P1P00617BAL421</u>	<u>8P1P00417BAL621</u>
<u>8P1P01017BNL421</u>	<u>8P1P00617BGL421</u>	<u>8P1P00917BRL421</u>	<u>8P1P01017BJL621</u>	<u>8P1P00717BNL421</u>
<u>8P1P01417BGL421</u>	<u>8P1P00917BAL621</u>	<u>8P1P00417BNL421</u>	<u>8P1P00917BGL421</u>	<u>8P1P00317BJL521</u>
<u>8P1P01417BAL621</u>	<u>8P1P00317BVL621</u>	<u>8P1P00717BVL521</u>	<u>8P1P01017BJL421</u>	<u>8P1P00417BRL421</u>
<u>8P1P00817BNL421</u>	<u>8P1P00317BVL421</u>	<u>8P1P00217BVL421</u>	<u>8P1P01417BGL521</u>	<u>8P1P00817BAL521</u>
<u>8P1P01017BAL421</u>	<u>8P1P00217BNL621</u>	<u>8P1P00617BGL621</u>	<u>8P1P00717BVL421</u>	<u>8P1P00317BNL521</u>
<u>8P1P00217BAL621</u>	<u>8P1P00317BNL621</u>	<u>8P1P00417BGL621</u>	<u>8P1P00417BVL621</u>	<u>8P1P01417BJL521</u>
<u>8P1P00417BGL421</u>	<u>8P1P00217BRL421</u>	<u>8P1P00417BRL521</u>	<u>8P1P00617BJL621</u>	<u>8P1P00717BRL421</u>
<u>8P1P01417BVL621</u>	<u>8P1P01017BVL521</u>	<u>8P1P00517BAL621</u>	<u>8P1P00717BGL621</u>	<u>8P1P01017BGL421</u>
<u>8P1P00517BRL521</u>	<u>8P1P00217BVL521</u>	<u>8P1P00617BRL421</u>	<u>8P1P00817BRL621</u>	<u>8P1P01017BGL521</u>
<u>8P1P00717BGL421</u>	<u>8P1P00917BVL521</u>	<u>8P1P00417BVL421</u>	<u>8P1P00917BJL621</u>	<u>8P1P00217BGL621</u>
<u>8P1P00617BJL421</u>	<u>8P1P01417BRL621</u>	<u>8P1P00217BGL421</u>	<u>8P1P00217BAL421</u>	<u>8P1P01417BNL621</u>